




Clear Covers for HTCT HTAPs

Type CLRCVR

- Made of high impact plastic to provide high impact strength and 360° inspections of crimped connection to assure the crimp is complete and the correct die was used
- Incorporate dual self-latching spring loaded latches and supplied with two Panduit UL 94 V-0 cable ties to allow for easy snap-on assembly and ensure covers are secured
- Low profile design minimizes space requirements
- Each cover half supports installation information labels inside plastic retainer strips to allow labels to be viewed on either side of cover and to protect labels from being removed



- Incorporate molded in flash barriers which encompass the HTAP installation providing protection against electrical flash over
- UL 94 V-0 flame rating and oxygen index of 28 providing self-extinguishing, flame retardant properties
- Part number, voltage rating, temperature rating and HTCT part number molded into cover for easy identification
- See page D3.33 for detailed installation instructions



| Part Number | Use with HTAP Part Number | Figure Dimensions In. (mm) | | | Std. Pkg. Qty. |
|-------------|---------------------------|-------------------------------|----------------|----------------|----------------------|
| | | L | W | H | |
| CLRCVR1-1 | HTCT6X-6X | 4.48 (113.8) | 1.41 (35.8) | 1.20 (30.5) | 1 |
| CLRCVR2-1 | HTCT2-2 | 5.10 (129.5) | 1.66 (42.2) | 1.40 (35.6) | 1 |
| CLRCVR3-1 | HTCT250-2, HTCT250-250 | 5.35 (135.9) | 2.16 (54.9) | 1.40 (35.6) | 1 |




Black Covers for Copper HTAPs and CTAPs

- Used to insulate connectors and protect tap connections from corrosive environments
- UL Listed and CSA Certified with approved connectors for use up to 600 V and temperature rated to 90° C



- Made of durable, weather-resistant black polypropylene
- Double locking latches provide secure cover installation



| Part Number | Use with CTAP Part Number | Use with HTAP Part Number | Figure Dimensions (In.) | | | Std. Pkg. Qty. |
|-------------|---|----------------------------|----------------------------|------|------|----------------------|
| | | | L | W | H | |
| CVR6-1 | CTAP4-8-L, CTAP4-6-L, CTAP4-4-L | HTCT6X-6X-1 | 2.00 | 1.20 | 1.26 | 1 |
| CVR2-1 | CTAP2-4-Q, CTAP2-2-X, CTAP2/0-2-X | HTCT2-2-1 | 3.38 | 1.40 | 2.00 | 1 |
| CVR250-1 | CTAP2/0-2/0-X | HTCT250-2-1, HTCT250-250-1 | 3.38 | 1.55 | 2.05 | 1 |
| CVR500-1* | CTAP4/0-2-X, CTAP4/0-2/0-X, CTAP4/0-4/0-X | — | 3.86 | 1.97 | 2.66 | 1 |
| CVR1000-1* | — | — | 5.62 | 2.45 | 3.72 | 1 |

For information on copper HTAPs, see page D3.14

For information on copper CTAPs, see page D3.12

*Not CSA Certified.

A.
System
Overview

B1.
Cable Ties

B2.
Cable
Accessories

B3.
Stainless
Steel Ties

C1.
Wiring
Duct

C2.
Surface
Raceway

C3.
Abrasion
Protection

C4.
Cable
Management

D1.
Terminals

D2.
Power
Connectors

D3.
Grounding
Connectors

E1.
Labeling
Systems

E2.
Labels

E3.
Pre-Printed
& Write-On
Markers

E4.
Permanent
Identification

E5.
Lockout/
Tagout
& Safety
Solutions

F.
Index

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[CVR1000-1](#) [CVR6-1](#) [CVR2-1](#)