


QuickNet™ PanMPO™ Round Interconnect Cable Assemblies

technical information

PanMPO™ Round Interconnect Cable Assemblies are pre-terminated 12-fiber cable assemblies. The unique design of the PanMPO™ Connector allows for rapid gender and polarity change in the field, in support of standards-compliant cable plant migration from 10G cassette-based systems to 40G MPO connector-based parallel optics cable plant. PanMPO™ Interconnect Assemblies meet the demands of 10G Ethernet and higher speed 40G Ethernet and high speed ANSI Fibre Channel systems while maintaining compliance to the recommendations of TIA 568C for both Serial Duplex and Parallel Optics wiring schemes.



application

Method A and Method B TIA-568-C compliant for 40G parallel optics multimode applications. 10G Horizontal cabling systems with cassettes and/or harnesses; Horizontal cabling systems and patch cords for 40G parallel optic multimode systems. In horizontal cabling applications, intended for use in FiberRunner® or equivalent protected pathway. Provides easy migration path from 10G serial to 40G parallel optics for horizontal cabling applications.

construction

Cable type:	3.0mm indoor round	
Cable jacket ratings:	Optical Fiber Nonconductive Plenum (OFNP) Low Smoke Zero Halogen (LSZH)	
Fiber types:	Multimode:	OM3 50/125µm OM4 50/125µm
Connector types; end 'A' and end 'B':	PanMPO Female or PanMPO Male	
Fiber count:	12	
Jacket color:	OM3:	Aqua
	OM4:	Aqua

physical properties

Cable outside diameter (OD):	3.0mm
Minimum bend radius:	30mm
Cable retention strength:	50N
Flex:	100 cycles at 4.9N
Twist:	10 cycles at 15N
Connector durability:	500 mating cycles*
Gender reversal durability:	50 cycles
Polarity reversal durability:	50 cycles

optical properties

Maximum cable attenuation:	Multimode:	3.5dB/km at 850nm 1.5dB/km at 1300nm
Maximum connector insertion loss:	Standard Multimode: Optimized Multimode:	0.50dB 0.35dB
Minimum connector return loss:	Multimode:	OM3 26dB OM4 26dB

environmental properties

Storage and shipping temperature:	-40°C to 70°C
Installation temperature:	0°C to 40°C
Operating temperature:	-10°C to 60°C

standards

Meets or exceeds TIA/EIA-568-C.3,
TIA-604-5 (FOCIS-5), TIA/EIA-568-C.1, RoHS Compliant

*With proper cleaning and inspection.

QuickNet™ PanMPO™ Round Interconnect Cable Assemblies

part number

Example: FZTRP7N7NANM001 = Fiber OM4, 12-fibers, 3.0mm round indoor, plenum rated, PanMPO female to PanMPO female, polarity method A, no pulling eye, 1 meter

CHARACTER	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15
EXAMPLE	F	Z	T	R	P	7	N	7	N	A	N	M	0	0	1

1 – Fiber Product

F = Fiber

2 – Fiber Type

X = OM3 50/125

Z = OM4 50/125

3 – Fiber Count

T = 12-fibers

4 – Cable Type

R = 3.0mm round indoor

5 – Jacket Type

L = Low Smoke Zero Halogen (LSZH)

P = Optical Fiber Nonconductive

Plenum (OFNP)

6 – Connector Type End 'A'

7 = PanMPO female

8 = PanMPO male

7 – Connector Variant (end A)

N = No variant

8 – Connector Type End 'B'

7 = PanMPO female

8 = PanMPO male

9 – Connector Variant (end B)

N = No variant

10 – Construction/Performance

A = Polarity A – standard IL

B = Polarity B – standard IL

X = Polarity A – optimized IL

Y = Polarity B – optimized IL

11 – Other

N = No pulling eye

12 – Unit of Length

F = Feet


M = Meters

13, 14, 15 – Length

1 – 30m (001-030)

3 – 100 feet (003-100)

cable assembly detail



WORLDWIDE SUBSIDIARIES AND SALES OFFICES

PANDUIT CANADA
Markham, Ontario
cs-cdn@panduit.com
Phone: 800.777.3300

PANDUIT EUROPE LTD.
London, UK
cs-emea@panduit.com
Phone: 44.20.8601.7200

PANDUIT SINGAPORE PTE. LTD.
Republic of Singapore
cs-ap@panduit.com
Phone: 65.6305.7575

PANDUIT JAPAN
Tokyo, Japan
cs-japan@panduit.com
Phone: 81.3.6863.6000

PANDUIT LATIN AMERICA
Guadalajara, Mexico
cs-la@panduit.com
Phone: 52.33.3777.6000

PANDUIT AUSTRALIA PTY. LTD.
Victoria, Australia
cs-aus@panduit.com
Phone: 61.3.9794.9020

For a copy of Panduit product warranties, log on to www.panduit.com/warranty

For more information

Visit us at www.panduit.com

Contact Customer Service by email: cs@panduit.com
or by phone: 800.777.3300

PANDUIT®

©2013 Panduit Corp.
ALL RIGHTS RESERVED.
FBSP76--WW-ENG
6/2013

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

FXTRP7N7NYNM019	FXTRP7N7NXNM023	FXTRP7N7NBNM023	FXTRP7N7NANM005	FXTRP7N7NXNM026
FXTRP7N7NXNM016	FXTRP7N7NBNM003	FXTRP7N7NANM023	FXTRP7N7NANM013	FXTRP7N7NXNM003
FXTRP7N7NXNM020	FXTRP7N7NBNM013	FXTRP7N7NYNM029	FXTRP7N7NYNM003	FXTRP7N7NXNM013
FXTRP7N7NANM007	FXTRP7N7NANM009	FXTRP7N7NBNM012	FXTRP7N7NYNM028	FXTRP7N7NANM029
FXTRP7N7NYNM009	FXTRP7N7NBNM019	FXTRP7N7NBNM010	FXTRP7N7NYNM026	FXTRP7N7NBNM020
FXTRP7N7NBNM016	FXTRP7N7NANM026	FXTRP7N7NANM016	FXTRP7N7NANM019	FXTRP7N7NYNM016
FXTRP7N7NANM027	FXTRP7N7NYNM024	FXTRP7N7NYNM008	FXTRP7N7NANM015	FXTRP7N7NYNM006
FXTRP7N7NBNM006	FXTRP7N7NYNM015	FXTRP7N7NXNM008	FXTRP7N7NYNM005	FXTRP7N7NANM008
FXTRP7N7NYNM011	FXTRP7N7NYNM022	FXTRP7N7NBNM026	FXTRP7N7NXNM012	FXTRP7N7NBNM009
FXTRP7N7NANM018	FXTRP7N7NXNM015	FXTRP7N7NANM012	FXTRP7N7NANM006	FXTRP7N7NBNM008
FXTRP7N7NXNM028	FXTRP7N7NXNM010	FXTRP7N7NBNM022	FXTRP7N7NXNM025	FXTRP7N7NXNM006
FXTRP7N7NBNM018	FXTRP7N7NXNM021	FXTRP7N7NBNM025	FXTRP7N7NYNM023	FXTRP7N7NBNM024
FXTRP7N7NYNM007	FXTRP7N7NXNM009	FXTRP7N7NYNM012	FXTRP7N7NXNM029	FXTRP7N7NBNM005
FXTRP7N7NBNM017	FXTRP7N7NXNM018	FXTRP7N7NBNM028	FXTRP7N7NXNM005	FXTRP7N7NYNM010
FXTRP7N7NANM024	FXTRP7N7NBNM021	FXTRP7N7NANM021	FXTRP7N7NYNM014	FXTRP7N7NANM022
FXTRP7N7NBNM011	FXTRP7N7NBNM014	FXTRP7N7NXNM004	FXTRP7N7NXNM007	FXTRP7N7NANM014
FXTRP7N7NANM004	FXTRP7N7NANM025	FXTRP7N7NYNM017	FXTRP7N7NXNM011	FXTRP7N7NANM002
FXTRP7N7NBNM007	FXTRP7N7NXNM027	FXTRP7N7NXNM014	FXTRP7N7NYNM013	FXTRP7N7NANM017
FXTRP7N7NXNM002	FXTRP7N7NANM020	FXTRP7N7NXNM019	FXTRP7N7NYNM004	FXTRP7N7NANM028
FXTRP7N7NBNM015	FXTRP7N7NYNM021	FXTRP7N7NXNM017	FXTRP7N7NXNM022	FXTRP7N7NANM011