WWW.PHIHONG.COM

20 Watt Interchangeable Plug Series

Interchangeable Clips Sold Separately

Features

- Efficiency Level VI Compliant
- Class B EMI
- Ecodesign ErP Directive 2009/125/EC Level 2 annex 1b Compliant
- No-load Power Saving
- High Efficiency
- Compact Size
- Class II Double Insulated

Applications

- Peripherals
- Gaming Machines
- Point of Sale Equipment
- Network Equipment

Safety Approvals

- UL/cUL 60950-1
- CE
- CB
- SAA+C-TICK+MEPS

Mechanical Characteristics

- Length: 82.7mm (3.26in)
- Width: 55mm (2.17in)
- Height: 39mm (1.54in)
- Weight: 180g (6.35oz)

Output Specifications

Model	DC Output Voltage	Load		Regulation		Ripple[1] P-P (max.)	Output Power
		Min.	Max.	Line	Load		
PSAA20R-050L6	5V	0A	4.00A	±5%		100mV	20W

Notes:1- Measured with by-pass capacitors 0.1uF/10uF at output connector terminal & oscilloscope set at 20 MHz.(30 minute warm up period)

Phihong is not responsible for any error, and reserves the right to make changes without notice. Please visit our website at www.phihong.com for the most up-to-date specifications and contact information.

PSAA20R Characteristics WWW.PHIHONG.COM

Input:

AC Input Voltage Rating
100 to 240V AC

AC Input Voltage Range
90V AC to 264V AC

AC Input Frequency
47 to 63Hz

Input Current
0.8A (RMS) Max. @120VAC & Max. load
0.5A (RMS) Max. @240VAC & Max. load

Leakage Current
0.25mA maximum at 264V AC/60Hz

Inrush Current
60A Max. @100VAC & Max. load
100A Max. @240VAC & Max. load (Cold start at ambient 25°C)

Input Power Saving
<0.1W Max. @230VAC, 50Hz

Output

Efficiency
DOE Level VI

Hold-up Time
10ms Min.@ full load 115VAC/ 60Hz

Over-Current Protection
Auto Restart.

Short-Circuit Protection
Output can be shorted permanently without damage

Over Voltage Protection
10VDC max

Environmental:

Temperature

Operation	0 to +40°C
Non-operation	-20 to +75°C
Humidity	20 to 90%

Emissions
Complies with FCC Class B
Complies with EN55032 Class B

Immunity

EN61000-4-2	Level 4
EN61000-4-3	Level 2
EN61000-4-4	Level 2
EN61000-4-5	Level 2
EN61000-4-6	Level 2
EN61000-4-8	Level 1
EN61000-4-11	

Dielectric Withstand (Hi-pot) Test
Primary to Secondary: 3000 Vac or 4242 Vdc , 10 mA 1minute. 3600 Vac or 5090 Vdc , 10 mA 3Second.

DC Output Connector
2.1mm x 5.5mm x 10mm Center conductor positive

DC Cord Length
1000mm

AC Input clips (sold separately)
RPA – US
RPB – Brazil
RPC – China
RPE – Europe
RPH – Korea
RPI – India
RPK – UK
RPN – Argentina
RPS – Australia
RPX – IEC320 C8

Dimension Diagram Unit: mm (inch)



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Phihong:
PSAA20R-050L6-R-CR1