

I/O extension module - NLC-IO-4AI - 2701098

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



I/O extension module for use with Nanoline base unit. Equipped with 4 analog input channels. A maximum of three I/O extension modules can be attached to a base unit.

Your advantages

- ✓ Automatically recognized by the firmware
- ✓ I/O modules are electrically isolated
- ✓ Can be powered from a secondary power supply
- ✓ A system may have up to 8 analog inputs and 8 analog outputs
- ✓ Configuration options for 0 - 10 V DC, ± 10 V DC, 4 - 20 mA, and 0 - 20 mA
- ✓ Up to 3 modules can be added to the right side of a base unit

RoHS

Key Commercial Data

Packing unit	1 pc
GTIN	 4 046356 325318
GTIN	4046356325318

Technical data

Note

Utilization restriction	EMC: class A product, see manufacturer's declaration in the download area
-------------------------	---

Dimensions

Width	40 mm
Height	103.5 mm
Depth	43 mm

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-25 °C ... 60 °C
Ambient temperature (storage/transport)	-25 °C ... 85 °C

I/O extension module - NLC-IO-4AI - 2701098

Technical data

Supply

Supply voltage	24 V DC
Supply current	nom. 50 µA
	max. 90 µA

Analog inputs


Description of the input	Single ended
Input name	Analog inputs
Number of inputs	4 (Voltage or current can be chosen separately)
Connection method	Individual wires
Connection technology	Screw connection
Resolution A/D	12 bit
Limit frequency (3 dB)	5 Hz
Current input signal	0 mA ... 20 mA
	4 mA ... 20 mA
Input resistance current input	120 Ω
Voltage input signal	0 V ... 10 V
	-10 V ... 10 V
Input resistance of voltage input	200 kΩ

Environmental Product Compliance


China RoHS	Environmentally Friendly Use Period = 50
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

Drawings

Dimensional drawing



Connection diagram



Approvals

Approvals

Approvals

UL Listed / EAC

I/O extension module - NLC-IO-4AI - 2701098

Approvals

Ex Approvals

Approval details

UL Listed



<http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm>

FILE E 238705

EAC



EAC-Zulassung

Phoenix Contact 2018 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[2701098](#)