

Mounting kit - NLC-OP1-MKT - 2701140

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Mounting kit



Product Description

Mounting kit for Nanoline Operator Panel. Includes receptor housing installed in base unit, mounting brackets for installation in cabinet and cable to connect base unit.

RoHS

Key Commercial Data

Packing unit	1 pc
GTIN	 4 046356 325271
GTIN	4046356325271

Technical data

Note

Utilization restriction	EMC: class A product, see manufacturer's declaration in the download area
-------------------------	---

Dimensions

Width	76 mm
Height	31.5 mm
Depth	46 mm

Ambient conditions

Ambient temperature (operation)	0 °C ... 50 °C
Ambient temperature (storage/transport)	0 °C ... 60 °C

Supply

Max. current consumption	50 mA
Typical current consumption	32 mA

General

Mounting kit - NLC-OP1-MKT - 2701140

Technical data

General


Mounting type	Control cabinet door mounting
---------------	-------------------------------

Environmental Product Compliance

China RoHS	Environmentally Friendly Use Period = 50
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

Drawings

Schematic diagram



Articles in set

Mounting unit - NLC-OP1-MKT-BASE - 2701250



Panel to mount in base unit, RJ-45 connector for remote Operator Panel

Mounting brackets - NLC-OP1-MKT-BRACKET - 2701263



Mounting bracket for remote installation of Operator Panel

Cable - NLC-OP1-MKT-CBL - 2701438



Cable for operator terminal

Phoenix Contact 2018 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[2701140](#)