

## Equipment marking - EML-ESD (8X8)R - 0830564

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Equipment marking, Roll, white, unlabeled, can be labeled with: THERMOMARK ROLLMASTER 300/600, THERMOMARK X1.2, THERMOMARK ROLL X1, THERMOMARK ROLL 2.0, THERMOMARK ROLL, mounting type: adhesive, lettering field size: 8 x 8 mm, Number of individual labels: 4000

### Your advantages

- ✓ The EML-ESD label is well suited for marking sensitive components on printed-circuit boards
- ✓ The label includes an adhesive that dissipates static electricity, which prevents the transmission of electrostatic voltages and protects the component
- ✓ When combined with the right ink ribbon, the marking is highly resistant to solvents
- ✓ The EML-ESD ... materials are UL-listed
- ✓ Labeling service: Phoenix Contact can custom-label all EML-ESD ... markers in accordance with your requirements



### Key Commercial Data

|              |                                                                                                         |
|--------------|---------------------------------------------------------------------------------------------------------|
| Packing unit | 1 pc                                                                                                    |
| GTIN         | <br>4 046356 719131 |
| GTIN         | 4046356719131                                                                                           |

### Technical data

#### Dimensions

|            |      |
|------------|------|
| Length (b) | 8 mm |
| Width (a)  | 8 mm |

#### Ambient conditions

|                                 |                                                                                                         |
|---------------------------------|---------------------------------------------------------------------------------------------------------|
| Ambient temperature (operation) | -40 °C ... 150 °C                                                                                       |
| Ambient temperature (assembly)  | > 4 °C                                                                                                  |
| Recommended storage conditions  | 23 °C/50 % relative humidity. Storage in a dry and dark place in the original packaging is recommended. |

#### General

|            |                                |
|------------|--------------------------------|
| Color      | white                          |
| Components | free from silicone and halogen |

## Equipment marking - EML-ESD (8X8)R - 0830564

### Technical data

#### General

|                                                                     |                                     |
|---------------------------------------------------------------------|-------------------------------------|
| Material                                                            | Polyester                           |
| RoHS compliant                                                      | Yes                                 |
| Wipe resistance                                                     | DIN EN 61010-1 (VDE 0411-1)         |
| Number of individual labels                                         | 4000                                |
| Number of individual labels per row                                 | 4                                   |
| Adhesive                                                            | Acrylic                             |
| Printability                                                        | Thermal transfer                    |
| Device                                                              | 1085260 THERMOMARK ROLL 2.0         |
|                                                                     | 0804501 THERMOMARK ROLLMASTER 300   |
|                                                                     | 0804663 THERMOMARK ROLLMASTER 600   |
|                                                                     | 5146723 THERMOMARK ROLL X1          |
|                                                                     | 5146231 THERMOMARK X1.2             |
| Ink ribbon                                                          | 5145384 THERMOMARK-RIBBON 110       |
| Test for substances that would hinder coating with paint or varnish | VW PV 3.10.7:2005-02                |
| Result                                                              | Test passed                         |
| Test specification weathering-resistance                            | Following ISO 4892-2:2013-03        |
| Test duration                                                       | 96 h                                |
| Result of weather resistance test                                   | Test passed                         |
| Salt spray test specification                                       | DIN EN 60068-2-11:2000-02           |
| Test duration                                                       | 96 h                                |
| Salt spray testing result                                           | Test passed                         |
| Wipe resistance of test specification inscriptions                  | DIN EN 61010-1 (VDE 0411-1):2011-07 |
| Result of wipe resistance test                                      | Test passed                         |
| Foil strength                                                       | 52 µm                               |
| Adhesive strength                                                   | 24 µm                               |
| Marking mounting type                                               | adhesive                            |
| File number                                                         | UL-MH48542 / PC-026                 |

#### Standards and Regulations

|                                  |                             |
|----------------------------------|-----------------------------|
| Connection in acc. with standard | UL                          |
| Wipe resistance                  | DIN EN 61010-1 (VDE 0411-1) |

### Classifications

#### eCl@ss

|               |          |
|---------------|----------|
| eCl@ss 10.0.1 | 27400629 |
| eCl@ss 4.0    | 24190200 |
| eCl@ss 4.1    | 24190200 |
| eCl@ss 5.0    | 27149100 |
| eCl@ss 5.1    | 27141100 |
| eCl@ss 6.0    | 27149100 |

## Equipment marking - EML-ESD (8X8)R - 0830564

### Classifications

#### eCl@ss

|            |          |
|------------|----------|
| eCl@ss 7.0 | 27149129 |
| eCl@ss 8.0 | 27149129 |
| eCl@ss 9.0 | 27400629 |

#### ETIM

|          |          |
|----------|----------|
| ETIM 3.0 | EC000761 |
| ETIM 4.0 | EC000761 |
| ETIM 5.0 | EC001288 |
| ETIM 6.0 | EC001288 |
| ETIM 7.0 | EC001288 |

#### UNSPSC

|               |          |
|---------------|----------|
| UNSPSC 6.01   | 30211811 |
| UNSPSC 7.0901 | 39121410 |
| UNSPSC 11     | 39121410 |
| UNSPSC 12.01  | 39121410 |
| UNSPSC 13.2   | 39131504 |
| UNSPSC 18.0   | 39131504 |
| UNSPSC 19.0   | 39131504 |
| UNSPSC 20.0   | 39131504 |
| UNSPSC 21.0   | 39131504 |

### Approvals

#### Approvals

Approvals

UL Recognized

Ex Approvals

#### Approval details

UL Recognized



<http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm> FILE MH 48542

Phoenix Contact 2020 © - all rights reserved  
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG  
Flachsmarktstr. 8  
32825 Blomberg  
Germany  
Tel. +49 5235 300  
Fax +49 5235 3 41200  
<http://www.phoenixcontact.com>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[0830564](#)