

## Cable marker - WMTB-AL (D30) - 0830804

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Cable marker, Aluminum label, aluminum color, unlabeled, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, BLUEMARK CLED, mounting type: Assembly with cable binders, cable diameter: > 2.9 mm, lettering field size: d 30 mm



### Your advantages

- ✓ Aluminum cable marking for assembly with cable binders
- ✓ High-quality appearance
- ✓ Suitable for large-surface marking of conductors and cables > 2.9 mm in diameter

RoHS

### Key Commercial Data

|                        |                                                                                                         |
|------------------------|---------------------------------------------------------------------------------------------------------|
| Packing unit           | 90 pc                                                                                                   |
| Minimum order quantity | 90 pc                                                                                                   |
| GTIN                   | <br>4 046356 780780 |
| GTIN                   | 4046356780780                                                                                           |

### Technical data

#### Dimensions

|                        |         |
|------------------------|---------|
| Length (b)             | 30 mm   |
| Width (a)              | 30 mm   |
| Material thickness (g) | 0.80 mm |

#### Ambient conditions

|                                |             |
|--------------------------------|-------------|
| Recommended storage conditions | 5°C to 25°C |
|--------------------------------|-------------|

#### General

|                 |                                          |
|-----------------|------------------------------------------|
| Color           | aluminum color                           |
| Type            | Roll                                     |
| Components      | free from silicone, halogen, and cadmium |
| Material        | Aluminum                                 |
| Wipe resistance | DIN EN 61010-1 (VDE 0411-1)              |

## Cable marker - WMTB-AL (D30) - 0830804

### Technical data

#### General

|                                                                     |                                     |
|---------------------------------------------------------------------|-------------------------------------|
| Printability                                                        | UV LED technology                   |
| Device                                                              | 5147999 BLUEMARK CLED               |
|                                                                     | 5146662 BLUEMARK CLED-FLUID-CARTR.  |
| Test for substances that would hinder coating with paint or varnish | VW PV 3.10.7:2005-02                |
| Result                                                              | Test passed                         |
| Test specification weathering-resistance                            | Following ISO 4892-2:2013-03        |
| Test duration                                                       | 96 h                                |
| Result of weather resistance test                                   | Test passed                         |
| Salt spray test specification                                       | DIN EN 60068-2-11:2000-02           |
| Test duration                                                       | 96 h                                |
| Salt spray testing result                                           | Test passed                         |
| Alternating condensation climate with SO2 test specification        | following DIN 50018:2013-05         |
| Climate level                                                       | AHT 1.0 S                           |
| Cycles                                                              | 2                                   |
| Condensation test result                                            | Test passed                         |
| Wipe resistance of test specification inscriptions                  | DIN EN 61010-1 (VDE 0411-1):2011-07 |
| Result of wipe resistance test                                      | Test passed                         |
| Marking mounting type                                               | Assembly with cable binders         |
| Min. cross section                                                  | 4 mm <sup>2</sup>                   |

#### Standards and Regulations

|                 |                             |
|-----------------|-----------------------------|
| Wipe resistance | DIN EN 61010-1 (VDE 0411-1) |
|-----------------|-----------------------------|

### Classifications

#### eCl@ss

|               |          |
|---------------|----------|
| eCl@ss 10.0.1 | 27400401 |
| eCl@ss 4.0    | 27061700 |
| eCl@ss 4.1    | 27061700 |
| eCl@ss 5.0    | 27149100 |
| eCl@ss 5.1    | 27400400 |
| eCl@ss 6.0    | 27149100 |
| eCl@ss 7.0    | 27149129 |
| eCl@ss 8.0    | 27400401 |
| eCl@ss 9.0    | 27400401 |

#### ETIM

|          |          |
|----------|----------|
| ETIM 3.0 | EC000761 |
| ETIM 4.0 | EC001530 |
| ETIM 5.0 | EC001288 |
| ETIM 6.0 | EC001530 |

## Cable marker - WMTB-AL (D30) - 0830804

### Classifications

#### ETIM

|          |          |
|----------|----------|
| ETIM 7.0 | EC001530 |
|----------|----------|

#### UNSPSC

|               |          |
|---------------|----------|
| UNSPSC 6.01   | 30211811 |
| UNSPSC 7.0901 | 39121410 |
| UNSPSC 11     | 39121410 |
| UNSPSC 12.01  | 39121410 |
| UNSPSC 13.2   | 39131504 |
| UNSPSC 18.0   | 39131504 |
| UNSPSC 19.0   | 39131504 |
| UNSPSC 20.0   | 39131504 |
| UNSPSC 21.0   | 39131504 |

### Accessories

#### Accessories

#### Magazine

Magazine - BLUEMARK MAG WM-M (D30) - 0802747



Magazine, width: 76 mm, color: white

---

Phoenix Contact 2020 © - all rights reserved  
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG  
Flachsmarktstr. 8  
32825 Blomberg  
Germany  
Tel. +49 5235 300  
Fax +49 5235 3 41200  
<http://www.phoenixcontact.com>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Phoenix Contact:

0830804