

## Printed-circuit board connector - FKC 2,5/ 3-ST-5,08CP2,3BDR13SO - 1711023

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

PCB connector, nominal current: 12 A, rated voltage (III/2): 320 V, number of positions: 3, pitch: 5.08 mm, connection method: Push-in spring connection, color: green, contact surface: Tin



The figure shows a 10-position version of the product

### Your advantages

- ✓ Time saving push-in connection, tools not required
- ✓ Intuitive use through colour coded actuation lever
- ✓ Quick and convenient testing using integrated test option
- ✓ Can be combined with the MSTB 2,5 range



### Key Commercial Data

|              |               |
|--------------|---------------|
| Packing unit | 50 pc         |
| GTIN         |               |
| GTIN         | 4055626200705 |

### Technical data

#### Dimensions

|             |          |
|-------------|----------|
| Width [ w ] | 10.15 mm |
| Pitch       | 5.08 mm  |
| Dimension a | 5.08 mm  |

#### General

|                             |                           |
|-----------------------------|---------------------------|
| Range of articles           | FKC 2,5/...-ST            |
| Number of positions         | 3                         |
| Connection method           | Push-in spring connection |
| Insulating material group   | I                         |
| Rated surge voltage (III/3) | 4 kV                      |

# Printed-circuit board connector - FKC 2,5/ 3-ST-5,08CP2,3BDR13SO - 1711023

## Technical data

### General

|                                        |                     |
|----------------------------------------|---------------------|
| Rated surge voltage (III/2)            | 4 kV                |
| Rated surge voltage (II/2)             | 4 kV                |
| Rated voltage (III/3)                  | 320 V               |
| Rated voltage (III/2)                  | 320 V               |
| Rated voltage (II/2)                   | 630 V               |
| Nominal current I <sub>N</sub>         | 12 A                |
| Nominal cross section                  | 2.5 mm <sup>2</sup> |
| Flammability rating according to UL 94 | V0                  |
| Internal cylindrical gage              | A2                  |
| Stripping length                       | 10 mm               |

### Standards and Regulations

|                                        |    |
|----------------------------------------|----|
| Flammability rating according to UL 94 | V0 |
|----------------------------------------|----|

### Environmental Product Compliance

|            |                                                         |
|------------|---------------------------------------------------------|
| China RoHS | Environmentally friendly use period: unlimited = EFUP-e |
|            | No hazardous substances above threshold values          |

## Approvals

### Approvals

#### Approvals

cULus Recognized

#### Ex Approvals

### Approval details

|                                                                                                                                                                                                                                                                            |       |       |
|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------|-------|
| cULus Recognized  <a href="http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm">http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm</a> E60425-19931011 |       |       |
|                                                                                                                                                                                                                                                                            | D     | B     |
| Nominal voltage U <sub>N</sub>                                                                                                                                                                                                                                             | 300 V | 300 V |
| Nominal current I <sub>N</sub>                                                                                                                                                                                                                                             | 10 A  | 10 A  |
| mm <sup>2</sup> /AWG/kcmil                                                                                                                                                                                                                                                 | 26-12 | 26-12 |

Phoenix Contact 2018 © - all rights reserved  
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG  
Flachsmarktstr. 8  
32825 Blomberg  
Germany  
Tel. +49 5235 300  
Fax +49 5235 3 41200  
<http://www.phoenixcontact.com>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[1711023](#)