

## Mandatory sign - US-PML-M100 (D50) - 1014176

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Mandatory sign, Card, blue/white, unlabeled, can be labeled with: THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD: Blank, mounting type: adhesive, diameter: 50 mm, lettering field size: d: 50 mm, Number of individual labels: 4

### Your advantages

- ✓ UniSheet - stick-on mandatory signs, color preprinted, without symbol
- ✓ Suitable for indoor and outdoor use
- ✓ The mandatory signs conform to the ISO 7010 international standard
- ✓ Highly flexible, plasticized PVC labels which are ideal for uneven surfaces



### Key Commercial Data

|                        |                                                                                                         |
|------------------------|---------------------------------------------------------------------------------------------------------|
| Packing unit           | 10 pc                                                                                                   |
| Minimum order quantity | 10 pc                                                                                                   |
| GTIN                   | <br>4 046356 786447 |
| GTIN                   | 4046356786447                                                                                           |

### Technical data

#### Dimensions

|            |          |
|------------|----------|
| Width (a)  | 0 mm     |
| Height (c) | 0 mm     |
| Diameter   | 50.00 mm |

#### Ambient conditions

|                                 |                                                                                                         |
|---------------------------------|---------------------------------------------------------------------------------------------------------|
| Ambient temperature (operation) | -40 °C ... 90 °C                                                                                        |
| Ambient temperature (assembly)  | > 8 °C                                                                                                  |
| Recommended storage conditions  | 23 °C/50 % relative humidity. Storage in a dry and dark place in the original packaging is recommended. |

#### General

|       |            |
|-------|------------|
| Color | blue/white |
| Type  | Round      |

# Mandatory sign - US-PML-M100 (D50) - 1014176

## Technical data

### General

|                                                              |                                     |
|--------------------------------------------------------------|-------------------------------------|
| Components                                                   | Silicone-free                       |
| Material                                                     | PVC                                 |
| Wipe resistance                                              | DIN EN 61010-1 (VDE 0411-1)         |
| Printing                                                     | Blank                               |
| Number of individual labels                                  | 4                                   |
| Adhesive                                                     | Acrylic                             |
| Printability                                                 | Thermal transfer                    |
| Device                                                       | 5148888 THERMOMARK PRIME            |
| Ink ribbon                                                   | 0803376 TMP-RIBBON 110 WH 100       |
| Test specification weathering-resistance                     | Following ISO 4892-2:2013-03        |
| Test duration                                                | 96 h                                |
| Result of weather resistance test                            | Test passed                         |
| Salt spray test specification                                | DIN EN 60068-2-11:2000-02           |
| Procedure                                                    | A                                   |
| Test duration                                                | 96 h                                |
| Salt spray testing result                                    | Test passed                         |
| Alternating condensation climate with SO2 test specification | following DIN 50018:2013-05         |
| Climate level                                                | AHT 1.0 S                           |
| Cycles                                                       | 2                                   |
| Condensation test result                                     | Test passed                         |
| Wipe resistance of test specification inscriptions           | DIN EN 61010-1 (VDE 0411-1):2011-07 |
| Result of wipe resistance test                               | Test passed                         |
| Foil strength                                                | 50 µm                               |
| Marking mounting type                                        | adhesive                            |

### Standards and Regulations

|                 |                             |
|-----------------|-----------------------------|
| Wipe resistance | DIN EN 61010-1 (VDE 0411-1) |
|-----------------|-----------------------------|

## Classifications

### eCl@ss

|               |          |
|---------------|----------|
| eCl@ss 10.0.1 | 40200201 |
| eCl@ss 4.0    | 40200100 |
| eCl@ss 4.1    | 40200100 |
| eCl@ss 5.0    | 40200100 |
| eCl@ss 5.1    | 27371300 |
| eCl@ss 6.0    | 40200100 |
| eCl@ss 7.0    | 40200103 |
| eCl@ss 8.0    | 40200201 |
| eCl@ss 9.0    | 40200201 |

## Mandatory sign - US-PML-M100 (D50) - 1014176

### Classifications

#### ETIM

|          |          |
|----------|----------|
| ETIM 3.0 | EC000712 |
| ETIM 4.0 | EC002498 |
| ETIM 5.0 | EC001777 |
| ETIM 6.0 | EC001777 |
| ETIM 7.0 | EC001777 |

#### UNSPSC

|               |          |
|---------------|----------|
| UNSPSC 6.01   | 43172501 |
| UNSPSC 7.0901 | 43212107 |
| UNSPSC 11     | 43172501 |
| UNSPSC 12.01  | 43212107 |
| UNSPSC 13.2   | 55121718 |
| UNSPSC 18.0   | 55121718 |
| UNSPSC 19.0   | 55121718 |
| UNSPSC 20.0   | 55121718 |
| UNSPSC 21.0   | 55121718 |

### Accessories

#### Accessories

##### Ink ribbon

Ink ribbon - TM-RIBBON 110 WH 100 - 0804661



Ink ribbon, For THERMOMARK roll printers and THERMOMARK CARD for printing the material off the roll product groups: EML..., EMLP ..., EMLF..., PML-M..., PML-T... and US material product groups: US-EML(S)P..., US-EMLP-HA..., US-EM(S)P..., US-WMT..., US-WMTB ..., US-PML-M..., US-EMLF..., width: 110 mm, color: white

Ink ribbon cartridge - TMP-RIBBON 110 WH 100 - 0803376



Ink ribbon cartridge, for THERMOMARK PRIME for printing product groups US(2)-TM(F)..., US-TM(F)L..., US-WMTB..., US-EML..., US-EML(S)P..., US-EMLP-HA..., US-EM(S)P..., US-EML-RS..., width: 110 mm, color: white

### Magazine

## Mandatory sign - US-PML-M100 (D50) - 1014176

### Accessories

Magazine - TMP-US-MAG1 - 0803341



Magazine, For THERMOMARK CARD and THERMOMARK PRIME, for accommodating US cards

---

Phoenix Contact 2020 © - all rights reserved  
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG  
Flachsmarktstr. 8  
32825 Blomberg  
Germany  
Tel. +49 5235 300  
Fax +49 5235 3 41200  
<http://www.phoenixcontact.com>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[1014176](#)