

DIN rail, unperforated - NS 35/15 CU UNPERF 2000MM - 1201895

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



DIN rail, unperforated, Standard profile, width: 35 mm, height: 15 mm, similar to EN 60715, material: Copper, uncoated, length: 2000 mm, color: copper-colored

RoHS

Key Commercial Data

Packing unit	5 pc
GTIN	 4 017918 017583
GTIN	4017918017583

Technical data

Dimensions

Height	15 mm
Length	2000 mm
Width	35 mm
Hole width	0.00 mm
Hole height	0.00 mm
Drill hole spacing	0.00 mm

General

Material	Copper
Coating	uncoated
Color	copper-colored
Max. permissible thermal nominal current for PEN function	232.00 A



Standards and Regulations

Test standard	similar to EN 60715
Connection in acc. with standard	IEC / EN

Drawings

DIN rail, unperforated - NS 35/15 CU UNPERF 2000MM - 1201895

Dimensional drawing



Classifications

eCl@ss

eCl@ss 10.0.1	27400602
eCl@ss 4.0	27110800
eCl@ss 4.1	27110800
eCl@ss 5.0	27141100
eCl@ss 5.1	27141100
eCl@ss 6.0	27400600
eCl@ss 7.0	27400602
eCl@ss 8.0	27400602
eCl@ss 9.0	27400602

DIN rail, unperforated - NS 35/15 CU UNPERF 2000MM - 1201895

Classifications

ETIM

ETIM 2.0	EC001285
ETIM 3.0	EC001285
ETIM 4.0	EC000212
ETIM 5.0	EC000212
ETIM 6.0	EC001285
ETIM 7.0	EC001285

UNSPSC

UNSPSC 6.01	30212109
UNSPSC 7.0901	39121708
UNSPSC 11	39121708
UNSPSC 12.01	39121708
UNSPSC 13.2	39121708
UNSPSC 18.0	39121708
UNSPSC 19.0	39121708
UNSPSC 20.0	39121708
UNSPSC 21.0	39121708

Phoenix Contact 2020 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[1201895](#)