

FO patch cable - FOC-ST:A-SJ:A-GZ02/2 - 1400711

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Assembled FO cable, zip cord cable, multi-mode fiberglass 50/125 µm, OM3, plug: B-FOC (ST)/SC-RJ, degree of protection: IP20, for installation in cable ducts or control cabinets, length: 2 m

Your advantages

- ✓ Multi-mode patch cable for indoor installation
- ✓ Ideal for use in distributor systems and for connecting termination devices
- ✓ All components satisfy UL 94, V0
- ✓ 2.8 mm single elements made from halogen-free and flame-retardant material
- ✓ Interferometer tests at every stage of the certification process
- ✓ Excellent mechanical and optical properties
- ✓ Satisfies optical and mechanical industry standards
- ✓ Connector with UPC polishing for optimum attenuation values
- ✓ Low-bend fiber
- ✓ Insertion loss ≤ 0.5 dB
- ✓ Return loss ≥ 35 dB
- ✓ Comprehensively tested according to IEC 61753-122-2 and IEC 61753-1 Cat. C
- ✓ Temperature fluctuation test according to IEC 61300-2-1
- ✓ Vibration test according to IEC 61300-2-1
- ✓ Tensile strength of the cable connection according to IEC 61300-2-5



Key Commercial Data

Packing unit	1 pc
GTIN	 4 046356 735087
GTIN	4046356735087

Technical data

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
China RoHS	Environmentally Friendly Use Period = 50 years

FO patch cable - FOC-ST:A-SJ:A-GZ02/2 - 1400711

Technical data

Environmental Product Compliance

	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"
--	---

Classifications

eCl@ss

eCl@ss 10.0.1	27061003
eCl@ss 4.0	27260700
eCl@ss 4.1	27260700
eCl@ss 5.0	27260700
eCl@ss 5.1	27260700
eCl@ss 6.0	27260700
eCl@ss 7.0	27440309
eCl@ss 8.0	27061003
eCl@ss 9.0	27061003

ETIM

ETIM 3.0	EC001121
ETIM 4.0	EC000034
ETIM 5.0	EC001263
ETIM 6.0	EC001263
ETIM 7.0	EC001263

UNSPSC

UNSPSC 6.01	31261501
UNSPSC 7.0901	31261501
UNSPSC 11	31261501
UNSPSC 12.01	31261501
UNSPSC 13.2	26121607
UNSPSC 18.0	26121607
UNSPSC 19.0	26121607
UNSPSC 20.0	26121607
UNSPSC 21.0	26121607

Approvals

Approvals

Approvals

UL Listed / EAC

FO patch cable - FOC-ST:A-SJ:A-GZ02/2 - 1400711

Approvals

Ex Approvals

Approval details

UL Listed



<http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm> E308814-20070105

EAC



B.01687

Phoenix Contact 2020 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[1400711](#)