

## Electronic housing - UEGM 40/2-FS/FS - 2792099

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Electronic housing, 40 mm wide, fully equipped with 12 slip-on connections per side for two printed circuit boards


The figure shows version UEGM 40/1-FS/FS

### Your advantages

- ✓ Cost-effective series production, since the base element and the assembled PCB are soldered by machine
- ✓ Efficient assembly thanks to overlapping housing parts
- ✓ Can be snapped onto standard NS 35/7,5 and NS 35/15 DIN rails
- ✓ Complex electronic circuits can be integrated, with up to 24 connections on two levels

RoHS

### Key Commercial Data

Packing unit	10 pc
GTIN	 4 017918 072568
GTIN	4017918072568

### Technical data

#### General

Housing type	Complete housing
Housing material	Polyamide (PA 6.6)
Color (RAL)	green

#### Ambient conditions

Ambient temperature (operation)	-40 °C ... 105 °C
---------------------------------	-------------------

#### Dimensions

Length	101 mm
Height	85.5 mm
Width	40 mm
Depth	101 mm

## Electronic housing - UEGM 40/2-FS/FS - 2792099

### Technical data

#### Technical data

Power dissipation without gap	5.2 W
Power dissipation with 20 mm gap	11.2 W
Number of positions	24

#### Connection data

Conductor cross section solid min.	0.2 mm <sup>2</sup>
Conductor cross section solid max.	4 mm <sup>2</sup>
Conductor cross section flexible min.	0.2 mm <sup>2</sup>
Conductor cross section flexible max.	2.5 mm <sup>2</sup>
Conductor cross section AWG min.	24
Conductor cross section AWG max.	12

#### Standards and Regulations


Flammability rating according to UL 94	V2
--	----

#### Environmental Product Compliance


China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

### Drawings

Explosion drawing




Dimensional drawing




## Electronic housing - UEGM 40/2-FS/FS - 2792099

Dimensional drawing



Schematic diagram



### Approvals

#### Approvals

Approvals

UL Recognized / EAC

Ex Approvals

#### Approval details

UL Recognized



<http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm>

FILE E 240868

EAC



B.01742

Phoenix Contact 2018 © - all rights reserved  
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG  
Flachsmarktstr. 8  
32825 Blomberg  
Germany  
Tel. +49 5235 300  
Fax +49 5235 3 41200  
<http://www.phoenixcontact.com>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Phoenix Contact:

2792099