

Electronic housing - ME MAX 45 F G 3-3 KMGY VPE1 - 2201330

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Complete housing, length: 85 mm, without vents, Cross connection: DIN rail bus connector, color: light gray, width: 45 mm, height: 92 mm, number of positions cross connector: 5

RoHS

Key Commercial Data

Packing unit	1 pc
GTIN	 4 046356 767071
GTIN	4046356767071

Technical data

General

Housing type	Complete housing
Housing material	Polyamide
Color (RAL)	light gray (7035)

Ambient conditions

Ambient temperature (storage/transport)	-40 °C ... 70 °C
Ambient temperature (assembly)	-5 °C ... 100 °C
Ambient temperature (operation)	-40 °C ... 105 °C (depending on power dissipation)

Dimensions

Length	85 mm
Height	92 mm
Width	45 mm
Depth	85 mm

Technical data

Connection in acc. with standard	CUL
Indicator1	CUL1
Power dissipation without gap	5.5 W

Electronic housing - ME MAX 45 F G 3-3 KMGY VPE1 - 2201330

Technical data

Technical data

Power dissipation with 20 mm gap	9.6 W
Number of positions	48

Standards and Regulations

Connection in acc. with standard	CUL
Flammability rating according to UL 94	V0

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Approvals

Approvals

Approvals

UL Recognized

Ex Approvals

Approval details

UL Recognized		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	FILE E 240868
---------------	---	---	---------------

Phoenix Contact 2018 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[2201330](#)