

## Shock protection - EMLPR (26,5X17,5) - 0800360

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Shock protection, Sheet, transparent, unlabeled, mounting type: adhesive, lettering field size: 26.5 x 17.5 mm, Number of individual labels: 42

### Your advantages

- ✓ High level of mechanical and chemical stability
- ✓ Suitable for permanent outdoor use
- ✓ Stuck or snapped onto labeled CARRIER ... to protect the labeling
- ✓ Extremely thick, yet flexible and transparent shock protection

RoHS

### Key Commercial Data

|                        |                                                                                                         |
|------------------------|---------------------------------------------------------------------------------------------------------|
| Packing unit           | 10 pc                                                                                                   |
| Minimum order quantity | 10 pc                                                                                                   |
| GTIN                   | <br>4 046356 612500 |
| GTIN                   | 4046356612500                                                                                           |

### Technical data

#### Dimensions

|            |         |
|------------|---------|
| Length (b) | 17.5 mm |
| Width (a)  | 26.5 mm |

#### Ambient conditions

|                                 |                                    |
|---------------------------------|------------------------------------|
| Ambient temperature (operation) | -40 °C ... 90 °C                   |
| Recommended storage conditions  | 18-26 °C / 60 % relative humidity. |

#### General

|                             |              |
|-----------------------------|--------------|
| Color                       | transparent  |
| Components                  | halogen-free |
| Material                    | PUR          |
| Number of individual labels | 42           |

# Shock protection - EMLPR (26,5X17,5) - 0800360

## Technical data

### General

|                                                                     |                              |
|---------------------------------------------------------------------|------------------------------|
| Number of individual labels per row                                 | 3                            |
| Adhesive                                                            | Acrylic                      |
| Test for substances that would hinder coating with paint or varnish | VW PV 3.10.7:2005-02         |
| Result                                                              | Test passed                  |
| Test specification weathering-resistance                            | Following ISO 4892-2:2013-03 |
| Test duration                                                       | 4000 h                       |
| Result of weather resistance test                                   | Test passed                  |
| Alternating condensation climate with SO2 test specification        | following DIN 50018:2013-05  |
| Climate level                                                       | AHT 1.0 S                    |
| Cycles                                                              | 2                            |
| Condensation test result                                            | Test passed                  |
| Foil strength                                                       | 210 µm                       |
| Marking mounting type                                               | adhesive                     |

### Environmental Product Compliance

|            |                                                                                                     |
|------------|-----------------------------------------------------------------------------------------------------|
| REACH SVHC | 2-(2H-benzotriazol-2-yl)-4,6-ditertpentylphenol (UV-328) 25973-55-1                                 |
| China RoHS | For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration" |

## Classifications

### eCl@ss

|               |          |
|---------------|----------|
| eCl@ss 10.0.1 | 27400629 |
| eCl@ss 4.0    | 24190200 |
| eCl@ss 4.1    | 24190200 |
| eCl@ss 5.0    | 27149100 |
| eCl@ss 5.1    | 27141100 |
| eCl@ss 6.0    | 27149100 |
| eCl@ss 7.0    | 27149129 |
| eCl@ss 8.0    | 27149129 |
| eCl@ss 9.0    | 27400629 |

### ETIM

|          |          |
|----------|----------|
| ETIM 3.0 | EC000761 |
| ETIM 4.0 | EC002848 |
| ETIM 5.0 | EC001288 |
| ETIM 6.0 | EC001288 |
| ETIM 7.0 | EC001288 |

### UNSPSC

|               |          |
|---------------|----------|
| UNSPSC 6.01   | 30211811 |
| UNSPSC 7.0901 | 39121410 |

## Shock protection - EMLPR (26,5X17,5) - 0800360

### Classifications

#### UNSPSC

|              |          |
|--------------|----------|
| UNSPSC 11    | 39121410 |
| UNSPSC 12.01 | 39121410 |
| UNSPSC 13.2  | 39131504 |
| UNSPSC 18.0  | 39131504 |
| UNSPSC 19.0  | 39131504 |
| UNSPSC 20.0  | 39131504 |
| UNSPSC 21.0  | 39131504 |

Phoenix Contact 2020 © - all rights reserved  
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG  
Flachsmarktstr. 8  
32825 Blomberg  
Germany  
Tel. +49 5235 300  
Fax +49 5235 3 41200  
<http://www.phoenixcontact.com>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[0800360](#)