

Shrink sleeve - MM-WMS 6,4 (EX10)R C1 WH/BK - 0803925

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Shrink sleeve, Roll, white, unlabeled, can be labeled with: THERMOFOX, THERMOMARK GO, THERMOMARK GO.K, mounting type: slide-on, cable diameter range: 2.1 ... 6.4 mm, lettering field size: continuous x 10#mm

Your advantages

- ✓ Easy and efficient material cartridge system: Includes both the material to be printed and the corresponding ink ribbon
- ✓ No visible difference between retrospective marking and existing markings created with a desktop roll printer
- ✓ The conductor to be marked is simply threaded through the shrink sleeve, which is fixed to the conductor by heating the sleeve accordingly
- ✓ The shrink sleeve material provides additional electrical insulation and mechanical protection for conductors
- ✓ Thanks to the continuous format, a shrink sleeve marker of the appropriate length can be created flexibly for the relevant application
- ✓ The material is cUL certified
- ✓ High-quality and solvent-resistant marking solution for industrial applications that is created by means of thermal transfer printing



Key Commercial Data

Packing unit	1 pc
GTIN	 4 055626 212050
GTIN	4055626212050

Technical data

Dimensions

Length (b)	1.8 m
Width (a)	10 mm
Cable diameter	2.1 mm ... 6.4 mm

Ambient conditions

Ambient temperature (operation)	-55 °C ... 135 °C
---------------------------------	-------------------

General

Color	white
Base element material	polyolefine
Type	Shrink sleeve

Shrink sleeve - MM-WMS 6,4 (EX10)R C1 WH/BK - 0803925

Technical data

General

Components	free from silicone, halogen, and cadmium
Material	Polyolefine
Shrink rate	3:1
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Printability	Thermal transfer
Device	0803984 THERMOFOX
	1090747 THERMOMARK GO
	1184146 THERMOMARK GO.K
Marking mounting type	slide-on

Standards and Regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Classifications

eCl@ss

eCl@ss 10.0.1	27400401
eCl@ss 4.0	24190200
eCl@ss 4.1	24190200
eCl@ss 5.0	27400100
eCl@ss 5.1	27400100
eCl@ss 6.0	27400100
eCl@ss 7.0	27400105
eCl@ss 8.0	27400105
eCl@ss 9.0	27400401

ETIM

ETIM 3.0	EC001530
ETIM 4.0	EC000217
ETIM 5.0	EC000217
ETIM 6.0	EC001530
ETIM 7.0	EC001530

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410

Shrink sleeve - MM-WMS 6,4 (EX10)R C1 WH/BK - 0803925

Classifications

UNSPSC

UNSPSC 13.2	39131504
UNSPSC 18.0	39131504
UNSPSC 19.0	39131504
UNSPSC 20.0	39131504
UNSPSC 21.0	39131504

Approvals

Approvals

Approvals

cULus Recognized

Ex Approvals

Approval details

cULus Recognized		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	E310982
------------------	---	---	---------

Phoenix Contact 2020 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Phoenix Contact:

0803925