

Label - EML (20X8)R - 0816786

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Label, Roll, white, unlabeled, can be labeled with: THERMOMARK ROLLMASTER 300/600, THERMOMARK X1.2, THERMOMARK ROLL X1, THERMOMARK ROLL 2.0, THERMOMARK ROLL, mounting type: adhesive, lettering field size: 20 mm x 8 mm, Number of individual labels: 2500

Your advantages

- ✓ The EML ... self-adhesive device markers are particularly well suited for marking various types of equipment in control, system, and control cabinet manufacturing.
- ✓ A wide range of marker sizes and colors are available for custom designs
- ✓ When combined with the right ink ribbon, the marking is highly resistant to solvents and mechanical influences. The marking is even suitable for use under harsh industrial conditions.
- ✓ The EML ... materials are UL-listed
- ✓ Labeling service: Phoenix Contact can custom-label all EM ... markers in accordance with your requirements

RoHS

Key Commercial Data

Packing unit	1 pc
GTIN	 4 046356 107525
GTIN	4046356107525

Technical data

Dimensions

Length (b)	8 mm
Width (a)	20 mm

Ambient conditions

Ambient temperature (operation)	-40 °C ... 150 °C
Ambient temperature (assembly)	> 5 °C
Recommended storage conditions	23 °C/50 % relative humidity. Storage in a dry and dark place in the original packaging is recommended.

General

Color	white
Components	free from silicone and halogen

Label - EML (20X8)R - 0816786

Technical data

General

Material	Polyester
RoHS compliant	Yes
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Number of individual labels	2500
Number of individual labels per row	4
Adhesive	Acrylic
Printability	Thermal transfer
Device	1085260 THERMOMARK ROLL 2.0
	0804501 THERMOMARK ROLLMASTER 300
	0804663 THERMOMARK ROLLMASTER 600
Ink ribbon	5145384 THERMOMARK-RIBBON 110
	0829544 THERMOMARK-RIBBON 110 BU
	0829542 THERMOMARK-RIBBON 110 GN
	0829543 THERMOMARK-RIBBON 110 RD
Test for substances that would hinder coating with paint or varnish	VW PV 3.10.7:2005-02
Result	Test passed
Test specification weathering-resistance	Following ISO 4892-2:2013-03
Test duration	96 h
Result of weather resistance test	Test passed
Salt spray test specification	DIN EN 60068-2-11:2000-02
Test duration	96 h
Salt spray testing result	Test passed
Wipe resistance of test specification inscriptions	DIN EN 61010-1 (VDE 0411-1):2011-07
Result of wipe resistance test	Test passed
Foil strength	50 µm
Adhesive strength	20 µm
Marking mounting type	adhesive
File number	UL-MH48542 / PC-010 (white foil)

Standards and Regulations

Connection in acc. with standard	UL
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)

Classifications

eCl@ss

eCl@ss 10.0.1	27400629
eCl@ss 4.0	24190200
eCl@ss 4.1	24190200
eCl@ss 5.0	27149100
eCl@ss 5.1	27141100

Label - EML (20X8)R - 0816786

Classifications

eCl@ss

eCl@ss 6.0	27149100
eCl@ss 7.0	27149129
eCl@ss 8.0	27149129
eCl@ss 9.0	27400629

ETIM

ETIM 2.0	EC000761
ETIM 3.0	EC000761
ETIM 4.0	EC000761
ETIM 5.0	EC001288
ETIM 6.0	EC001288
ETIM 7.0	EC001288

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39131504
UNSPSC 18.0	39131504
UNSPSC 19.0	39131504
UNSPSC 20.0	39131504
UNSPSC 21.0	39131504

Approvals

Approvals

Approvals

UL Recognized / CSA

Ex Approvals

Approval details

UL Recognized



<http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm>

FILE MH 48542

Label - EML (20X8)R - 0816786

Approvals

CSA



<http://www.csagroup.org/services-industries/product-listing/>

70191766

Accessories

Accessories

Ink ribbon

Ink ribbon - THERMOMARK-RIBBON 110 - 5145384



Ink ribbon, for roll printers for printing the product groups TML..., WML..., WML HF..., WML-FLAG..., EML..., EML-ESD..., EML-RM..., EML-HA..., EMLS..., EMLC..., EMLP... and PMM..., width: 110 mm, color: black

Phoenix Contact 2020 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[0816786](#)