

Plastic label with drill hole - EMLP 32 (38X14) - 0822291

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Plastic label with drill hole, Card, white, unlabeled, can be labeled with: P1 ENGRAVING UNIT, ENGRAVING UNIT, CMS-P1-PLOTTER, PLOTMARK, mounting type: adhesive, lettering field size: 38 x 14 mm, Number of individual labels: 6

Your advantages

- ✓ Can be engraved using the P1 ENGRAVING UNIT
- ✓ Can be labeled easily using the CMS-P1-PLOTTER
- ✓ Labeling service: Phoenix Contact can custom-label all EMLP ... markers according to your requirements
- ✓ High-quality appearance
- ✓ High level of resistance to chemical and mechanical influences
- ✓ For marking components, devices, and buttons

RoHS

Key Commercial Data

Packing unit	1 pc
GTIN	 4 046356 318334
GTIN	4046356318334

Technical data

Dimensions

Length (b)	50 mm
Width (a)	38 mm

Ambient conditions

Ambient temperature (operation)	-20 °C ... 80 °C
Recommended storage conditions	20°C/50% relative humidity. Storage in the original packaging is recommended.

General

Color	white
Components	free from silicone and halogen
Material	TRANSPLY-ABS

Plastic label with drill hole - EMLP 32 (38X14) - 0822291

Technical data

General

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Number of individual labels	6
Number of individual labels per row	2
Adhesive	Acrylic
Printability	Plotter
	Engraving
Device	5144615 CMS-P1-PLOTTER
	5145546 P1 ENGRAVING UNIT
Test for substances that would hinder coating with paint or varnish	VW PV 3.10.7:2005-02
Result	Test passed
Test specification weathering-resistance	Following ISO 4892-2:2013-03
Test duration	96 h
Result of weather resistance test	Test passed
Salt spray test specification	DIN EN 60068-2-11:2000-02
Test duration	96 h
Salt spray testing result	Test passed
Alternating condensation climate with SO2 test specification	DIN 50018:2013-05
Climate level	AHT 1.0 S
Cycles	2
Condensation test result	Test passed
Adhesive strength	50 µm
Marking mounting type	adhesive

Standards and Regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

Classifications

eCl@ss

eCl@ss 10.0.1	27400629
eCl@ss 4.0	24190200
eCl@ss 4.1	24190200
eCl@ss 5.0	27149100
eCl@ss 5.1	27141100
eCl@ss 6.0	27149100
eCl@ss 7.0	27149129
eCl@ss 8.0	27149129
eCl@ss 9.0	27400629

ETIM

ETIM 2.0	EC000761
----------	----------

Plastic label with drill hole - EMLP 32 (38X14) - 0822291

Classifications

ETIM

ETIM 3.0	EC000761
ETIM 4.0	EC000761
ETIM 5.0	EC001288
ETIM 6.0	EC001288
ETIM 7.0	EC001288

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39131504
UNSPSC 18.0	39131504
UNSPSC 19.0	39131504
UNSPSC 20.0	39131504
UNSPSC 21.0	39131504

Accessories

Accessories

Magazine

Magazine - CMS-P1-M/GPE ENGRAVING - 5145711



Magazine for CMS-P1-PLOTTER, to accommodate GPE materials, especially for the purpose of engraving

Phoenix Contact 2020 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Phoenix Contact:

0822291