

Cable marker - US-WMTB (24X5) VT - 0829323

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Cable marker, Card, violet, unlabeled, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD, mounting type: thread on, cable diameter: > 13 mm, lettering field size: 24 x 5 mm, Number of individual labels: 35

Your advantages

- ✓ The US-WMTB... UniSheet labeling range includes markers that can be secured using standard cable binders
- ✓ The markers, which are supplied in uniform sheets, can be labeled quickly, easily, and cost-effectively using the THERMOMARK CARD
- ✓ The perforated marking strips are easy to separate and can be easily fitted
- ✓ The sheets provide space for including function texts



Key Commercial Data

Packing unit	10 pc
Minimum order quantity	10 pc
GTIN	 4 046356 613309
GTIN	4046356613309

Technical data

Dimensions

Length (b)	24 mm
Width (a)	14 mm

Ambient conditions

Ambient temperature (operation)	-30 °C ... 80 °C
Recommended storage conditions	23 °C/50 % relative humidity. Storage in a dry and dark place in the original packaging is recommended.

General

Color	violet
Type	Card form
Components	Silicone-free
Flammability rating according to UL 94	V0

Cable marker - US-WMTB (24X5) VT - 0829323

Technical data

General

Material	PVC
	PVC
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Number of individual labels	35
Number of individual labels per row	7
Test for substances that would hinder coating with paint or varnish	VW PV 3.10.7:2005-02
Result	Test passed
Test specification weathering-resistance	Following ISO 4892-2:2013-03
Test duration	96 h
Result of weather resistance test	Test passed
Salt spray test specification	DIN EN 60068-2-11:2000-02
Test duration	96 h
Salt spray testing result	Test passed
Wipe resistance of test specification inscriptions	DIN EN 61010-1 (VDE 0411-1):2011-07
Result of wipe resistance test	Test passed
Marking mounting type	thread on

Standards and Regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Flammability rating according to UL 94	V0

Classifications

eCl@ss

eCl@ss 10.0.1	27400401
eCl@ss 4.0	27061700
eCl@ss 4.1	27061700
eCl@ss 5.0	27400400
eCl@ss 5.1	27400400
eCl@ss 6.0	27400400
eCl@ss 7.0	27400401
eCl@ss 8.0	27400401
eCl@ss 9.0	27400401

ETIM

ETIM 2.0	EC000761
ETIM 3.0	EC000761
ETIM 4.0	EC001530
ETIM 5.0	EC001530
ETIM 6.0	EC001530
ETIM 7.0	EC001530

Cable marker - US-WMTB (24X5) VT - 0829323

Classifications

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39131504
UNSPSC 18.0	39131504
UNSPSC 19.0	39131504
UNSPSC 20.0	39131504
UNSPSC 21.0	39131504

Accessories

Accessories

Ink ribbon

Ink ribbon - TM-RIBBON 110 WH 100 - 0804661



Ink ribbon, For THERMOMARK roll printers and THERMOMARK CARD for printing the material off the roll product groups: EML..., EMLP ..., EMLF..., PML-M..., PML-T... and US material product groups: US-EML(S)P..., US-EMLP-HA..., US-EM(S)P..., US-WMT..., US-WMTB ..., US-PML-M..., US-EMLF..., width: 110 mm, color: white

Magazine

Magazine - TMP-US-MAG1 - 0803341



Magazine, For THERMOMARK CARD and THERMOMARK PRIME, for accommodating US cards

Phoenix Contact 2020 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Phoenix Contact:

0829323