

## Conductor connectors - QPD C 2PE1,5 1X8-13 BK - 1414701

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Conductor connectors, QUICKON connection, number of positions: 2+PE, 0.5 mm<sup>2</sup> ... 1.5 mm<sup>2</sup>, 690 V, 17.5 A, black, with one QUICKON nut, cable diameter range: 10 mm ... 13 mm

### Your advantages

- ✓ Innovative and time saving - QUICKON fast connection for time saving of up to 80 % for on-site connection
- ✓ Convenient: quick and easy assembly without special tools
- ✓ Robust throughout: housing with IP68/IP69K and IK07 protection for a wide range of applications
- ✓ Safer connection thanks to polarization against mismatching and touch-proof protection according to DIN EN 0105
- ✓ Easy and safe - with the cable connector, you can repair or extend cables quickly, in combination with the connector as well as the coupling connection

RoHS

### Key Commercial Data

|              |                                                                                                         |
|--------------|---------------------------------------------------------------------------------------------------------|
| Packing unit | 1 pc                                                                                                    |
| GTIN         | <br>4 055626 031637 |
| GTIN         | 4055626031637                                                                                           |

### Technical data

#### General

|                                       |                     |
|---------------------------------------|---------------------|
| Type                                  | QPD 3x1,5           |
| Color                                 | black               |
| Locking type                          | Screw locking       |
| Connection method                     | QUICKON connection  |
|                                       | IDC connection      |
| Number of positions                   | 3                   |
| Note number of positions              | 2+PE                |
| Tightening torque, union nut          | 8 Nm                |
| Tightening torque, counter nut        | 5 Nm                |
| Conductor cross section flexible min. | 0.5 mm <sup>2</sup> |
| Conductor cross section flexible max. | 1.5 mm <sup>2</sup> |

# Conductor connectors - QPD C 2PE1,5 1X8-13 BK - 1414701

## Technical data

### General

|                                    |                     |
|------------------------------------|---------------------|
| Conductor cross section solid min. | 0.5 mm <sup>2</sup> |
| Conductor cross section solid max. | 1.5 mm <sup>2</sup> |
| Conductor cross section AWG min.   | 20                  |
| Conductor cross section AWG max.   | 16                  |

### Cabel

|                                                                             |                                    |
|-----------------------------------------------------------------------------|------------------------------------|
| Structure of individual litz in acc. with VDE 0295 / smallest wire diameter | VDE 0295 class 1 to 6/min. 0.15 mm |
| Wire insulation material                                                    | PVC/PE/TPE/rubber                  |
| Wire diameter including insulation                                          | 1.6 mm ... 3 mm                    |
| External cable diameter                                                     | 10 mm ... 13 mm                    |
| Position marking                                                            | 1, 2, PE                           |

### Ambient conditions

|                                         |                   |
|-----------------------------------------|-------------------|
| Degree of protection                    | IP66              |
|                                         | IP68 (2 m / 24 h) |
|                                         | IP69K             |
| Ambient temperature (operation)         | -40 °C ... 100 °C |
| Ambient temperature (storage/transport) | -40 °C ... 100 °C |
| Temperature when conductor connected    | -5 °C ... 50 °C   |

### Electrical characteristics

|                                |          |
|--------------------------------|----------|
| Nominal current I <sub>N</sub> | 17.5 A   |
| Nominal voltage U <sub>N</sub> | 690 V AC |
|                                | 690 V DC |
| Rated current                  | 17.5 A   |
| Rated voltage (III/3)          | 690 V    |
| Rated voltage (III/2)          | 1000 V   |
| Rated voltage (II/2)           | 1000 V   |
| Rated surge voltage (III/3)    | 6 kV     |
| Rated surge voltage (III/2)    | 8 kV     |
| Rated surge voltage (II/2)     | 8 kV     |

### Mechanical characteristics

|                             |                                  |
|-----------------------------|----------------------------------|
| QUICKON connectability      | max. 10                          |
| Insertion/withdrawal cycles | 10 (QUICKON connections max. 10) |
| Category of shock impact    | IK07                             |

### Material data

|                                        |               |
|----------------------------------------|---------------|
| Contact material                       | Cu            |
| Contact surface material               | silver-plated |
| Contact carrier material               | PA            |
| Insulating material                    | PA            |
| Flammability rating according to UL 94 | V0            |

## Conductor connectors - QPD C 2PE1,5 1X8-13 BK - 1414701

### Technical data

#### Material data

|                      |     |
|----------------------|-----|
| Overvoltage category | III |
| Degree of pollution  | 3   |

#### Standards and Regulations


|                                        |      |
|----------------------------------------|------|
| Category of shock impact               | IK07 |
| Halogen-free                           | yes  |
| Flammability rating according to UL 94 | V0   |

#### Environmental Product Compliance

|            |                                                         |
|------------|---------------------------------------------------------|
| China RoHS | Environmentally friendly use period: unlimited = EFUP-e |
|            | No hazardous substances above threshold values          |

### Drawings

Dimensional drawing



Dimensional drawing

### Classifications

eCl@ss

|               |          |
|---------------|----------|
| eCl@ss 10.0.1 | 27440605 |
| eCl@ss 4.0    | 27140800 |
| eCl@ss 4.1    | 27140800 |
| eCl@ss 5.0    | 27143400 |
| eCl@ss 5.1    | 27143400 |
| eCl@ss 6.0    | 27143400 |
| eCl@ss 7.0    | 27440605 |
| eCl@ss 8.0    | 27440605 |

# Conductor connectors - QPD C 2PE1,5 1X8-13 BK - 1414701

## Classifications

### eCl@ss

|            |          |
|------------|----------|
| eCl@ss 9.0 | 27440605 |
|------------|----------|

### ETIM

|          |          |
|----------|----------|
| ETIM 5.0 | EC002560 |
| ETIM 6.0 | EC002560 |
| ETIM 7.0 | EC002560 |

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 13.2 | 39121402 |
| UNSPSC 18.0 | 39121402 |
| UNSPSC 19.0 | 39121402 |
| UNSPSC 20.0 | 39121402 |
| UNSPSC 21.0 | 39121402 |

## Approvals

### Approvals

#### Approvals

EAC / EAC / DNV GL / IECCEB Scheme / UL Listed / cUL Listed / VDE Zeichengenehmigung / cULus Listed

#### Ex Approvals

### Approval details

|     |                                                                                     |                          |
|-----|-------------------------------------------------------------------------------------|--------------------------|
| EAC |  | RU C-<br>DE.AI30.B.01102 |
|-----|-------------------------------------------------------------------------------------|--------------------------|

|     |                                                                                     |                          |
|-----|-------------------------------------------------------------------------------------|--------------------------|
| EAC |  | RU C-<br>DE.BL08.B.00511 |
|-----|-------------------------------------------------------------------------------------|--------------------------|

|        |                                                                                     |                                                                                   |            |
|--------|-------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------|------------|
| DNV GL |  | <a href="https://approvalfinder.dnvgl.com/">https://approvalfinder.dnvgl.com/</a> | TAE00003J5 |
|--------|-------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------|------------|

|               |                                                                                     |                                                           |           |
|---------------|-------------------------------------------------------------------------------------|-----------------------------------------------------------|-----------|
| IECCEB Scheme |  | <a href="http://www.iecee.org/">http://www.iecee.org/</a> | DE1-61559 |
|---------------|-------------------------------------------------------------------------------------|-----------------------------------------------------------|-----------|

## Conductor connectors - QPD C 2PE1,5 1X8-13 BK - 1414701

### Approvals

|                    |                                                                                   |                                                                                                                                                       |         |
|--------------------|-----------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------|---------|
| UL Listed          |  | <a href="http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm">http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm</a> | E468743 |
| Nominal voltage UN |                                                                                   | 600 V                                                                                                                                                 |         |
| Nominal current IN |                                                                                   | 8 A                                                                                                                                                   |         |
| mm²/AWG/kcmil      |                                                                                   | 16                                                                                                                                                    |         |

|                    |                                                                                   |                                                                                                                                                       |         |
|--------------------|-----------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------|---------|
| cUL Listed         |  | <a href="http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm">http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm</a> | E468743 |
| Nominal voltage UN |                                                                                   | 600 V                                                                                                                                                 |         |
| Nominal current IN |                                                                                   | 8 A                                                                                                                                                   |         |
| mm²/AWG/kcmil      |                                                                                   | 16                                                                                                                                                    |         |

|                        |                                                                                     |                                                                                                                                                                                                           |          |
|------------------------|-------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|----------|
| VDE Zeichengenehmigung |  | <a href="http://www2.vde.com/de/Institut/Online-Service/VDE-gepruefteProdukte/Seiten/Online-Suche.aspx">http://www2.vde.com/de/Institut/Online-Service/VDE-gepruefteProdukte/Seiten/Online-Suche.aspx</a> | 40029149 |
| Nominal voltage UN     |                                                                                     | 690 V                                                                                                                                                                                                     |          |
| Nominal current IN     |                                                                                     | 17.5 A                                                                                                                                                                                                    |          |
| mm²/AWG/kcmil          |                                                                                     | 0.5-1.5                                                                                                                                                                                                   |          |

|              |                                                                                     |  |  |
|--------------|-------------------------------------------------------------------------------------|--|--|
| cULus Listed |  |  |  |
|--------------|-------------------------------------------------------------------------------------|--|--|

### Accessories

#### Accessories

#### Coding element

Coding profile - CP-QPD 3/4X1,5 - 1414729



Coding profile red, for pushing into the QUICKON dome and connector, can be positioned in 90° steps.

#### Protective cap

## Conductor connectors - QPD C 2PE1,5 1X8-13 BK - 1414701

### Accessories

Protective cap - QPD QSK BK 3/4X1,5 FS - 1414722

Protective cap, plastic, for QUICKON connection, black, with retaining cord, IP68



---

Protective cap - QPD QSK 3/4X1,5 - 1414723



Protective cap plastic, for QPD-QUICKON connection 3(4) x 1.5 mm², IP50

---

### Sealing plugs

Closing cap - SEALING PLUG 10X16 RD - 1400284



Closing cap, material: PA, for threads pluggable, color: red

---

Phoenix Contact 2020 © - all rights reserved  
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG  
Flachsmarktstr. 8  
32825 Blomberg  
Germany  
Tel. +49 5235 300  
Fax +49 5235 3 41200  
<http://www.phoenixcontact.com>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Phoenix Contact:

1414701