

## H distributor - QPD H 2PE1,5 BK - 1414721

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



H distributor, QUICKON connection, number of positions: 2+PE, 0.5 mm<sup>2</sup> ... 1.5 mm<sup>2</sup>, 690 V, 17.5 A, black, without QUICKON nut

### Your advantages

- ✓ Innovative and time saving - QUICKON fast connection for time saving of up to 80 % for on-site connection
- ✓ Convenient: quick and easy assembly without special tools
- ✓ Robust throughout: housing with IP68/IP69K and IK07 protection for a wide range of applications
- ✓ Safer connection thanks to polarization against mismatching and touch-proof protection according to DIN EN 0105
- ✓ Flexible and compact - by connecting connections internally, H and T-distributors can be used to branch master cables or they can be used as star distributors

RoHS

### Key Commercial Data

|              |                                                                                                         |
|--------------|---------------------------------------------------------------------------------------------------------|
| Packing unit | 1 pc                                                                                                    |
| GTIN         | <br>4 055626 032221 |
| GTIN         | 4055626032221                                                                                           |

### Technical data

#### General

|                                       |                     |
|---------------------------------------|---------------------|
| Type                                  | H-distributor       |
| Color                                 | black               |
| Locking type                          | Screw locking       |
| Connection method                     | QUICKON connection  |
|                                       | IDC connection      |
| Number of positions                   | 3                   |
| Note number of positions              | 2+PE                |
| Wrench size, union nut                | 19 mm               |
| Tightening torque, union nut          | 8 Nm                |
| Number of connections                 | 3                   |
| Conductor cross section flexible min. | 0.5 mm <sup>2</sup> |

# H distributor - QPD H 2PE1,5 BK - 1414721

## Technical data

### General

|                                       |                     |
|---------------------------------------|---------------------|
| Conductor cross section flexible max. | 1.5 mm <sup>2</sup> |
| Conductor cross section solid min.    | 0.5 mm <sup>2</sup> |
| Conductor cross section solid max.    | 1.5 mm <sup>2</sup> |
| Conductor cross section AWG min.      | 20                  |
| Conductor cross section AWG max.      | 16                  |

### Cabel

|                                                                             |                                    |
|-----------------------------------------------------------------------------|------------------------------------|
| Structure of individual litz in acc. with VDE 0295 / smallest wire diameter | VDE 0295 class 1 to 6/min. 0.15 mm |
| Wire insulation material                                                    | PVC/PE/TPE/rubber                  |
| Wire diameter including insulation                                          | 1.6 mm ... 3 mm                    |
| Position marking                                                            | 1, 2, PE                           |

### Ambient conditions

|                                         |                                         |
|-----------------------------------------|-----------------------------------------|
| Degree of protection                    | IP66                                    |
|                                         | IP68 (2 m / 24 h)                       |
|                                         | IP69K (Distance from the nozzle 150 mm) |
| Ambient temperature (operation)         | -40 °C ... 100 °C                       |
| Ambient temperature (storage/transport) | -40 °C ... 100 °C                       |
| Temperature when conductor connected    | -5 °C ... 50 °C                         |

### Electrical characteristics

|                                |          |
|--------------------------------|----------|
| Nominal current I <sub>N</sub> | 17.5 A   |
| Nominal voltage U <sub>N</sub> | 690 V AC |
|                                | 690 V DC |
| Rated current                  | 17.5 A   |
| Rated voltage (III/3)          | 690 V    |
| Rated voltage (III/2)          | 1000 V   |
| Rated voltage (II/2)           | 1000 V   |
| Rated surge voltage (III/3)    | 6 kV     |
| Rated surge voltage (III/2)    | 8 kV     |
| Rated surge voltage (II/2)     | 8 kV     |

### Mechanical characteristics

|                             |                                  |
|-----------------------------|----------------------------------|
| QUICKON connectability      | max. 10                          |
| Insertion/withdrawal cycles | 10 (QUICKON connections max. 10) |
| Category of shock impact    | IK07 (-25 °C)                    |

### Material data

|                                        |               |
|----------------------------------------|---------------|
| Contact material                       | Cu            |
| Contact surface material               | silver-plated |
| Contact carrier material               | PA            |
| Insulating material                    | PA            |
| Flammability rating according to UL 94 | V0            |

## H distributor - QPD H 2PE1,5 BK - 1414721

### Technical data

#### Material data

|                      |     |
|----------------------|-----|
| Overvoltage category | III |
| Degree of pollution  | 3   |

#### Standards and Regulations


|                                        |               |
|----------------------------------------|---------------|
| Category of shock impact               | IK07 (-25 °C) |
| Flammability rating according to UL 94 | V0            |

#### Environmental Product Compliance

|            |                |
|------------|----------------|
| REACH SVHC | Lead 7439-92-1 |
|------------|----------------|


### Drawings

Circuit diagram




## H distributor - QPD H 2PE1,5 BK - 1414721

Diagram



Derating diagram

Dimensional drawing



Dimensional drawing

### Classifications

eCl@ss

|               |          |
|---------------|----------|
| eCl@ss 10.0.1 | 27440603 |
|---------------|----------|

## H distributor - QPD H 2PE1,5 BK - 1414721

### Classifications

#### eCl@ss

|            |          |
|------------|----------|
| eCl@ss 4.0 | 27140800 |
| eCl@ss 4.1 | 27140800 |
| eCl@ss 5.0 | 27143400 |
| eCl@ss 5.1 | 27143400 |
| eCl@ss 6.0 | 27143400 |
| eCl@ss 7.0 | 27440603 |
| eCl@ss 8.0 | 27440603 |
| eCl@ss 9.0 | 27440603 |

#### ETIM

|          |          |
|----------|----------|
| ETIM 5.0 | EC002567 |
| ETIM 6.0 | EC002567 |
| ETIM 7.0 | EC002567 |

#### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 13.2 | 31251501 |
| UNSPSC 18.0 | 39121410 |
| UNSPSC 19.0 | 39121410 |
| UNSPSC 20.0 | 39121410 |
| UNSPSC 21.0 | 39121410 |

### Approvals

#### Approvals

#### Approvals

EAC / EAC / DNV GL / IECCE CB Scheme / UL Listed / cUL Listed / VDE Zeichengenehmigung / cULus Listed

#### Ex Approvals

#### Approval details

|     |                                                                                     |                          |
|-----|-------------------------------------------------------------------------------------|--------------------------|
| EAC |  | RU C-<br>DE.AI30.B.01102 |
|-----|-------------------------------------------------------------------------------------|--------------------------|

|     |                                                                                     |                          |
|-----|-------------------------------------------------------------------------------------|--------------------------|
| EAC |  | RU C-<br>DE.BL08.B.00511 |
|-----|-------------------------------------------------------------------------------------|--------------------------|

## H distributor - QPD H 2PE1,5 BK - 1414721

### Approvals

|        |                                                                                   |                                                                                   |            |
|--------|-----------------------------------------------------------------------------------|-----------------------------------------------------------------------------------|------------|
| DNV GL |  | <a href="https://approvalfinder.dnvgl.com/">https://approvalfinder.dnvgl.com/</a> | TAE00003J5 |
|--------|-----------------------------------------------------------------------------------|-----------------------------------------------------------------------------------|------------|

|                 |                                                                                   |                                                           |           |
|-----------------|-----------------------------------------------------------------------------------|-----------------------------------------------------------|-----------|
| IECEE CB Scheme |  | <a href="http://www.iecee.org/">http://www.iecee.org/</a> | DE1-61559 |
|-----------------|-----------------------------------------------------------------------------------|-----------------------------------------------------------|-----------|

|                    |                                                                                   |                                                                                                                                                       |         |
|--------------------|-----------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------|---------|
| UL Listed          |  | <a href="http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm">http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm</a> | E468743 |
| Nominal voltage UN |                                                                                   | 600 V                                                                                                                                                 |         |
| Nominal current IN |                                                                                   | 8 A                                                                                                                                                   |         |
| mm²/AWG/kcmil      |                                                                                   | 16                                                                                                                                                    |         |

|                    |                                                                                     |                                                                                                                                                       |         |
|--------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------|---------|
| cUL Listed         |  | <a href="http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm">http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm</a> | E468743 |
| Nominal voltage UN |                                                                                     | 600 V                                                                                                                                                 |         |
| Nominal current IN |                                                                                     | 8 A                                                                                                                                                   |         |
| mm²/AWG/kcmil      |                                                                                     | 16                                                                                                                                                    |         |

|                        |                                                                                     |                                                                                                                                                                                                           |          |
|------------------------|-------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|----------|
| VDE Zeichengenehmigung |  | <a href="http://www2.vde.com/de/Institut/Online-Service/VDE-gepruefteProdukte/Seiten/Online-Suche.aspx">http://www2.vde.com/de/Institut/Online-Service/VDE-gepruefteProdukte/Seiten/Online-Suche.aspx</a> | 40029149 |
| Nominal voltage UN     |                                                                                     | 690 V                                                                                                                                                                                                     |          |
| Nominal current IN     |                                                                                     | 17.5 A                                                                                                                                                                                                    |          |
| mm²/AWG/kcmil          |                                                                                     | 0.5-1.5                                                                                                                                                                                                   |          |

|              |                                                                                     |  |  |
|--------------|-------------------------------------------------------------------------------------|--|--|
| cULus Listed |  |  |  |
|--------------|-------------------------------------------------------------------------------------|--|--|

### Accessories

Accessories

Coding element

## H distributor - QPD H 2PE1,5 BK - 1414721

### Accessories

Coding profile - CP-QPD 3/4X1,5 - 1414729



Coding profile red, for pushing into the QUICKON dome and connector, can be positioned in 90° steps.

---

### Device marking

Engraving material - GPE 13X 9 WH - 0806932



Engraving material, Sheet, white, unlabeled, can be labeled with: PLOTMARK, ENGRAVING UNIT, CMS-P1-PLOTTER, P1 ENGRAVING UNIT, mounting type: adhesive, lettering field size: 13 x 9 mm, Number of individual labels: 120

---

Plastic label - EMLP (13X9)R - 0819453



Plastic label, Roll, white, unlabeled, can be labeled with: THERMOMARK ROLLMASTER 300/600, THERMOMARK X1.2, THERMOMARK ROLL X1, THERMOMARK ROLL 2.0, THERMOMARK ROLL, mounting type: adhesive, lettering field size: 13 x 9 mm, Number of individual labels: 500

---

### Protective cap

Protective cap - QPD QSK BK 3/4X1,5 FS - 1414722



Protective cap, plastic, for QUICKON connection, black, with retaining cord, IP68

---

Protective cap - QPD QSK 3/4X1,5 - 1414723



Protective cap plastic, for QPD-QUICKON connection 3(4) x 1.5 mm², IP50

Phoenix Contact 2020 © - all rights reserved  
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG  
Flachsmarktstr. 8  
32825 Blomberg  
Germany  
Tel. +49 5235 300  
Fax +49 5235 3 41200  
<http://www.phoenixcontact.com>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Phoenix Contact:

1414721