

## Label, can be removed - EML-RM (32X10)RL-T - 0830547

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Label, can be removed, Roll, white, unlabeled, can be labeled with: THERMOMARK ROLLMASTER 300/600, THERMOMARK X1.2, THERMOMARK ROLL X1, THERMOMARK ROLL 2.0, THERMOMARK ROLL, mounting type: adhesive, lettering field size: 32 x 10 mm, Number of individual labels: 10000

### Your advantages

- ✓ The EML-RM label is ideal for temporary marking.
- ✓ This label features solid and reliable adhesion, but can also be easily removed again without any leftover residue. Once removed, it cannot be re-used
- ✓ When combined with the right ink ribbon, the marking is highly resistant to solvents and mechanical influences. The marking is even suitable for use under harsh industrial conditions.
- ✓ The EML-RM ... materials are UL-listed
- ✓ Labeling service: Phoenix Contact can custom-label all EML-RM ... markers in accordance with your requirements

RoHS

### Key Commercial Data

|              |                                                                                                         |
|--------------|---------------------------------------------------------------------------------------------------------|
| Packing unit | 1 pc                                                                                                    |
| GTIN         | <br>4 046356 720595 |
| GTIN         | 4046356720595                                                                                           |

### Technical data

#### Dimensions

|            |       |
|------------|-------|
| Length (b) | 10 mm |
| Width (a)  | 32 mm |

#### Ambient conditions

|                                 |                                                                                         |
|---------------------------------|-----------------------------------------------------------------------------------------|
| Ambient temperature (operation) | -40 °C ... 120 °C                                                                       |
| Ambient temperature (assembly)  | 15 °C                                                                                   |
| Recommended storage conditions  | 23 °C / 50% relative humidity. Storage in poly bags is recommended prior to processing. |

#### General

|            |                                |
|------------|--------------------------------|
| Color      | white                          |
| Components | free from silicone and halogen |

## Label, can be removed - EML-RM (32X10)RL-T - 0830547

### Technical data

#### General

|                                                                     |                                     |
|---------------------------------------------------------------------|-------------------------------------|
| Material                                                            | Polyester                           |
| RoHS compliant                                                      | Yes                                 |
| Wipe resistance                                                     | DIN EN 61010-1 (VDE 0411-1)         |
| Number of individual labels                                         | 10000                               |
| Number of individual labels per row                                 | 1                                   |
| Adhesive                                                            | Acrylic                             |
| Printability                                                        | Thermal transfer                    |
| Device                                                              | 5146477 THERMOMARK ROLL             |
|                                                                     | 5146723 THERMOMARK ROLL X1          |
|                                                                     | 5146231 THERMOMARK X1.2             |
| Ink ribbon                                                          | 5145384 THERMOMARK-RIBBON 110       |
| Test for substances that would hinder coating with paint or varnish | VW PV 3.10.7:2005-02                |
| Result                                                              | Test passed                         |
| Test specification weathering-resistance                            | Following ISO 4892-2:2013-03        |
| Test duration                                                       | 96 h                                |
| Result of weather resistance test                                   | Test passed                         |
| Salt spray test specification                                       | DIN EN ISO 9227:2012-09             |
| Test duration                                                       | 96 h                                |
| Salt spray testing result                                           | Test passed                         |
| Alternating condensation climate with SO2 test specification        | DIN 50018:2013-05                   |
| Climate level                                                       | AHT 1.0 S                           |
| Cycles                                                              | 2                                   |
| Condensation test result                                            | Test passed                         |
| Wipe resistance of test specification inscriptions                  | DIN EN 61010-1 (VDE 0411-1):2011-07 |
| Result of wipe resistance test                                      | Test passed                         |
| Foil strength                                                       | 50 µm                               |
| Adhesive strength                                                   | 20 µm                               |
| Marking mounting type                                               | adhesive                            |

#### Standards and Regulations

|                                  |                             |
|----------------------------------|-----------------------------|
| Connection in acc. with standard | UL                          |
| Wipe resistance                  | DIN EN 61010-1 (VDE 0411-1) |

### Classifications

#### eCl@ss

|               |          |
|---------------|----------|
| eCl@ss 10.0.1 | 27400629 |
| eCl@ss 4.0    | 24190200 |
| eCl@ss 4.1    | 24190200 |
| eCl@ss 5.0    | 27149100 |
| eCl@ss 5.1    | 27141100 |

## Label, can be removed - EML-RM (32X10)RL-T - 0830547

### Classifications

#### eCl@ss

|            |          |
|------------|----------|
| eCl@ss 6.0 | 27149100 |
| eCl@ss 7.0 | 27149129 |
| eCl@ss 8.0 | 27149129 |
| eCl@ss 9.0 | 27400629 |

#### ETIM

|          |          |
|----------|----------|
| ETIM 3.0 | EC000761 |
| ETIM 4.0 | EC000761 |
| ETIM 5.0 | EC001288 |
| ETIM 6.0 | EC001288 |
| ETIM 7.0 | EC001288 |

#### UNSPSC

|               |          |
|---------------|----------|
| UNSPSC 6.01   | 30211811 |
| UNSPSC 7.0901 | 39121410 |
| UNSPSC 11     | 39121410 |
| UNSPSC 12.01  | 39121410 |
| UNSPSC 13.2   | 39131504 |
| UNSPSC 18.0   | 39131504 |
| UNSPSC 19.0   | 39131504 |
| UNSPSC 20.0   | 39131504 |
| UNSPSC 21.0   | 39131504 |

### Approvals

#### Approvals

##### Approvals

##### UL Recognized

##### Ex Approvals

#### Approval details

|               |                                                                                     |                                                                                                                                                       |               |
|---------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------|---------------|
| UL Recognized |  | <a href="http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm">http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm</a> | FILE MH 48542 |
|---------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------|---------------|

### Accessories

#### Accessories

## Label, can be removed - EML-RM (32X10)RL-T - 0830547

### Accessories

Ink ribbon

Ink ribbon - THERMOMARK-RIBBON 110 - 5145384



Ink ribbon, for roll printers for printing the product groups TML..., WML..., WML HF..., WML-FLAG..., EML..., EML-ESD..., EML-RM..., EML-HA..., EMLS..., EMLC..., EMLP... and PMM..., width: 110 mm, color: black

---

Phoenix Contact 2020 © - all rights reserved  
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG  
Flachsmarktstr. 8  
32825 Blomberg  
Germany  
Tel. +49 5235 300  
Fax +49 5235 3 41200  
<http://www.phoenixcontact.com>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Phoenix Contact:

0830547