

## Marker for terminal blocks - US-TML (104X3,8) - 0830768

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Marker for terminal blocks, Card, white, unlabeled, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD, mounting type: adhesive, lettering field size: 104 x 3.8 mm, Number of individual labels: 22

### Your advantages

- ✓ UniSheet marker strips, self-adhesive, for terminal blocks without marker groove
- ✓ The perforated marking strips are easy to separate and can be easily fitted

RoHS

### Key Commercial Data

|                        |                                                                                                         |
|------------------------|---------------------------------------------------------------------------------------------------------|
| Packing unit           | 10 pc                                                                                                   |
| Minimum order quantity | 10 pc                                                                                                   |
| GTIN                   | <br>4 046356 752565 |
| GTIN                   | 4046356752565                                                                                           |

### Technical data

#### Dimensions

|            |        |
|------------|--------|
| Length (b) | 104 mm |
| Width (a)  | 3.8 mm |

#### Ambient conditions

|                                 |                                                                                                         |
|---------------------------------|---------------------------------------------------------------------------------------------------------|
| Ambient temperature (operation) | -40 °C ... 150 °C                                                                                       |
| Recommended storage conditions  | 23 °C/50 % relative humidity. Storage in a dry and dark place in the original packaging is recommended. |

#### General

|                 |                                |
|-----------------|--------------------------------|
| Color           | white                          |
| Type            | Label                          |
| Components      | free from silicone and halogen |
| Material        | Polyester                      |
| RoHS compliant  | Yes                            |
| Wipe resistance | DIN EN 61010-1 (VDE 0411-1)    |

# Marker for terminal blocks - US-TML (104X3,8) - 0830768

## Technical data

### General

|                                                                     |                                     |
|---------------------------------------------------------------------|-------------------------------------|
| Number of individual labels                                         | 22                                  |
| Number of individual labels per row                                 | 1                                   |
| Adhesive                                                            | Acrylic                             |
| Test for substances that would hinder coating with paint or varnish | VW PV 3.10.7:2005-02                |
| Result                                                              | Test passed                         |
| Test specification weathering-resistance                            | Following ISO 4892-2:2013-03        |
| Test duration                                                       | 96 h                                |
| Result of weather resistance test                                   | Test passed                         |
| Salt spray test specification                                       | DIN EN 60068-2-11:2000-02           |
| Test duration                                                       | 96 h                                |
| Salt spray testing result                                           | Test passed                         |
| Wipe resistance of test specification inscriptions                  | DIN EN 61010-1 (VDE 0411-1):2011-07 |
| Result of wipe resistance test                                      | Test passed                         |
| Marking mounting type                                               | adhesive                            |

### Standards and Regulations

|                 |                             |
|-----------------|-----------------------------|
| Wipe resistance | DIN EN 61010-1 (VDE 0411-1) |
|-----------------|-----------------------------|

## Classifications

### eCl@ss

|               |          |
|---------------|----------|
| eCl@ss 10.0.1 | 27141137 |
| eCl@ss 4.0    | 24190200 |
| eCl@ss 4.1    | 24190200 |
| eCl@ss 5.0    | 27141100 |
| eCl@ss 5.1    | 27141100 |
| eCl@ss 6.0    | 27141100 |
| eCl@ss 7.0    | 27141137 |
| eCl@ss 8.0    | 27141137 |
| eCl@ss 9.0    | 27141137 |

### ETIM

|          |          |
|----------|----------|
| ETIM 3.0 | EC000761 |
| ETIM 4.0 | EC000761 |
| ETIM 5.0 | EC000761 |
| ETIM 6.0 | EC000761 |
| ETIM 7.0 | EC000761 |

### UNSPSC

|               |          |
|---------------|----------|
| UNSPSC 6.01   | 30211811 |
| UNSPSC 7.0901 | 39121410 |
| UNSPSC 11     | 39121410 |

## Marker for terminal blocks - US-TML (104X3,8) - 0830768

### Classifications

#### UNSPSC

|              |          |
|--------------|----------|
| UNSPSC 12.01 | 39121410 |
| UNSPSC 13.2  | 39131505 |
| UNSPSC 18.0  | 39131505 |
| UNSPSC 19.0  | 39131505 |
| UNSPSC 20.0  | 39131505 |
| UNSPSC 21.0  | 39131505 |

Phoenix Contact 2020 © - all rights reserved  
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG  
Flachsmarktstr. 8  
32825 Blomberg  
Germany  
Tel. +49 5235 300  
Fax +49 5235 3 41200  
<http://www.phoenixcontact.com>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[0830768](#)