

Fuse insert - S 6 A/380 V - 0913032

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Fuse insert, nominal current: 6 A, length: 36 mm, diameter: 11 mm, color: green

Your advantages

- ✓ Contains no lead, cadmium, chromium 6 (ROHS-compliant)
- ✓ Colored indicating pins on the butt contact show the operating state
- ✓ NEOZED® fuse-links with gG characteristic for protecting lines and equipment
- ✓ Safe shutoff of impermissible overcurrents and short-circuit currents up to the nominal shutoff current

RoHS

Key Commercial Data

Packing unit	10 pc
GTIN	 4 017918 008130
GTIN	4017918008130

Technical data

General

Color	green
Maximum power dissipation for nominal condition	1.8 W

Dimensions

Length	36 mm
Diameter	11 mm

General

Fuse	gL/gK NEOZED
Nominal current I_N	6 A
Nominal voltage U_N	400 V AC (250 V DC)

Ambient conditions

Ambient temperature (operation)	-60 °C ... 85 °C
---------------------------------	------------------

Fuse insert - S 6 A/380 V - 0913032

Technical data

Ambient conditions

Ambient temperature (storage/transport)	-25 °C ... 55 °C (For a short time, not exceeding 24 h, -60 to +70 °C)
Permissible humidity (storage/transport)	30 % ... 70 %
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C

Classifications

eCl@ss

eCl@ss 10.0.1	27142002
eCl@ss 4.0	27142000
eCl@ss 4.1	27142000
eCl@ss 5.0	27142000
eCl@ss 5.1	27142000
eCl@ss 6.0	27142000
eCl@ss 7.0	27142002
eCl@ss 8.0	27142002
eCl@ss 9.0	27142002

ETIM

ETIM 2.0	EC000899
ETIM 3.0	EC000899
ETIM 4.0	EC000899
ETIM 5.0	EC002704
ETIM 6.0	EC002704
ETIM 7.0	EC002704

UNSPSC

UNSPSC 6.01	30211813
UNSPSC 7.0901	39121410
UNSPSC 11	39121412
UNSPSC 12.01	39121412
UNSPSC 13.2	39121627
UNSPSC 18.0	39121627
UNSPSC 19.0	39121627
UNSPSC 20.0	39121627
UNSPSC 21.0	39121627

Approvals

Approvals

Fuse insert - S 6 A/380 V - 0913032

Approvals

Approvals

EAC

Ex Approvals

Approval details

EAC		RU C- DE.BL08.B.00724
-----	---	--------------------------

Phoenix Contact 2020 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Phoenix Contact:

0913032