

Hazardous substances label - PML-GHS100 (13X13)R - 1014289

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Hazardous substances label, Roll, white/red, pre-printed, can be labeled with: THERMOMARK ROLLMASTER 300/600, THERMOMARK X1.2, THERMOMARK ROLL X1, THERMOMARK ROLL 2.0, THERMOMARK ROLL, mounting type: adhesive, diameter: 0 mm, lettering field size: 13 x 13 mm, Number of individual labels: 500

Your advantages

- ✓ The color preprinted PML-GHS ... hazardous substance labels without symbols allow you to create custom hazard notices. The PROJECT complete software offers a wide range of symbols
- ✓ The markers conform to the GHS international standard
- ✓ When combined with the right ink ribbon, the marking is highly resistant to solvents and mechanical influences. The marking is even suitable for use under harsh industrial conditions.



Key Commercial Data

Packing unit	1 pc
GTIN	 4 046356 787048
GTIN	4046356787048

Technical data

Dimensions

Length (b)	13 mm
Width (a)	13 mm
Height (c)	13 mm
Diameter	0.00 mm

Ambient conditions

Ambient temperature (operation)	-40 °C ... 150 °C
---------------------------------	-------------------

General

Color	white/red
Type	Diamond
Components	Silicone-free
Material	Polyester

Hazardous substances label - PML-GHS100 (13X13)R - 1014289

Technical data

General

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Number of individual labels	500
Number of individual labels per row	3
Marking mounting type	adhesive

Standards and Regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

Classifications

eCl@ss

eCl@ss 10.0.1	40200202
eCl@ss 4.0	40200100
eCl@ss 4.1	40200100
eCl@ss 5.0	40200100
eCl@ss 5.1	27371300
eCl@ss 6.0	40200100
eCl@ss 7.0	40200103
eCl@ss 8.0	40200202
eCl@ss 9.0	40200202

ETIM

ETIM 3.0	EC000712
ETIM 4.0	EC002498
ETIM 5.0	EC001777
ETIM 6.0	EC001777
ETIM 7.0	EC001777

UNSPSC

UNSPSC 6.01	43172501
UNSPSC 7.0901	43212107
UNSPSC 11	43172501
UNSPSC 12.01	43212107
UNSPSC 13.2	55121718
UNSPSC 18.0	55121718
UNSPSC 19.0	55121718
UNSPSC 20.0	55121718
UNSPSC 21.0	55121718

Accessories

Accessories

Hazardous substances label - PML-GHS100 (13X13)R - 1014289

Accessories

Ink ribbon

Ink ribbon - THERMOMARK-RIBBON 110 - 5145384



Ink ribbon, for roll printers for printing the product groups TML..., WML..., WML HF..., WML-FLAG..., EML..., EML-ESD..., EML-RM..., EML-HA..., EMLS..., EMLC..., EMLP... and PMM..., width: 110 mm, color: black

Labeled systems marker

Pipeline markers - PML-T101 (26X280)R CUS - 1014249



Pipeline markers, can be ordered: by line, green, labeled according to customer specifications: Water, mounting type: adhesive, diameter: 0 mm, lettering field size: 26 x 280 mm

Pipeline markers - PML-T101 (52X560)R CUS - 1014250

Pipeline markers, can be ordered: by line, green, labeled according to customer specifications: Water, mounting type: adhesive, diameter: 0 mm, lettering field size: 52 x 560 mm



Pipeline markers - PML-T102 (26X280)R CUS - 1014251



Pipeline markers, can be ordered: by line, red, labeled according to customer specifications: Steam, mounting type: adhesive, diameter: 0 mm, lettering field size: 26 x 280 mm

Pipeline markers - PML-T102 (52X560)R CUS - 1014252

Pipeline markers, can be ordered: by line, red, labeled according to customer specifications: Steam, mounting type: adhesive, diameter: 0 mm, lettering field size: 52 x 560 mm



Hazardous substances label - PML-GHS100 (13X13)R - 1014289

Accessories

Pipeline markers - PML-T103 (26X280)R CUS - 1014253



Pipeline markers, can be ordered: by line, gray, labeled according to customer specifications: Air, mounting type: adhesive, diameter: 0 mm, lettering field size: 26 x 280 mm

Pipeline markers - PML-T103 (52X560)R CUS - 1014254



Pipeline markers, can be ordered: by line, gray, labeled according to customer specifications: Air, mounting type: adhesive, diameter: 0 mm, lettering field size: 52 x 560 mm

Pipeline markers - PML-T104 (26X280)R CUS - 1014255



Pipeline markers, can be ordered: by line, yellow/red, labeled according to customer specifications: flammable gases, mounting type: adhesive, diameter: 0 mm, lettering field size: 26 x 280 mm

Pipeline markers - PML-T104 (52X560)R CUS - 1014256



Pipeline markers, can be ordered: by line, yellow/red, labeled according to customer specifications: flammable gases, mounting type: adhesive, diameter: 0 mm, lettering field size: 52 x 560 mm

Pipeline markers - PML-T105 (26X280)R CUS - 1014257



Pipeline markers, can be ordered: by line, yellow/black, labeled according to customer specifications: Non-flammable liquids, mounting type: adhesive, diameter: 0 mm, lettering field size: 26 x 280 mm

Hazardous substances label - PML-GHS100 (13X13)R - 1014289

Accessories

Pipeline markers - PML-T105 (52X560)R CUS - 1014258

Pipeline markers, can be ordered: by line, yellow/black, labeled according to customer specifications: Non-flammable liquids, mounting type: adhesive, diameter: 0 mm, lettering field size: 52 x 560 mm



Pipeline markers - PML-T106 (26X280)R CUS - 1014259



Pipeline markers, can be ordered: by line, orange, labeled according to customer specifications: Acids, mounting type: adhesive, diameter: 0 mm, lettering field size: 26 x 280 mm

Pipeline markers - PML-T106 (52X560)R CUS - 1014260

Pipeline markers, can be ordered: by line, orange, labeled according to customer specifications: Acids, mounting type: adhesive, diameter: 0 mm, lettering field size: 52 x 560 mm



Pipeline markers - PML-T107 (26X280)R CUS - 1014261



Pipeline markers, can be ordered: by line, violet, labeled according to customer specifications: Alkalies, mounting type: adhesive, diameter: 0 mm, lettering field size: 26 x 280 mm

Pipeline markers - PML-T107 (52X560)R CUS - 1014262

Pipeline markers, can be ordered: by line, violet, labeled according to customer specifications: Alkalies, mounting type: adhesive, diameter: 0 mm, lettering field size: 52 x 560 mm



Hazardous substances label - PML-GHS100 (13X13)R - 1014289

Accessories

Pipeline markers - PML-T108 (26X280)R CUS - 1014263



Pipeline markers, can be ordered: by line, brown/red, labeled according to customer specifications: flammable liquids, mounting type: adhesive, diameter: 0 mm, lettering field size: 26 x 280 mm

Pipeline markers - PML-T108 (52X560)R CUS - 1014264



Pipeline markers, can be ordered: by line, brown/red, labeled according to customer specifications: flammable liquids, mounting type: adhesive, diameter: 0 mm, lettering field size: 52 x 560 mm

Pipeline markers - PML-T109 (26X280)R CUS - 1014265



Pipeline markers, can be ordered: by line, brown/black, labeled according to customer specifications: Non-flammable liquids, mounting type: adhesive, diameter: 0 mm, lettering field size: 26 x 280 mm

Pipeline markers - PML-T109 (52X560)R CUS - 1014266



Pipeline markers, can be ordered: by line, brown/black, labeled according to customer specifications: Non-flammable liquids, mounting type: adhesive, diameter: 0 mm, lettering field size: 52 x 560 mm

Pipeline markers - PML-T110 (26X280)R CUS - 1014267



Pipeline markers, can be ordered: by line, blue, labeled according to customer specifications: Oxygen, mounting type: adhesive, diameter: 0 mm, lettering field size: 26 x 280 mm

Hazardous substances label - PML-GHS100 (13X13)R - 1014289

Accessories

Pipeline markers - PML-T110 (52X560)R CUS - 1014268

Pipeline markers, can be ordered: by line, blue, labeled according to customer specifications: Oxygen, mounting type: adhesive, diameter: 0 mm, lettering field size: 52 x 560 mm



System marking

Pipeline markers - PML-T101 (26X280)R - 1014229



Pipeline markers, Roll, green, pre-printed, can be labeled with: THERMOMARK ROLLMaster 300/600, THERMOMARK X1.2, THERMOMARK ROLL X1, THERMOMARK ROLL 2.0, THERMOMARK ROLL, mounting type: adhesive, diameter: 0 mm, lettering field size: 26 x 280 mm, Number of individual labels: 250

Pipeline markers - PML-T101 (52X560)R - 1014230

Pipeline markers, Roll, green, pre-printed, can be labeled with: THERMOMARK ROLLMaster 300/600, THERMOMARK X1.2, THERMOMARK ROLL X1, THERMOMARK ROLL 2.0, THERMOMARK ROLL, mounting type: adhesive, diameter: 0 mm, lettering field size: 52 x 560 mm, Number of individual labels: 250



Pipeline markers - PML-T102 (26X280)R - 1014231



Pipeline markers, Roll, red, pre-printed, can be labeled with: THERMOMARK ROLLMaster 300/600, THERMOMARK X1.2, THERMOMARK ROLL X1, THERMOMARK ROLL 2.0, THERMOMARK ROLL, mounting type: adhesive, diameter: 0 mm, lettering field size: 26 x 280 mm, Number of individual labels: 250

Pipeline markers - PML-T102 (52X560)R - 1014232

Pipeline markers, Roll, red, pre-printed, can be labeled with: THERMOMARK ROLLMaster 300/600, THERMOMARK X1.2, THERMOMARK ROLL X1, THERMOMARK ROLL 2.0, THERMOMARK ROLL, mounting type: adhesive, diameter: 0 mm, lettering field size: 52 x 560 mm, Number of individual labels: 250



Hazardous substances label - PML-GHS100 (13X13)R - 1014289

Accessories

Pipeline markers - PML-T103 (26X280)R - 1014233



Pipeline markers, Roll, gray, pre-printed, can be labeled with: THERMOMARK ROLLMASTER 300/600, THERMOMARK X1.2, THERMOMARK ROLL X1, THERMOMARK ROLL 2.0, THERMOMARK ROLL, mounting type: adhesive, diameter: 0 mm, lettering field size: 26 x 280 mm, Number of individual labels: 250

Pipeline markers - PML-T103 (52X560)R - 1014234



Pipeline markers, Roll, gray, pre-printed, can be labeled with: THERMOMARK ROLLMASTER 300/600, THERMOMARK X1.2, THERMOMARK ROLL X1, THERMOMARK ROLL 2.0, THERMOMARK ROLL, mounting type: adhesive, diameter: 0 mm, lettering field size: 52 x 560 mm, Number of individual labels: 250

Pipeline markers - PML-T104 (26X280)R - 1014235



Pipeline markers, Roll, yellow/red, pre-printed, can be labeled with: THERMOMARK ROLLMASTER 300/600, THERMOMARK X1.2, THERMOMARK ROLL X1, THERMOMARK ROLL 2.0, THERMOMARK ROLL, mounting type: adhesive, diameter: 0 mm, lettering field size: 26 x 280 mm, Number of individual labels: 250

Pipeline markers - PML-T104 (52X560)R - 1014236



Pipeline markers, Roll, yellow/red, pre-printed, can be labeled with: THERMOMARK ROLLMASTER 300/600, THERMOMARK X1.2, THERMOMARK ROLL X1, THERMOMARK ROLL 2.0, THERMOMARK ROLL, mounting type: adhesive, diameter: 0 mm, lettering field size: 52 x 560 mm, Number of individual labels: 250

Pipeline markers - PML-T105 (26X280)R - 1014237



Pipeline markers, Roll, yellow/black, pre-printed, can be labeled with: THERMOMARK ROLLMASTER 300/600, THERMOMARK X1.2, THERMOMARK ROLL X1, THERMOMARK ROLL 2.0, THERMOMARK ROLL, mounting type: adhesive, diameter: 0 mm, lettering field size: 26 x 280 mm, Number of individual labels: 250

Hazardous substances label - PML-GHS100 (13X13)R - 1014289

Accessories

Pipeline markers - PML-T105 (52X560)R - 1014238

Pipeline markers, Roll, yellow/black, pre-printed, can be labeled with: THERMOMARK ROLLMASTER 300/600, THERMOMARK X1.2, THERMOMARK ROLL X1, THERMOMARK ROLL 2.0, THERMOMARK ROLL, mounting type: adhesive, diameter: 0 mm, lettering field size: 52 x 560 mm, Number of individual labels: 250



Pipeline markers - PML-T106 (26X280)R - 1014239



Pipeline markers, Roll, orange, pre-printed, can be labeled with: THERMOMARK ROLLMASTER 300/600, THERMOMARK X1.2, THERMOMARK ROLL X1, THERMOMARK ROLL 2.0, THERMOMARK ROLL, mounting type: adhesive, diameter: 0 mm, lettering field size: 26 x 280 mm, Number of individual labels: 250

Pipeline markers - PML-T106 (52X560)R - 1014240



Pipeline markers, Roll, orange, pre-printed, can be labeled with: THERMOMARK ROLLMASTER 300/600, THERMOMARK X1.2, THERMOMARK ROLL X1, THERMOMARK ROLL 2.0, THERMOMARK ROLL, mounting type: adhesive, diameter: 0 mm, lettering field size: 52 x 560 mm, Number of individual labels: 250

Pipeline markers - PML-T107 (26X280)R - 1014241



Pipeline markers, Roll, violet, pre-printed, can be labeled with: THERMOMARK ROLLMASTER 300/600, THERMOMARK X1.2, THERMOMARK ROLL X1, THERMOMARK ROLL 2.0, THERMOMARK ROLL, mounting type: adhesive, diameter: 0 mm, lettering field size: 26 x 280 mm, Number of individual labels: 250

Pipeline markers - PML-T107 (52X560)R - 1014242



Pipeline markers, Roll, violet, pre-printed, can be labeled with: THERMOMARK ROLLMASTER 300/600, THERMOMARK X1.2, THERMOMARK ROLL X1, THERMOMARK ROLL 2.0, THERMOMARK ROLL, mounting type: adhesive, diameter: 0 mm, lettering field size: 52 x 560 mm, Number of individual labels: 250

Hazardous substances label - PML-GHS100 (13X13)R - 1014289

Accessories

Pipeline markers - PML-T108 (26X280)R - 1014243



Pipeline markers, Roll, brown/red, pre-printed, can be labeled with: THERMOMARK ROLLMASTER 300/600, THERMOMARK X1.2, THERMOMARK ROLL X1, THERMOMARK ROLL 2.0, THERMOMARK ROLL, mounting type: adhesive, diameter: 0 mm, lettering field size: 26 x 280 mm, Number of individual labels: 250

Pipeline markers - PML-T108 (52X560)R - 1014244



Pipeline markers, Roll, brown/red, pre-printed, can be labeled with: THERMOMARK ROLLMASTER 300/600, THERMOMARK X1.2, THERMOMARK ROLL X1, THERMOMARK ROLL 2.0, THERMOMARK ROLL, mounting type: adhesive, diameter: 0 mm, lettering field size: 52 x 560 mm, Number of individual labels: 250

Pipeline markers - PML-T109 (26X280)R - 1014245



Pipeline markers, Roll, brown/black, pre-printed, can be labeled with: THERMOMARK ROLLMASTER 300/600, THERMOMARK X1.2, THERMOMARK ROLL X1, THERMOMARK ROLL 2.0, THERMOMARK ROLL, mounting type: adhesive, diameter: 0 mm, lettering field size: 26 x 280 mm, Number of individual labels: 250

Pipeline markers - PML-T109 (52X560)R - 1014246



Pipeline markers, Roll, brown/black, pre-printed, can be labeled with: THERMOMARK ROLLMASTER 300/600, THERMOMARK X1.2, THERMOMARK ROLL X1, THERMOMARK ROLL 2.0, THERMOMARK ROLL, mounting type: adhesive, diameter: 0 mm, lettering field size: 52 x 560 mm, Number of individual labels: 250

Pipeline markers - PML-T110 (26X280)R - 1014247



Pipeline markers, Roll, blue, pre-printed, can be labeled with: THERMOMARK ROLLMASTER 300/600, THERMOMARK X1.2, THERMOMARK ROLL X1, THERMOMARK ROLL 2.0, THERMOMARK ROLL, mounting type: adhesive, diameter: 0 mm, lettering field size: 26 x 280 mm, Number of individual labels: 250

Hazardous substances label - PML-GHS100 (13X13)R - 1014289

Accessories

Pipeline markers - PML-T110 (52X560)R - 1014248

Pipeline markers, Roll, blue, pre-printed, can be labeled with: THERMOMARK ROLLMASTER 300/600, THERMOMARK X1.2, THERMOMARK ROLL X1, THERMOMARK ROLL 2.0, THERMOMARK ROLL, mounting type: adhesive, diameter: 0 mm, lettering field size: 52 x 560 mm, Number of individual labels: 250



Phoenix Contact 2020 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[1014289](#)