

Power distributor - SACB-4/T-L-8FUSE DIAG CT AXL - 1411048

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Power distributor, application: Power supply, connection method: M12 socket Metal, number of slots: 4, number of positions: 4, coding: T power, slot assignment: single, status display: yes, Universal; master cable connection: Plug-in master cable connection 90°, shielding: no, Diagnostics port, M12, A-coded, 12-pos.

Your advantages

- ✓ Safety in the field, thanks to molded housing and high degree of protection
- ✓ Convenient: increased machine availability thanks to quick and easy diagnostics
- ✓ Flexible: distributor box with connector hood for on-site assembly

RoHS

Key Commercial Data

Packing unit	1 pc
GTIN	 4 046356 920254
GTIN	4046356920254

Technical data

General

Rated voltage	24 V DC
Max. operating voltage U_{max}	30.5 V DC
Current carrying capacity per I/O signal	10 A (M12 diagnostic socket for each channel max. 50 mA)
Current carrying capacity per slot	2x 9.25 A (at 40 °C)
Total rated current	70 A (at 40°C, observe the distribution of the current paths under load)
Protective circuit	Overload protection for the outputs Fuse in header
Number of positions	4
Number of slots	4
Flammability rating according to UL 94	V0
Sensor/actuator connection system	M12 socket
Note	NOTE: Observe the permissible bending radii when laying conductors, since the degree of protection may be put in jeopardy if the bending forces are too high. Alleviate mechanical loads upstream of the connector, e.g. by using cable ties.

Power distributor - SACB-4/T-L-8FUSE DIAG CT AXL - 1411048

Technical data

General

	Unused slots are to be sealed off prior to commissioning. Suitable sealing elements are to be found under "Accessories".
--	--

Ambient conditions

Degree of protection	IP66
	IP67
Ambient temperature (operation)	-25 °C ... 60 °C
Ambient temperature (storage/transport)	-25 °C ... 80 °C

Local diagnostics function

Local diagnostics	Supply voltage per module Green LED
	Status display I/O Yellow LED

Master cable data/connection data

Connection method	Plug-in master cable connection
Conductor cross section min. (energy)	2.5 mm ²
Conductor cross section max. (energy)	6 mm ²
Conductor cross section AWG min. (energy)	14
Conductor cross section AWG max. (energy)	10
External cable diameter min.	9 mm
External cable diameter max.	15.5 mm
Tightening torque, cover screw	0.6 Nm
Tightening torque, union nut	5 Nm
Tightening torque slot sensor/actuator cable	0.4 Nm

Insulation material

Housing material	PBT
Material of the moulding mass	PUR
Contact material	Cu alloy
Contact surface material	pre-nickel plated, gold-plated
Contact carrier material	PA
Material of contact, master cable side	CU alloy
Material of contact surface, master cable side	Silver-plated
Material of the contact carrier on the master cable side	PC
Material of threaded sleeve	Zinc die-cast
Material of threaded sleeve surface	Nickel-plated
Sealing material	Viton (M12 socket)
	NBR (Master cable side)

Standards and Regulations

Standards/specifications	M12 connector IEC 61076-2-111
	Shock, vibration EN 60068-2-6 EN 60068-2-27 EN 60068-2-64
Flammability rating according to UL 94	V0

Power distributor - SACB-4/T-L-8FUSE DIAG CT AXL - 1411048


Technical data

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
China RoHS	Environmentally Friendly Use Period = 50 years
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

Drawings


Connection diagram



The fuses for the individual current paths can be monitored via the M12 diagnostics interface. Monitoring is via optocouplers and is therefore electrically isolated from the power distribution.

Power distributor - SACB-4/T-L-8FUSE DIAG CT AXL - 1411048


Schematic diagram



Pin assignment of M12 socket, 12-pos., A-coded, view of socket side, assignment: see connection drawing


Power distributor - SACB-4/T-L-8FUSE DIAG CT AXL - 1411048

Dimensional drawing




Power distributor - SACB-4/T-L-8FUSE DIAG CT AXL - 1411048

Circuit diagram




Circuit diagram



Power distributor - SACB-4/T-L-8FUSE DIAG CT AXL - 1411048

Schematic diagram



Pin assignment of M12 socket, 4-pos., T-coded, socket side view

Classifications

eCl@ss

eCl@ss 10.0.1	27440111
eCl@ss 5.1	27250300
eCl@ss 6.0	27279200
eCl@ss 7.0	27279219
eCl@ss 8.0	27279219
eCl@ss 9.0	27440108

ETIM

ETIM 5.0	EC002585
----------	----------

Power distributor - SACB-4/T-L-8FUSE DIAG CT AXL - 1411048

Classifications

ETIM

ETIM 6.0	EC002585
ETIM 7.0	EC002585

UNSPSC

UNSPSC 13.2	31251501
UNSPSC 19.0	31251501
UNSPSC 20.0	31251501
UNSPSC 21.0	31251501

Approvals

Approvals

Approvals

EAC

Ex Approvals

Approval details

EAC		RU C- DE.BL08.B.00511
-----	---	--------------------------

Accessories

Accessories

Circular connector (cable-side)

Power connectors - SACC-M12MST-3PECON-PG11-M - 1404643



Power connectors, Power, 4-position, unshielded, Plug straight M12, Coding: T, Screw connection, knurl material: Zinc die-cast, nickel-plated, cable gland Pg11, external cable diameter 8 mm ... 10 mm, For direct current up to 12 A/63 V, Contact 4 leading

Power distributor - SACB-4/T-L-8FUSE DIAG CT AXL - 1411048

Accessories

Power connectors - SACC-M12MRT-4CON-PG11-M - 1408988



Power connectors, 4-position, Plug angled M12, Coding: T, Screw connection, knurl material: Zinc die-cast, nickel-plated, cable gland Pg11, external cable diameter 8 mm ... 10 mm, For direct current up to 12 A/63 V, Contact 4 leading

Crimping tool

Crimping pliers - CRIMPFOX-TC 10 - 1212114



Crimping pliers, for turned contacts with a pin diameter of 4.0 mm, two marked die stations, pressure lock can be released, lateral entry, incl. positioning help

Crimping pliers - CRIMPFOX-TC 4 - 1212113



Crimping pliers, for CK 1,6-ED..., CK 2,5-ED..., CK 4,0-ED... turned contacts, 4 marked die stations, unlockable pressure lock, lateral entry, incl. positioning tool

Device marking

Snap-in markers - UCT-EM (7X10) - 0830765



Snap-in markers, Sheet, white, unlabeled, can be labeled with: TOPMARK NEO, TOPMARK LASER, BLUEMARK ID COLOR, BLUEMARK ID, BLUEMARK CLED, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD, mounting type: snapped into marker carrier, lettering field size: 7 x 10 mm, Number of individual labels: 30

Plug for cable screw gland

Screw plug - PROT-MS SCO - 1553129



Power cable

Power distributor - SACB-4/T-L-8FUSE DIAG CT AXL - 1411048

Accessories

Power cable - SAC-4P-M12MST/ 1,0-PUR/M12FST - 1408808



Power cable, 4-position, PUR halogen-free, black-gray RAL 7021, Plug straight M12, coding: T, on Socket straight M12, coding: T, cable length: 1 m, For direct current up to 12 A/63 V

Screwdriver tools

Tool - SAC BIT M12-D15 - 1208432



Nut for assembling sensor/actuator cables with M12 connector and M12 connectors for assembly, with a knurl diameter of 15 mm, for 4 mm hexagonal drive

Tool - SACC BIT M12-D20 - 1208445



Nut for assembling M12 connectors for assembly with a knurl diameter of 20 mm, for 4 mm hexagonal drive

Philips screwdriver - SZK PZ1 VDE - 1206450



Screwdriver, PZ crosshead, VDE insulated, size: PZ 1 x 80 mm, 2-component grip, with non-slip grip

Sensor/actuator cable

Sensor/actuator cable - SAC-12P-MS/10,0-PVC SCO - 1554801



Sensor/actuator cable, 12-position, PVC, black RAL 9005, Plug straight M12 SPEEDCON, coding: A, on free cable end, cable length: 10 m

Torque tool

Power distributor - SACB-4/T-L-8FUSE DIAG CT AXL - 1411048

Accessories

Torque screwdriver - TSD 04 SAC - 1208429



Torque screwdriver, with preset torque of 0.4 Nm and 4 mm hexagonal drive for M12 connectors

Necessary add-on products

Crimp contact - CK4,0-ED-6,00BU AG - 1663307



Turned 4.0 crimp contact, individual female contact, core diameter 6.00 mm², silver-plated

Crimp contact - CK4,0-ED-4,00BU AG - 1663297



Turned 4.0 crimp contact, individual female contact, core diameter 4.00 mm², silver-plated

Crimp contact - CK4,0-ED-2,50BU AG - 1663284



Turned 4.0 crimp contact, individual female contact, core diameter 2.50 mm², silver-plated

Contact insert - HC-COM- 4/2-EBUC - 1408517



HEAVYCON crimp contact insert for compact plastic housing, socket version; 4-pos. + PE supply circuit, 2-pos. control circuit

Power distributor - SACB-4/T-L-8FUSE DIAG CT AXL - 1411048

Accessories

Housing - HC-COM-K-TFL-O1PG16-S - 1408339



Sleeve housing for single locking engagement nose, lateral cable outlet, for HC-COM-K-KV-PG16 screw connections...

Housing - HC-COM-K-TFL-O1PG16-G - 1408342



Sleeve housing for single locking engagement nose, straight cable outlet, for HC-COM-K-KV-PG16 screw connections...

Cable gland - VC-K-KV-PG16(11,5-15,5) - 1854844



Half screw connection Pg16, made of plastic, consisting of rubber seal with one hole and one pressure screw, for type 1 housings, cable [mm] 11.5 - 15.5

Cable gland - VC-K-KV-PG16(9-13) - 1853764



Half screw connection Pg16, made of plastic, consisting of rubber seal with one hole and one pressure screw, for type 1 housings, cable [mm] 9 - 13

Phoenix Contact 2020 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[1411048](#)