

## Interface module - FLKM-D15 SUB/B/ZFKDS - 2304047

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Standard 1:1 D-SUB module, with spring-cage connection and D-SUB socket strip, no. of positions 15

The figure shows the version  
FLKM-D37 SUB/S/ZFKDS

### Your advantages

- ✓ 9 to 50-pos.
- ✓ Spring-cage connection technology
- ✓ According to IEC 60807-2
- ✓ 1:1 connection



### Key Commercial Data

|              |                                                                                      |
|--------------|--------------------------------------------------------------------------------------|
| Packing unit | 1 pc                                                                                 |
| GTIN         |  |
| GTIN         | 4017918944018                                                                        |

### Technical data

#### Dimensions

|        |       |
|--------|-------|
| Width  | 45 mm |
| Height | 77 mm |
| Depth  | 52 mm |

#### Ambient conditions

|                                         |                  |
|-----------------------------------------|------------------|
| Ambient temperature (operation)         | -20 °C ... 50 °C |
| Ambient temperature (storage/transport) | -20 °C ... 70 °C |

#### General

|                                 |         |
|---------------------------------|---------|
| Max. perm. operating voltage    | 25 V AC |
|                                 | 60 V DC |
| Max. perm. current (per branch) | 2.5 A   |

# Interface module - FLKM-D15 SUB/B/ZFKDS - 2304047

## Technical data

### General

|                       |                                        |
|-----------------------|----------------------------------------|
|                       | 1.5 A (with even load on all branches) |
| Number of positions   | 15                                     |
| Status display        | No                                     |
| Mounting position     | any                                    |
| Assembly instructions | In rows with zero spacing              |
| Degree of protection  | IP20                                   |

### Connection data for connection 1

|                                  |                                             |
|----------------------------------|---------------------------------------------|
| Connection name                  | Field level                                 |
| Connection method                | Spring-cage connection                      |
| Stripping length                 | 7 mm                                        |
| Conductor cross section solid    | 0.2 mm <sup>2</sup> ... 4 mm <sup>2</sup>   |
| Conductor cross section flexible | 0.2 mm <sup>2</sup> ... 2.5 mm <sup>2</sup> |
| Conductor cross section AWG      | 24 ... 12                                   |
| Number of positions              | 16                                          |

### Connection data for connection 2

|                     |                    |
|---------------------|--------------------|
| Connection name     | Controller level   |
| Connection method   | D-SUB socket strip |
| Number of positions | 15                 |

### Standards and Regulations

|                                  |                       |
|----------------------------------|-----------------------|
| Connection in acc. with standard | CUL                   |
| Standards/regulations            | IEC 60664             |
|                                  | DIN EN 50178          |
| Rated insulation voltage         | 125 V                 |
| Rated surge voltage              | 1.2 kV                |
| Insulation                       | Functional insulation |
| Degree of pollution              | 2                     |
| Overvoltage category             | II                    |


### Environmental Product Compliance

|            |                                                                                                     |
|------------|-----------------------------------------------------------------------------------------------------|
| China RoHS | Environmentally Friendly Use Period = 50                                                            |
|            | For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration" |

## Drawings

## Interface module - FLKM-D15 SUB/B/ZFKDS - 2304047

Circuit diagram



### Approvals

#### Approvals

Approvals

UL Recognized / cUL Recognized / EAC / cULus Recognized

Ex Approvals

#### Approval details

|                    |                                                                                     |                                                                                                                                                       |               |
|--------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------|---------------|
| UL Recognized      |  | <a href="http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm">http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm</a> | FILE E 238705 |
| Nominal voltage UN |                                                                                     | 125 V                                                                                                                                                 |               |
| Nominal current IN |                                                                                     | 2.5 A                                                                                                                                                 |               |

|                    |                                                                                     |                                                                                                                                                       |               |
|--------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------|---------------|
| cUL Recognized     |  | <a href="http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm">http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm</a> | FILE E 238705 |
| Nominal voltage UN |                                                                                     | 125 V                                                                                                                                                 |               |
| Nominal current IN |                                                                                     | 2.5 A                                                                                                                                                 |               |

|     |                                                                                     |                          |  |
|-----|-------------------------------------------------------------------------------------|--------------------------|--|
| EAC |  | RU C-<br>DE.A*30.B.01742 |  |
|-----|-------------------------------------------------------------------------------------|--------------------------|--|

|                  |                                                                                     |  |  |
|------------------|-------------------------------------------------------------------------------------|--|--|
| cULus Recognized |  |  |  |
|------------------|-------------------------------------------------------------------------------------|--|--|

Phoenix Contact 2018 © - all rights reserved  
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG  
Flachsmarktstr. 8  
32825 Blomberg  
Germany  
Tel. +49 5235 300  
Fax +49 5235 3 41200  
<http://www.phoenixcontact.com>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Phoenix Contact:

2304047