

Marker for terminal blocks - TMT (EX5,5)R - 0803062

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Marker for terminal blocks, Roll, white, unlabeled, can be labeled with: THERMOMARK ROLL 2.0, THERMOMARK ROLL, THERMOMARK ROLL X1, THERMOMARK ROLLMASTER 300/600, THERMOMARK X1.2, mounting type: snap into universal marker groove, snap into flat marker groove, for terminal block width: 50000 mm, lettering field size: 5.5 x 50,000 mm, Number of individual labels: 1

Your advantages

- ✓ The TMT labeling range includes markers for all products with tall and flat marker grooves
- ✓ Quick and inexpensive marking with THERMOMARK ... roll printers from PHOENIX CONTACT
- ✓ The thermal transfer printer cutting units make it possible to trim precisely to the required length. This enables faster and cleaner equipment marking.
- ✓ When combined with the right ink ribbon, the marking is highly resistant to solvents and mechanical influences. The marking is even suitable for use under harsh industrial conditions.
- ✓ Labeling service: Phoenix Contact can custom-label all TMT ... markers in accordance with your requirements

RoHS

Key Commercial Data

Packing unit	1 pc
GTIN	 4 046356 935517
GTIN	4046356935517

Technical data

Dimensions

Length (b)	50 m
Width (a)	5.5 mm

Ambient conditions

Ambient temperature (operation)	-30 °C ... 80 °C
Recommended storage conditions	10-30 °C / 40-70 % relative humidity. Storage in the original packaging is recommended prior to processing.

General

Color	white
Type	flat
Components	Silicone-free

Marker for terminal blocks - TMT (EX5,5)R - 0803062

Technical data

General

Flammability rating according to UL 94	V0
Material	PVC
RoHS compliant	Yes
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Number of individual labels	1
Number of individual labels per row	1
Test for substances that would hinder coating with paint or varnish	VW PV 3.10.7:2005-02
Result	Test passed
Test specification weathering-resistance	Following ISO 4892-2:2013-03
Test duration	96 h
Result of weather resistance test	Test passed
Salt spray test specification	DIN EN 60068-2-11:2000-02
Test duration	96 h
Salt spray testing result	Test passed
Alternating condensation climate with SO2 test specification	following DIN 50018:2013-05
Climate level	AHT 1.0 S
Cycles	2
Condensation test result	Test passed
Wipe resistance of test specification inscriptions	DIN EN 61010-1 (VDE 0411-1):2011-07
Result of wipe resistance test	Test passed
Marking mounting type	snap into universal marker groove

Standards and Regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Flammability rating according to UL 94	V0

Classifications

eCl@ss

eCl@ss 10.0.1	27141137
eCl@ss 5.0	27141100
eCl@ss 5.1	27141100
eCl@ss 6.0	27141100
eCl@ss 7.0	27141137
eCl@ss 8.0	27141137
eCl@ss 9.0	27141137

ETIM

ETIM 4.0	EC000761
ETIM 5.0	EC000761
ETIM 6.0	EC000761

Marker for terminal blocks - TMT (EX5,5)R - 0803062

Classifications

ETIM

ETIM 7.0	EC000761
----------	----------

UNSPSC

UNSPSC 13.2	39131505
UNSPSC 18.0	39131505
UNSPSC 19.0	39131505
UNSPSC 20.0	39131505
UNSPSC 21.0	39131505

Accessories

Accessories

Ink ribbon

Ink ribbon - THERMOMARK-RIBBON 110-WMTB HF - 5148007



Ink ribbon, for roll printer for printing product groups WMTB HF..., WMS-2 HF..., TMT..., and EMT..., width: 110 mm, color: black

Phoenix Contact 2020 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Phoenix Contact:

0803062