

## Housing screw connection - SACC-FP-M-M8/M10 SMD - 1412502

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




M8 pin, front mounting SMD with M10 screw fastening

### Your advantages

- ✓ Reduced mounting costs thanks to two-piece device connector
- ✓ Easy device integration, thanks to mechanical port screw connections with threaded fastening
- ✓ Efficient PCB assembly: two-piece connectors for SMT soldering

RoHS

### Key Commercial Data

Packing unit	10 pc
Minimum order quantity	10 pc
GTIN	 4 046356 989084
GTIN	4046356989084

### Technical data

#### Ambient conditions

Ambient temperature (operation)	-25 °C ... 85 °C (Plug / socket)
	-40 °C ... 85 °C (without mechanical actuation)
Degree of protection	IP67 (correctly plugged in and locked)

#### General

Note	The electrical and mechanical data specified assume that the connector pair is correctly locked and mounted. If the connector is unlocked and if there is a danger of contamination, the connector must be sealed using a protective cap > IP54. Influences arising from litz wires, cables or PCB assembly must also be taken into consideration.
Standards/regulations	M8 connector IEC 61076-2-104 In line with
Torque	2 Nm ... 3 Nm (Installation-side)
Mounting type	Front mounting M10 x 0.75

#### Material

## Housing screw connection - SACC-FP-M-M8/M10 SMD - 1412502

### Technical data

#### Material

Material, knurls	Nickel-plated brass
Material	Brass, nickel-plated
Sealing material	FKM (O-ring on housing)
	FKM (O-ring (pin connector pattern))

#### Cable

Standards/specifications	M8 connector IEC 61076-2-104 In line with
--------------------------	---

#### Standards and Regulations


Standards/specifications	M8 connector IEC 61076-2-104 In line with
--------------------------	---

#### Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
China RoHS	Environmentally Friendly Use Period = 50 years
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

### Drawings

Dimensional drawing



## Housing screw connection - SACC-FP-M-M8/M10 SMD - 1412502

### Classifications

#### eCl@ss

eCl@ss 10.0.1	27371392
eCl@ss 4.0	27378000
eCl@ss 4.1	27378000
eCl@ss 5.0	27379100
eCl@ss 5.1	27379100
eCl@ss 6.0	27379200
eCl@ss 7.0	27379201
eCl@ss 8.0	27379201
eCl@ss 9.0	27379201

#### ETIM

ETIM 5.0	EC002498
ETIM 6.0	EC002498
ETIM 7.0	EC002498

#### UNSPSC

UNSPSC 13.2	39121421
UNSPSC 18.0	39121421
UNSPSC 19.0	39121421
UNSPSC 20.0	39121421
UNSPSC 21.0	39121421

### Approvals

#### Approvals

Approvals

EAC

Ex Approvals

#### Approval details

EAC		B.01687
-----	---	---------

### Accessories

Accessories

Panel mounting base

## Housing screw connection - SACC-FP-M-M8/M10 SMD - 1412502

### Accessories

Nut - SACC-M10-NUT - 1412508



M10 flat nut

---

Phoenix Contact 2020 © - all rights reserved  
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG  
Flachsmarktstr. 8  
32825 Blomberg  
Germany  
Tel. +49 5235 300  
Fax +49 5235 3 41200  
<http://www.phoenixcontact.com>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[1412502](#)