

Marker strip - SK CUS - 0828492

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Marker strip, Card, can be ordered: by card, white, labeled according to customer specifications, mounting type: adhesive, for terminal block width: 52 mm, lettering field size: 50 x 100 mm

Your advantages

- ✓ Labeling service: Phoenix Contact can custom-label SK markers according to your requirements
- ✓ The SK labeling range offers self-adhesive marker strips for labeling products that do not have a marker groove
- ✓ The markers that are supplied in roll format can be labeled quickly and cost-effectively using THERMOMARK printers



Key Commercial Data

Packing unit	1 pc
GTIN	
GTIN	4046356512633

Technical data

Dimensions

Width (a)	50 mm
-----------	-------

Ambient conditions

Ambient temperature (operation)	-40 °C ... 150 °C
Ambient temperature (assembly)	> 15 °C
Recommended storage conditions	23 °C / 50% relative humidity. Storage in the original packaging is recommended prior to processing.

General

Note	Marking up to max. 25-pos.
Color	white
Type	Label
Components	free from silicone and halogen
Material	Polyester
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)

Marker strip - SK CUS - 0828492

Technical data

General

Adhesive	Acrylic
Printability	Thermal transfer
Device	5146477 THERMOMARK ROLL
	5146231 THERMOMARK X1.2
Ink ribbon	5145384 THERMOMARK-RIBBON 110
Test for substances that would hinder coating with paint or varnish	VW PV 3.10.7:2005-02
Result	Test passed
Test specification weathering-resistance	Following ISO 4892-2:2013-03
Test duration	96 h
Result of weather resistance test	Test passed
Salt spray test specification	DIN EN 60068-2-11:2000-02
Test duration	96 h
Salt spray testing result	Test passed
Alternating condensation climate with SO2 test specification	DIN 50018:2013-05
Climate level	AHT 1.0 S
Cycles	2
Condensation test result	Test passed
Wipe resistance of test specification inscriptions	DIN EN 61010-1 (VDE 0411-1):2011-07
Result of wipe resistance test	Test passed
Foil strength	53 µm
Adhesive strength	20 µm
Marking mounting type	adhesive

Standards and Regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

Environmental Product Compliance

China RoHS	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"
------------	---

Drawings

Marker strip - SK CUS - 0828492

Schematic diagram



- ① Horizontal
- ② Vertical

Classifications

eCl@ss

eCl@ss 10.0.1	27141137
eCl@ss 4.0	24190200
eCl@ss 4.1	24190200
eCl@ss 5.0	27141100
eCl@ss 5.1	27141100
eCl@ss 6.0	27141100
eCl@ss 7.0	27141137
eCl@ss 8.0	27141137
eCl@ss 9.0	27141137

ETIM

ETIM 3.0	EC000761
ETIM 4.0	EC000761
ETIM 5.0	EC000761

Marker strip - SK CUS - 0828492

Classifications

ETIM

ETIM 6.0	EC000761
ETIM 7.0	EC000761

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39131505
UNSPSC 18.0	39131505
UNSPSC 19.0	39131505
UNSPSC 20.0	39131505
UNSPSC 21.0	39131505

Phoenix Contact 2020 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Phoenix Contact:

0828492