

Marker for terminal blocks - UCT1-TMF 6 CUS - 0829724

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Marker for terminal blocks, can be ordered: by sheet, white, labeled according to customer specifications, mounting type: snap into flat marker groove, for terminal block width: 6.2 mm, lettering field size: 5.2 x 5.45 mm, Number of individual labels: 60

Your advantages

- ✓ The UCT1-TMF ... UniCard labeling range includes markers for Weidmüller, Wago, ABB (entrelec), Conta-Clip, and Klemsan terminal blocks
- ✓ Labeling service: Phoenix Contact can custom-label all UniCard markers according to your requirements



Key Commercial Data

Packing unit	1 pc
GTIN	 4 046356 598774
GTIN	4046356598774

Technical data

Dimensions

Length (b)	5.2 mm
Width (a)	5.45 mm
Height (c)	2.36 mm

Ambient conditions

Ambient temperature (operation)	-40 °C ... 120 °C
Recommended storage conditions	23 °C/50 % relative humidity. Storage in a dry and dark place in the original packaging is recommended.

General

Note	Can be labeled via thermal transfer
Color	white
Type	flat
Components	free from silicone and halogen
Flammability rating according to UL 94	V0
Material	PC

Marker for terminal blocks - UCT1-TMF 6 CUS - 0829724

Technical data

General

	PC
RoHS compliant	Yes
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Number of individual labels	60
Number of individual labels per row	10
Test for substances that would hinder coating with paint or varnish	VW PV 3.10.7:2005-02
Result	Test passed
Test specification weathering-resistance	Following ISO 4892-2:2013-03
Test duration	96 h
Result of weather resistance test	Test passed
Salt spray test specification	DIN EN 60068-2-11:2000-02
Test duration	96 min.
Salt spray testing result	Test passed
Wipe resistance of test specification inscriptions	DIN EN 61010-1 (VDE 0411-1):2011-07
Result of wipe resistance test	Test passed
Marking mounting type	snap into flat marker groove
Result	Test passed
Oxygen index (DIN EN ISO 4589-2)	32.4 %
R22	HL 1 - HL 3
R23	HL 1 - HL 3
R24	HL 1 - HL 3


Standards and Regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Flammability rating according to UL 94	V0

Drawings

Marker for terminal blocks - UCT1-TMF 6 CUS - 0829724

Schematic diagram



- ① Horizontal
- ② Vertical

Classifications

eCl@ss

eCl@ss 10.0.1	27141137
eCl@ss 4.0	24190200
eCl@ss 4.1	24190200
eCl@ss 5.0	27141100
eCl@ss 5.1	27141100
eCl@ss 6.0	27141100
eCl@ss 7.0	27141137
eCl@ss 8.0	27141137
eCl@ss 9.0	27141137

ETIM

ETIM 4.0	EC000761
ETIM 5.0	EC000761
ETIM 6.0	EC000761

Marker for terminal blocks - UCT1-TMF 6 CUS - 0829724

Classifications

ETIM

ETIM 7.0	EC000761
----------	----------

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39131505
UNSPSC 18.0	39131505
UNSPSC 19.0	39131505
UNSPSC 20.0	39131505
UNSPSC 21.0	39131505

Phoenix Contact 2020 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[0829724](#)