

Housing - HC-COM-BAWS-EL-AL - 1078593

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Panel mounting base COM, with single locking latch, material: Die-cast aluminum, salt water resistant, height: 37.5 mm, cable gland: none, support sleeve: no, Standard



COMPLIANT

Key Commercial Data

Packing unit	1 pc
GTIN	 4 055626 794112
GTIN	4055626794112

Technical data

Dimensions

Height	37.5 mm
Width	49.5 mm
Length	63.5 mm
Length of the assembly cutout	27 mm
Width of the assembly cutout	24.5 mm

Ambient conditions

Degree of protection (IP)	IP66
Ambient temperature (operation)	-40 °C ... 125 °C

General

Size	COM
Housing type	Panel mounting base
Color	gray aluminum
Locking type	with single locking latch
Screw connection	none
Housing material	Die-cast aluminum, salt water resistant
Seal material	NBR
Material lock	PA

Housing - HC-COM-BAWS-EL-AL - 1078593


Technical data

General


Flammability rating according to UL 94	V0 (Interlock)
--	----------------

Drawings

Dimensional drawing



Dimensional drawing



Mounting cutout

Housing - HC-COM-BAWS-EL-AL - 1078593

Classifications

eCl@ss

eCl@ss 10.0.1	27440202
eCl@ss 4.0	27140816
eCl@ss 4.1	27140816
eCl@ss 5.0	27143424
eCl@ss 5.1	27261200
eCl@ss 6.0	27261200
eCl@ss 7.0	27440202
eCl@ss 8.0	27440202
eCl@ss 9.0	27440202

ETIM

ETIM 4.0	EC000437
ETIM 5.0	EC000437
ETIM 6.0	EC000437
ETIM 7.0	EC000437

UNSPSC

UNSPSC 6.01	31261502
UNSPSC 7.0901	31261502
UNSPSC 11	31261502
UNSPSC 12.01	31261502
UNSPSC 13.2	31261501
UNSPSC 18.0	31261501
UNSPSC 19.0	31261501
UNSPSC 20.0	31261501
UNSPSC 21.0	31261501

Approvals

Approvals

Approvals

UL Recognized / cUL Recognized / cULus Recognized

Ex Approvals

Approval details

Housing - HC-COM-BAWS-EL-AL - 1078593

Approvals

UL Recognized



<http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm>

E255026

cUL Recognized



<http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm>

E255026

cULus Recognized



Phoenix Contact 2020 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[1078593](#)