

Holder - HS EH-B 140,5 DCS - 1082302

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




140.5 mm housing attachment, for max. load 10 kg, with ball joint and fastening plate 60 mm, pivotable in 15° increments, for 30 mm wall/profile bracket, material: black glass-fiber reinforced polycarbonate PC, and black anodized aluminum, 342 g

Your advantages

- ✓ Secure mounting of small and large monitors and operator interfaces, thanks to the high load-bearing capacity
- ✓ Can be swiveled and tilted in three axes for optimum alignment with the field of view
- ✓ VESA interface in standard VESA 75 and VESA 100 for easy wall or aluminum profile mounting
- ✓ Item belongs to the DCS product range

RoHS

Key Commercial Data

Packing unit	1 pc
GTIN	 4 055626 812748
GTIN	4055626812748

Technical data

Item properties

Type	HS EH-B 140,5 DCS
Order No.	1082302
Housing type	Housing bracket
Type	Ball joint

Packaging information

Pieces per package	1
Denomination packing units	Pcs.

Classifications

eCl@ss

eCl@ss 10.0.1	27182702
---------------	----------

Holder - HS EH-B 140,5 DCS - 1082302

Classifications

eCl@ss

eCl@ss 5.1	27180506
eCl@ss 6.0	27180800
eCl@ss 7.0	27182702
eCl@ss 8.0	27182702
eCl@ss 9.0	27182702

ETIM

ETIM 5.0	EC001031
ETIM 6.0	EC001031
ETIM 7.0	EC001031

Accessories

Additional products

Holder - HS WM-S 75 DCS - 1082304



75 mm wall bracket, pivotable, with four 6.5 mm mounting holes and mounting diameter of 30 mm for housing attachment, black glass-fiber reinforced polycarbonate PC, and aluminum, 306 g

Holder - HS PM-S 40 DCS - 1082305



Profile console for 40 mm aluminum profile, pivotable with mounting kit, bracket for housing attachment diameter 30 mm, material: black glass-fiber reinforced polycarbonate PC, and aluminum, 270 g

Connecting plate - HS MP VESA75/100 DCS - 1082303



VESA 75/100 connection plate with M5 mounting kit for DCS 15" display support, die cast aluminum, 80 g

Electronic housing - DCS 15 M C O SLV C 7035 - 2203190



Display housing, 15", light gray, central window, front level, with ventilation slots, cutout for connection technology angle plate, and VESA mount consisting of two half shells with screws

Holder - HS EH-B 140,5 DCS - 1082302

Accessories

Phoenix Contact 2020 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Phoenix Contact:

1082302