

Crimping pliers - CRIMPFOX VARIO 16S - 1108767

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Crimping pliers, type of contact: Insulated and uninsulated ferrules, standards/specifications: DIN 46228-1, DIN 46228-4, min. cross section: 6 mm², max. cross section: 16 mm², compression: square, black/green

Your advantages

- ✓ Lateral conductor entry
- ✓ Proven high-quality technology
- ✓ "The original"
- ✓ Suitable for TWIN sleeves
- ✓ Unlockable pressure lock



Key Commercial Data

Packing unit	1 pc
GTIN	 4 063151 016449
GTIN	4063151016449

Technical data

Dimensions

Length (b)	222 mm
Width (a)	76 mm
Height (c)	25 mm

General

Color	black/green
Compression	square
Type of contact	Insulated and uninsulated ferrules
Designation	Crimping position 1
Max. cross section	6 mm ²
AWG max	10
Designation	Crimping position 2
Max. cross section	10 mm ²
AWG max	8

Crimping pliers - CRIMPFOX VARIO 16S - 1108767

Technical data

General

Designation	Crimping position 3
Max. cross section	16 mm ²
AWG max	6
Weight	582 g
Min. cross section	6 mm ²
Max. cross section	16 mm ²
AWG min	10
AWG max	6

Classifications

eCl@ss

eCl@ss 9.0	21043811
------------	----------

Approvals

Approvals

Approvals

EAC

Ex Approvals

Approval details

EAC		RU x- DE.xx08.B.02974
-----	---	--------------------------

Phoenix Contact 2020 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[1108767](#)