

## Sensor/actuator cable - SAC-5P-MS/10,0-186/FS SCO - 1518452

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Sensor/actuator cable, 5-position, PUR, black-gray RAL 7021, Plug straight M12 SPEEDCON, coding: A, on Socket straight M12 SPEEDCON, coding: A, cable length: 10 m

### Your advantages

- ✓ Easy and safe: 100% electrically tested plug-in components
- ✓ Save time, thanks to installation with SPEEDCON fast locking system
- ✓ High-performance: connectors and cables with a large conductor cross section for power supply



### Key Commercial Data

|              |                                                                                                         |
|--------------|---------------------------------------------------------------------------------------------------------|
| Packing unit | 1 pc                                                                                                    |
| GTIN         | <br>4 017918 968571 |
| GTIN         | 4017918968571                                                                                           |

### Technical data

#### Dimensions

|                 |      |
|-----------------|------|
| Length of cable | 10 m |
|-----------------|------|

#### Ambient conditions

|                                 |                                  |
|---------------------------------|----------------------------------|
| Ambient temperature (operation) | -25 °C ... 90 °C (Plug / socket) |
| Degree of protection            | IP65                             |
|                                 | IP67                             |
|                                 | IP68                             |

#### General

|                       |          |
|-----------------------|----------|
| Rated current at 40°C | 4 A      |
| Rated voltage         | 48 V AC  |
|                       | 60 V DC  |
| Number of positions   | 5        |
| Insulation resistance | ≥ 100 MΩ |

# Sensor/actuator cable - SAC-5P-MS/10,0-186/FS SCO - 1518452

## Technical data

### General

|                              |              |
|------------------------------|--------------|
| Coding                       | A - standard |
| Status display               | No           |
| Protective circuit/component | unwired      |
| Overvoltage category         | II           |
| Degree of pollution          | 3            |
| Insertion/withdrawal cycles  | ≥ 100        |

### Material

|                                        |                                             |
|----------------------------------------|---------------------------------------------|
| Flammability rating according to UL 94 | HB                                          |
| Contact material                       | CuSn                                        |
| Contact surface material               | Ni/Au                                       |
| Contact carrier material               | TPU GF                                      |
| Material of grip body                  | TPU, hardly inflammable, self-extinguishing |
| Material, knurls                       | Zinc die-cast, nickel-plated                |
| Sealing material                       | NBR                                         |

### Standards and Regulations

|                                        |    |
|----------------------------------------|----|
| Flammability rating according to UL 94 | HB |
|----------------------------------------|----|

### Cable

|                                               |                                      |
|-----------------------------------------------|--------------------------------------|
| Cable type                                    | PUR POWER 0.75 mm <sup>2</sup> black |
| Cable type (abbreviation)                     | 186                                  |
| Cable abbreviation                            | LiY11Y                               |
| Conductor cross section                       | 5x 0.75 mm <sup>2</sup> (power line) |
| AWG signal line                               | 18                                   |
| Conductor structure signal line               | 42x 0.15 mm                          |
| Core diameter including insulation            | 1.7 mm ±0.05 mm                      |
| Thickness, insulation                         | ≥ 0.23 mm (Core insulation)          |
|                                               | ≥ 0.76 mm (Outer cable sheath)       |
| Wire colors                                   | Brown, white, blue, black, gray      |
| Overall twist                                 | 5 wires around filler to the core    |
| External sheath, color                        | black-gray RAL 7021                  |
| External cable diameter D                     | 6.3 mm ±0.2 mm                       |
| Smallest bending radius, movable installation | 63 mm                                |
| Number of bending cycles                      | 2000000                              |
| Bending radius                                | 63 mm                                |
| Traversing path                               | 5 m                                  |
| Traversing rate                               | 3 m/s                                |
| Acceleration                                  | 5 m/s <sup>2</sup>                   |
| Cable weight                                  | 67 kg/km                             |
| Outer sheath, material                        | PUR                                  |
| Material conductor insulation                 | PVC                                  |

## Sensor/actuator cable - SAC-5P-MS/10,0-186/FS SCO - 1518452

### Technical data

#### Cable


|                                 |                                                     |
|---------------------------------|-----------------------------------------------------|
| Conductor material              | Bare Cu litz wires                                  |
| Insulation resistance           | $\geq 1 \text{ M}\Omega \cdot \text{km}$ (at 20 °C) |
| Conductor resistance            | max. 26 $\Omega/\text{km}$ (at 20 °C)               |
| Nominal voltage, cable          | $\leq 300 \text{ V}$                                |
| Test voltage, cable             | $\geq 3000 \text{ V}$                               |
| Flame resistance                | in accordance with DIN UL-Style 20549               |
| Ambient temperature (operation) | -25 °C ... 80 °C (cable, fixed installation)        |
|                                 | -5 °C ... 80 °C (cable, flexible installation)      |

#### Environmental Product Compliance

|            |                                                         |
|------------|---------------------------------------------------------|
| China RoHS | Environmentally friendly use period: unlimited = EFUP-e |
|            | No hazardous substances above threshold values          |


### Drawings

Dimensional drawing



Plug, M12 x 1, straight, shielded

Dimensional drawing



M12 x 1 socket, straight

## Sensor/actuator cable - SAC-5P-MS/10,0-186/FS SCO - 1518452


Circuit diagram



Contact assignment of the M12 plug and the M12 socket

## Sensor/actuator cable - SAC-5P-MS/10,0-186/FS SCO - 1518452


Schematic diagram



Pin assignment M12 male connector, 5-pos., A-coded, male side

## Sensor/actuator cable - SAC-5P-MS/10,0-186/FS SCO - 1518452


Schematic diagram



Pin assignment M12 socket, 5-pos., A-coded, socket side view

## Sensor/actuator cable - SAC-5P-MS/10,0-186/FS SCO - 1518452

Cable cross section



PUR POWER 0.75 mm² black [186]

### Classifications

eCl@ss

|               |          |
|---------------|----------|
| eCl@ss 10.0.1 | 27060311 |
| eCl@ss 4.0    | 27060300 |
| eCl@ss 4.1    | 27060300 |
| eCl@ss 5.0    | 27061800 |
| eCl@ss 5.1    | 27061800 |
| eCl@ss 6.0    | 27279200 |
| eCl@ss 7.0    | 27279218 |
| eCl@ss 8.0    | 27279218 |
| eCl@ss 9.0    | 27060311 |

# Sensor/actuator cable - SAC-5P-MS/10,0-186/FS SCO - 1518452

## Classifications

### ETIM

|          |          |
|----------|----------|
| ETIM 2.0 | EC000830 |
| ETIM 3.0 | EC001855 |
| ETIM 4.0 | EC001855 |
| ETIM 5.0 | EC001855 |
| ETIM 6.0 | EC001855 |
| ETIM 7.0 | EC001855 |

### UNSPSC

|               |          |
|---------------|----------|
| UNSPSC 6.01   | 31251501 |
| UNSPSC 7.0901 | 31251501 |
| UNSPSC 11     | 31251501 |
| UNSPSC 12.01  | 31251501 |
| UNSPSC 13.2   | 31251501 |
| UNSPSC 19.0   | 31251501 |
| UNSPSC 20.0   | 31251501 |
| UNSPSC 21.0   | 31251501 |

## Approvals

### Approvals

#### Approvals

UL Listed / cUL Listed / EAC-RoHS / cULus Listed

#### Ex Approvals

### Approval details

|                    |                                                                                     |                                                                                                                                                       |               |
|--------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------|---------------|
| UL Listed          |  | <a href="http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm">http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm</a> | FILE E 221474 |
| Nominal voltage UN | 125 V                                                                               |                                                                                                                                                       |               |
| Nominal current IN | 4 A                                                                                 |                                                                                                                                                       |               |

|                    |                                                                                     |                                                                                                                                                       |               |
|--------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------|---------------|
| cUL Listed         |  | <a href="http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm">http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm</a> | FILE E 221474 |
| Nominal voltage UN | 125 V                                                                               |                                                                                                                                                       |               |



## Sensor/actuator cable - SAC-5P-MS/10,0-186/FS SCO - 1518452

### Approvals

|                                |     |
|--------------------------------|-----|
| Nominal current I <sub>N</sub> | 4 A |
|--------------------------------|-----|

|          |                                                                                   |                          |
|----------|-----------------------------------------------------------------------------------|--------------------------|
| EAC-RoHS |  | RU D-<br>DE.HB35.B.00387 |
|----------|-----------------------------------------------------------------------------------|--------------------------|

|              |                                                                                   |
|--------------|-----------------------------------------------------------------------------------|
| cULus Listed |  |
|--------------|-----------------------------------------------------------------------------------|

Phoenix Contact 2020 © - all rights reserved  
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG  
Flachsmarktstr. 8  
32825 Blomberg  
Germany  
Tel. +49 5235 300  
Fax +49 5235 3 41200  
<http://www.phoenixcontact.com>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Phoenix Contact:

1518452