

Media module - FL IF 2TX VS-RJ-F - 2832344

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Interface module for connecting twisted pair cable, RJ45, connection direction forward



Key Commercial Data

Packing unit	1 pc
Weight per Piece (excluding packing)	95.8 g
Custom tariff number	85366990
Country of origin	Germany

Technical data

Note

Utilization restriction	EMC: class A product, see manufacturer's declaration in the download area
-------------------------	---

Dimensions

Width	31 mm
Height	75.7 mm
Depth	75.5 mm

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-20 °C ... 55 °C (non-condensing)
Ambient temperature (storage/transport)	-20 °C ... 80 °C
Permissible humidity (operation)	10 % ... 95 % (non-condensing)
Permissible humidity (storage/transport)	10 % ... 95 % (non-condensing)

Interfaces

Interface 1	Ethernet
No. of ports	2 (RJ45 ports)

Media module - FL IF 2TX VS-RJ-F - 2832344

Technical data

Interfaces

Connection method	RJ45 socket
Transmission physics	Ethernet in RJ45 twisted pair
Transmission speed	10/100 MBit/s (connection direction forwards)
Transmission length	100 m (per segment)
Transmission speed	10/100 MBit/s (connection direction forwards)
Transmission length	100 m (per segment)

Function

Basic functions	Media module for modular managed switch
-----------------	---

Supply voltage

Supply voltage	via head station
Typical current consumption	10 mA

Conformity with EMC directives

Developed in acc. with standard	IEC 61000-6.2
Test standard	IEC 61000-4-2 (ESD)
Test result	Criterion B
Test standard	IEC 61000-4-3 (immunity to radiated interference)
Test result	Criterion A
Test standard	IEC 61000-4-4 (burst)
Test result	Criterion A
Test standard	IEC 61000-4-5 (surge)
Test result	Criterion A
Test standard	IEC 61000-4-6 (immunity to conducted interference)
Test result	Criterion A
Test standard	IEC 61000-4-8 (immunity to magnetic fields)
Test result	Criterion A
Test standard	EN 55022 (emitted interference)
Test result	Criterion A

Mechanical tests

Type of test	Shock in acc. with EN 60068-2-27/IEC 60068-2-27
Test result	Operation: 25g, 11 ms duration, semi-sinusoidal shock impulse
Type of test	Shock in acc. with EN 60068-2-27/IEC 60068-2-27
Test result	Storage/Transport: 50g, 11 ms duration, semi-sinusoidal shock impulse
Type of test	Vibration resistance in acc. with EN 60068-2-6/IEC 60068-2-6
Test result	Operation/Storage/Transport: 5g, 150 Hz, Criterion 3
Type of test	Free fall in acc. with IEC 60068-2-32

Media module - FL IF 2TX VS-RJ-F - 2832344

Technical data

Mechanical tests

Test result	1 m
Flammability rating according to UL 94	V0

General

Mounting type	In the host system
Type AX	Stand-alone
Net weight	70 g
Housing material	PA 6.6

Standards and Regulations

Electromagnetic compatibility	Conformance with EMC Directive 2004/108/EC
Developed in acc. with standard	IEC 61000-6.2
Test standard	IEC 61000-4-2 (ESD)
Test result	Criterion B
Test standard	IEC 61000-4-3 (immunity to radiated interference)
Test result	Criterion A
Test standard	IEC 61000-4-4 (burst)
Test result	Criterion A
Test standard	IEC 61000-4-5 (surge)
Test result	Criterion A
Test standard	IEC 61000-4-6 (immunity to conducted interference)
Test result	Criterion A
Test standard	IEC 61000-4-8 (immunity to magnetic fields)
Test result	Criterion A
Test standard	EN 55022 (emitted interference)
Test result	Criterion A
Type of test	Shock in acc. with EN 60068-2-27/IEC 60068-2-27
Test result	Operation: 25g, 11 ms duration, semi-sinusoidal shock impulse
Type of test	Shock in acc. with EN 60068-2-27/IEC 60068-2-27
Test result	Storage/Transport: 50g, 11 ms duration, semi-sinusoidal shock impulse
Type of test	Vibration resistance in acc. with EN 60068-2-6/IEC 60068-2-6
Test result	Operation/Storage/Transport: 5g, 150 Hz, Criterion 3
Type of test	Free fall in acc. with IEC 60068-2-32
Test result	1 m
Noise emission	EN 61000-6-3/-4
Noise immunity	EN 61000-6-2:2005
Vibration (storage/transport)	5g, 150 Hz, in acc. with IEC 60068-2-6
Free from substances that could impair the application of coating	In acc. with VW specification

Media module - FL IF 2TX VS-RJ-F - 2832344

Technical data

Standards and Regulations

Connection in acc. with standard	CUL
Flammability rating according to UL 94	V0
Vibration (operation)	In acc. with IEC 60068-2-6: 5g, 150 Hz

Classifications

eCl@ss

eCl@ss 4.0	27250501
eCl@ss 4.1	27250501
eCl@ss 5.0	27250501
eCl@ss 5.1	27250501
eCl@ss 6.0	19170106
eCl@ss 7.0	19170106
eCl@ss 8.0	19170390

ETIM

ETIM 2.0	EC000734
ETIM 3.0	EC000734
ETIM 4.0	EC001467
ETIM 5.0	EC000309

UNSPSC

UNSPSC 6.01	43172015
UNSPSC 7.0901	43201404
UNSPSC 11	43172015
UNSPSC 12.01	43201410
UNSPSC 13.2	43201410

Approvals

Approvals

Approvals

UL Recognized / cUL Recognized / BV / DNV / EAC / KC / cULus Recognized

Ex Approvals


UL Listed / cUL Listed / cULus Listed


Media module - FL IF 2TX VS-RJ-F - 2832344

Approvals

Approvals submitted

Approval details

UL Recognized 


cUL Recognized 

BV

DNV

EAC

KC

cULus Recognized 

Accessories

Accessories

Patch cable

Patch cable - FL CAT5 PATCH 0,3 - 2832250

Patch cable, CAT5, assembled, 0.3 m



Media module - FL IF 2TX VS-RJ-F - 2832344

Accessories

Patch cable - FL CAT5 PATCH 0,5 - 2832263



Patch cable, CAT5, assembled, 0.5 m

Patch cable - FL CAT5 PATCH 1,0 - 2832276



Patch cable, CAT5, assembled, 1.0 m

Patch cable - FL CAT5 PATCH 1,5 - 2832221



Patch cable, CAT5, assembled, 1.5 m

Patch cable - FL CAT5 PATCH 2,0 - 2832289



Patch cable, CAT5, assembled, 2.0 m

Patch cable - FL CAT5 PATCH 3,0 - 2832292



Patch cable, CAT5, assembled, 3.0 m

Media module - FL IF 2TX VS-RJ-F - 2832344

Accessories

Patch cable - FL CAT5 PATCH 5,0 - 2832580



Patch cable, CAT5, assembled, 5.0 m

Patch cable - FL CAT5 PATCH 7,5 - 2832616



Patch cable, CAT5, assembled, 7.5 m

Patch cable - FL CAT5 PATCH 10,0 - 2832629



Patch cable, CAT5, assembled, 10.0 m

Protective cap

Dust protection - FL RJ45 PROTECT CAP - 2832991




Dust protection caps for RJ45 socket

Drawings

Media module - FL IF 2TX VS-RJ-F - 2832344

Dimensional drawing



The illustration shows a version of the interface module with the head station FL SWITCH MM HS

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[2832344](#)