

Connector - ES-FT-BPC-S 16-25 OG - 1106303

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



High-voltage connector for new energy storage system, rated voltage: 1500 V, rated current: 120 A; wiring method: crimping; surface coating: silver; positive pole: orange; with one set of plug and socket each;



Key Commercial Data

Packing unit	1 pc
GTIN	
GTIN	4063151003494

Technical data

Ambient conditions

Ambient temperature (operation)	-40 °C ... 115 °C
Ambient temperature (storage/transport)	-40 °C ... 70 °C

General

Nominal voltage U_N	1500 V DC (TUV)
Connection method	Crimp
Degree of protection	IP65
Insulating material	PA
Contact surface material	Ni/Ag
Contact material	Cu/Al alloy
Seal material	Silicon
Contact resistance	$\leq 5 \text{ m}\Omega$
Insertion/withdrawal cycles	100
Insertion force	$\leq 75 \text{ N}$
Withdrawal force	$\geq 10 \text{ N}$
Current	120 A

Standards and Regulations

Flammability rating according to UL 94	V0
--	----

Connector - ES-FT-BPC-S 16-25 OG - 1106303

Technical data

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Classifications

eCl@ss

eCl@ss 9.0	27062002
------------	----------

Accessories

Accessories

Dust protection cover - ES-FT-BPC PROTECTION CAP - 1130817



Dust protection cap for energy storage connector , color: black RAL9005, ambient temperature for storage and transportation: -40°C ~70°C, operating temperature: -20°C ~105°C, halogen-free, engineering plastics: UL94 HB, protection class: IP65 (with socket)

Phoenix Contact 2020 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[1106303](#)