

Connector - ES-BPC-C 16-25 OG - 1106306

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




High-voltage connector for new energy storage system, rated voltage: 1500 V, rated current: 120 A; wiring method: crimping; surface coating: silver; negative pole: black; with one set of plug and socket each;

Your advantages

- ✓ Patented design with "three proofs and one rotation"
- ✓ Mismatching and short circuit proof
- ✓ Touch proof
- ✓ Foolproof mechanism installed
- ✓ Safety lock
- ✓ 360 degree free rotation and flexible wiring



Key Commercial Data

Packing unit	20 pc
GTIN	 4 063151 003470
GTIN	4063151003470

Technical data

Ambient conditions

Ambient temperature (operation)	-40 °C ... 115 °C
---------------------------------	-------------------

General

Insertion force	≤ 75 N
Disconnect force	≥ 10 N
Insertion/withdrawal cycles	> 100
Degree of pollution	2
Voltage	1500 V
Protection class	III

Material

Color	orange
-------	--------

Connector - ES-BPC-C 16-25 OG - 1106306

Technical data

Material

Insulating material	PA
Contact material	Cu/Al alloy
Contact surface material	Ni/Ag , Ni/Sn
Flammability rating according to UL 94	V0

Connection data

Connection method	Crimp
Contact resistance with connected conductor	$\leq 5 \text{ m}\Omega$
Stripping length	22 mm

Standards and Regulations

Flammability rating according to UL 94	V0
--	----

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Classifications

eCl@ss

eCl@ss 9.0	27062002
------------	----------

Phoenix Contact 2020 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[1106306](#)