

## Power cable - SAC-5P- 5,0-500/M12FRL FE SH - 1414811

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Power cable, 5-position, PVC, gray RAL 7001, shielded (Advanced Shielding Technology), Socket angled M12, coding: L, on free cable end, cable length: 5 m, for direct current up to 16 A/63 V

### Your advantages

- ✓ Easy and safe: 100% electrically tested plug-in components
- ✓ High-performance: DC connectors for up to 16 A and 63 V DC
- ✓ Protection against mismatching, thanks to special L-coding
- ✓ Shield power reliably – 360° shielding to reduce electromagnetic loads

RoHS

### Key Commercial Data

|              |                                                                                                         |
|--------------|---------------------------------------------------------------------------------------------------------|
| Packing unit | 1 pc                                                                                                    |
| GTIN         | <br>4 055626 034454 |
| GTIN         | 4055626034454                                                                                           |

### Technical data

#### Dimensions

|                 |     |
|-----------------|-----|
| Length of cable | 5 m |
|-----------------|-----|

#### Ambient conditions

|                                 |                                  |
|---------------------------------|----------------------------------|
| Ambient temperature (operation) | -25 °C ... 85 °C (Plug / socket) |
| Degree of protection            | IP65                             |
|                                 | IP67                             |
|                                 | IP68                             |

#### General

|                       |          |
|-----------------------|----------|
| Rated current at 40°C | 16 A     |
| Rated voltage         | 63 V DC  |
| Number of positions   | 5        |
| Insulation resistance | ≥ 100 MΩ |

# Power cable - SAC-5P- 5,0-500/M12FRL FE SH - 1414811

## Technical data

### General

|                              |                               |
|------------------------------|-------------------------------|
| Coding                       | L - Power                     |
| Standards/regulations        | M12 connector IEC 61076-2-111 |
| Status display               | No                            |
| Protective circuit/component | unwired                       |
| Overvoltage category         | III                           |
| Degree of pollution          | 3                             |
| Insertion/withdrawal cycles  | ≥ 100                         |
| Torque                       | 0.4 Nm (M12 connector)        |

### Material

|                                        |                              |
|----------------------------------------|------------------------------|
| Flammability rating according to UL 94 | V0                           |
| Contact material                       | CuZn                         |
| Contact surface material               | Ni/Au                        |
| Contact carrier material               | PA                           |
| Material of grip body                  | PP                           |
| Material, knurls                       | Zinc die-cast, nickel-plated |

### Standards and Regulations

|                                        |                               |
|----------------------------------------|-------------------------------|
| Standards/specifications               | M12 connector IEC 61076-2-111 |
| Flammability rating according to UL 94 | V0                            |

### Cable

|                                                 |                                 |
|-------------------------------------------------|---------------------------------|
| UL AWM style                                    | 20233 / 10493 (80°C/300 V)      |
| Conductor cross section                         | 5x 2.5 mm <sup>2</sup>          |
| AWG power supply                                | 14                              |
| Conductor structure, voltage supply             | 141x 0.15 mm                    |
| Core diameter including insulation              | 3 mm ±0.1 mm                    |
| Thickness, insulation                           | ≥ 0.36 mm                       |
| Wire colors                                     | Brown, white, blue, black, gray |
| External sheath, color                          | gray RAL 7001                   |
| Outer sheath thickness                          | approx. 0.76 mm                 |
| External cable diameter D                       | 10.8 mm ±0.3 mm                 |
| Minimum bending radius, fixed installation      | 5 x D                           |
| Minimum bending radius, flexible installation   | 10 x D                          |
| Number of bending cycles                        | 1000000                         |
| Minimum bending radius, drag chain applications | 10 x D                          |
| Traversing path                                 | 10 m                            |
| Traversing rate                                 | 3 m/s                           |
| Acceleration                                    | 10 m/s <sup>2</sup>             |
| Cable weight                                    | 231 kg/km                       |
| Outer sheath, material                          | PVC                             |
| Material conductor insulation                   | PVC                             |

## Power cable - SAC-5P- 5,0-500/M12FRL FE SH - 1414811

### Technical data

#### Cable

|                                 |                                                       |
|---------------------------------|-------------------------------------------------------|
| Conductor material              | Bare Cu litz wires                                    |
| Insulation resistance           | $\geq 100 \text{ M}\Omega \cdot \text{km}$ (at 20 °C) |
| Conductor resistance            | $\leq 8 \text{ }\Omega/\text{km}$ (at 20 °C)          |
| Nominal voltage, cable          | $\leq 300 \text{ V AC}$                               |
| Test voltage, cable             | $\geq 3000 \text{ V AC}$ (Spark test)                 |
| Flame resistance                | According to UL 758/1581 (Cable Flame)                |
|                                 | according to UL 758/1581 FT1                          |
|                                 | According to DIN EN 60332-1-2                         |
| Resistance to oil               | According to DIN EN 60811-404, 168 h at 60 °C         |
| Ambient temperature (operation) | -40 °C ... 80 °C (cable, fixed installation)          |
|                                 | -20 °C ... 80 °C (cable, flexible installation)       |


#### Environmental Product Compliance

|            |                                                                                                     |
|------------|-----------------------------------------------------------------------------------------------------|
| REACH SVHC | Lead 7439-92-1                                                                                      |
| China RoHS | Environmentally Friendly Use Period = 50 years                                                      |
|            | For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration" |

### Drawings

## Power cable - SAC-5P- 5,0-500/M12FRL FE SH - 1414811


Schematic diagram



Pin assignment of M12 socket, 5-pos., L-coded, socket side view

## Power cable - SAC-5P- 5,0-500/M12FRL FE SH - 1414811


Diagram



Current carrying capacity

## Power cable - SAC-5P- 5,0-500/M12FRL FE SH - 1414811


Dimensional drawing



M12 x 1 socket, angled

## Power cable - SAC-5P- 5,0-500/M12FRL FE SH - 1414811


Circuit diagram



Contact assignment of the M12 socket

## Power cable - SAC-5P- 5,0-500/M12FRL FE SH - 1414811

Cable cross section



PVC gray [500]

### Classifications

eCl@ss

|               |          |
|---------------|----------|
| eCl@ss 10.0.1 | 27440203 |
| eCl@ss 5.1    | 27061801 |
| eCl@ss 6.0    | 27279200 |
| eCl@ss 7.0    | 27279218 |
| eCl@ss 8.0    | 27440203 |
| eCl@ss 9.0    | 27440203 |

ETIM

|          |          |
|----------|----------|
| ETIM 3.0 | EC002061 |
| ETIM 4.0 | EC001855 |

# Power cable - SAC-5P- 5,0-500/M12FRL FE SH - 1414811

## Classifications

### ETIM

|          |          |
|----------|----------|
| ETIM 5.0 | EC002311 |
| ETIM 6.0 | EC002311 |
| ETIM 7.0 | EC002311 |

## Approvals

### Approvals

#### Approvals

UL Listed / cUL Listed / EAC-RoHS / EAC / cULus Listed

#### Ex Approvals

## Approval details

|                    |                                                                                     |                                                                                                                                                       |         |
|--------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------|---------|
| UL Listed          |  | <a href="http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm">http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm</a> | E468743 |
|                    |                                                                                     |                                                                                                                                                       |         |
| Nominal voltage UN | 63 V                                                                                |                                                                                                                                                       |         |
| Nominal current IN | 16 A                                                                                |                                                                                                                                                       |         |
| mm²/AWG/kcmil      | 14                                                                                  |                                                                                                                                                       |         |

|                    |  |                                                                                     |                                                                                                                                                       |         |
|--------------------|--|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------|---------|
| cUL Listed         |  |  | <a href="http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm">http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm</a> | E468743 |
|                    |  |                                                                                     |                                                                                                                                                       |         |
| Nominal voltage UN |  | 63 V                                                                                |                                                                                                                                                       |         |
| Nominal current IN |  | 16 A                                                                                |                                                                                                                                                       |         |
| mm²/AWG/kcmil      |  | 14                                                                                  |                                                                                                                                                       |         |

|          |                                                                                     |                          |
|----------|-------------------------------------------------------------------------------------|--------------------------|
| EAC-RoHS |  | RU D-<br>DE.HB35.B.00387 |
|----------|-------------------------------------------------------------------------------------|--------------------------|

|     |                                                                                     |                          |
|-----|-------------------------------------------------------------------------------------|--------------------------|
| EAC |  | RU C-<br>DE.BL08.B.00286 |
|-----|-------------------------------------------------------------------------------------|--------------------------|

## Power cable - SAC-5P- 5,0-500/M12FRL FE SH - 1414811

### Approvals

cULus Listed



### Accessories

#### Accessories

#### Screwdriver tools

Tool - SAC BIT M12-D16 - 1200305



Nut for assembling sensor/actuator cables with M12 connector and M12 connectors for assembly, knurl diameter: 16 mm, for 4 mm hexagonal drive

Screw plug - PROT M12 MS PWR - 1092802



An M12 screw plug for the unoccupied M12 females of the M12 POWER connectors, boxes, and flush-type connectors

Phoenix Contact 2020 © - all rights reserved  
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG  
Flachsmarktstr. 8  
32825 Blomberg  
Germany  
Tel. +49 5235 300  
Fax +49 5235 3 41200  
<http://www.phoenixcontact.com>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Phoenix Contact:

1414811