

Conductor connectors - Q 0,75/4IDC/18-18KU-KU BK - 1642140

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Conductor connectors, QUICKON connection, number of positions: 4, 0.34 mm² ... 0.75 mm², 250 V, 9 A, black, cable diameter range: 4 mm ... 8 mm, QUICKON fast connection

Your advantages

- ✓ Innovative and time saving - QUICKON fast connection for time saving of up to 80 % for on-site connection
- ✓ Convenient: quick and easy assembly without special tools
- ✓ Robust throughout: housing with IP68/IP69K and IK07 protection for a wide range of applications
- ✓ Safer connection thanks to polarization against mismatching and touch-proof protection according to DIN EN 0105
- ✓ Easy and safe - with the cable connector, you can repair or extend cables quickly, in combination with the connector as well as the coupling connection

RoHS

Key Commercial Data

Packing unit	1 pc
GTIN	 4 017918 923891
GTIN	4017918923891

Technical data

General

Color	black
Locking type	without
Connection method	QUICKON connection
	IDC connection
Number of positions	4
Wrench size, union nut	15 mm
Tightening torque, union nut	1.2 Nm
Wrench size, contact carrier	15 mm
Number of connections	4
Conductor cross section flexible min.	0.34 mm ²
Conductor cross section flexible max.	0.75 mm ²

Conductor connectors - Q 0,75/4IDC/18-18KU-KU BK - 1642140

Technical data

General

Conductor cross section solid min.	0.34 mm ²
Conductor cross section solid max.	0.5 mm ²
Conductor cross section AWG min.	22
Conductor cross section AWG max.	18

Cabel

Structure of individual litz in acc. with VDE 0295 / smallest wire diameter	VDE 0295 class 1 to 6/min. 0.15 mm
Wire insulation material	PVC / PE / PP / rubber
Wire diameter including insulation	1.3 mm ... 2.6 mm
External cable diameter	4 mm ... 8 mm
Position marking	1, 2, 3, 4

Ambient conditions

Degree of protection	IP65
	IP67
Ambient temperature (operation)	-40 °C ... 80 °C
Ambient temperature (storage/transport)	-40 °C ... 80 °C
Temperature when conductor connected	-5 °C ... 50 °C

Electrical characteristics

Nominal current I _N	9 A
Nominal voltage U _N	400 V AC
	400 V DC
Rated current	9 A
Rated voltage (III/3)	250 V
Rated voltage (III/2)	400 V
Rated voltage (II/2)	500 V
Rated surge voltage (III/3)	4 kV
Rated surge voltage (III/2)	4 kV
Rated surge voltage (II/2)	4 kV

Mechanical characteristics

QUICKON connectability	max. 10
Impact category	3
Category of shock impact	IK06

Material data

Contact material	Steel
Contact surface material	Tin-plated
Contact carrier material	PA
Insulating material	PA
Flammability rating according to UL 94	V0
Overvoltage category	III

Conductor connectors - Q 0,75/4IDC/18-18KU-KU BK - 1642140

Technical data

Material data

Degree of pollution	3
---------------------	---


Standards and Regulations

Category of shock impact	IK06
Connection in acc. with standard	CUL
Flammability rating according to UL 94	V0

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Drawings



Classifications

eCI@ss

eCI@ss 10.0.1	27440605
---------------	----------

Conductor connectors - Q 0,75/4IDC/18-18KU-KU BK - 1642140

Classifications

eCl@ss

eCl@ss 4.0	27140800
eCl@ss 4.1	27140800
eCl@ss 5.0	27143400
eCl@ss 5.1	27143400
eCl@ss 6.0	27143400
eCl@ss 7.0	27440605
eCl@ss 8.0	27440605
eCl@ss 9.0	27440605

ETIM

ETIM 2.0	EC000516
ETIM 3.0	EC000516
ETIM 4.0	EC000516
ETIM 5.0	EC002560
ETIM 6.0	EC002560
ETIM 7.0	EC002560

UNSPSC

UNSPSC 6.01	30211923
UNSPSC 7.0901	39121522
UNSPSC 11	39121522
UNSPSC 12.01	39121522
UNSPSC 13.2	39121402
UNSPSC 18.0	39121402
UNSPSC 19.0	39121402
UNSPSC 20.0	39121402
UNSPSC 21.0	39121402

Approvals

Approvals

Approvals

UL Recognized / cUL Recognized / VDE Zeichengenehmigung / EAC / EAC / EAC / EAC / cULus Recognized

Ex Approvals

Approval details

Conductor connectors - Q 0,75/4IDC/18-18KU-KU BK - 1642140

Approvals

UL Recognized			http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	FILE E 118976
Nominal voltage UN		250 V		
Nominal current IN		9 A		

cUL Recognized			http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	FILE E 118976
Nominal voltage UN		250 V		
Nominal current IN		6 A		

VDE Zeichengenehmigung		http://www2.vde.com/de/Institut/Online-Service/VDE-gepruefteProdukte/Seiten/Online-Suche.aspx	40030930
Nominal voltage UN	400 V		

EAC		RU C- DE.AI30.B.01102	
-----	---	--------------------------	--

EAC		EAC-Zulassung	
-----	---	---------------	--

EAC		RU C- DE.A*30.B.01102	
-----	---	--------------------------	--

EAC		RU C- DE.BL08.B.00511	
-----	---	--------------------------	--

cULus Recognized			
------------------	---	--	--

Conductor connectors - Q 0,75/4IDC/18-18KU-KU BK - 1642140

Accessories

Accessories

Electronics pliers

Diagonal cutter - MICROFOX-SB - 1212489



Electronic diagonal cutter, round head, without chamfer, with opening spring, mirror-polished and oiled, 2-component grip, cutting capacity: soft 0.2 - 2.0 mm; medium hard 1.2 mm; hard 0.5 mm diameter

Sealing plugs

Closing cap - SEALING PLUG 8X16 RD - 1400257



Closing cap, material: PA, color: red

Socket spanner

Socket wrench - QSS 15 - 1641992



Allen wrench, for loosening and fastening the QUICKON union nut, WAF 15 mm

Stripping tool

Stripping tool - WIREFOX SAC - 1212623



Stripping pliers, for halogen-free sensor/actuator cables (SAC cables), with PUR and PVC insulation, from Ø of 4.4 to 7 mm, any stripping length

Stripping tool - WIREFOX-D 16 - 1212173



Stripping tool, for stripping lines (specially for fiber optics lines) of Ø 4 - 16 mm

Conductor connectors - Q 0,75/4IDC/18-18KU-KU BK - 1642140

Accessories

Stripping tool - WIREFOX-D 40 - 1212161



Stripping tool, for stripping cables of 4.5 mm - 40 mm-Ø, insulation thickness of up to 4.5 mm, pivoting blade for round, lengthwise, and spiral cuts

Phoenix Contact 2020 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[1642140](#)