

## Bus system cable - SAC-5P-10,0-920/M12FS - 1507492

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Bus system cable, CANopen®, DeviceNet™, 5-position, PUR halogen-free, violet RAL 4001, shielded, free cable end, on Socket straight M12, coding: A, cable length: 10 m



DeviceNet CANopen

### Key Commercial Data

|              |                                                                                                         |
|--------------|---------------------------------------------------------------------------------------------------------|
| Packing unit | 1 pc                                                                                                    |
| GTIN         | <br>4 017918 900298 |
| GTIN         | 4017918900298                                                                                           |

### Technical data

#### Dimensions

|                                            |       |
|--------------------------------------------|-------|
| Length of cable                            | 10 m  |
| Stripping length of the free conductor end | 50 mm |

#### Ambient conditions

|                                 |                                  |
|---------------------------------|----------------------------------|
| Ambient temperature (operation) | -25 °C ... 90 °C (Plug / socket) |
| Degree of protection            | IP65                             |
|                                 | IP67                             |

#### General

|                       |                                                                                      |
|-----------------------|--------------------------------------------------------------------------------------|
| Note                  | Further products with variable cable lengths can be found in the accessories section |
| Rated current at 40°C | 4 A                                                                                  |
| Rated voltage         | 48 V AC                                                                              |
|                       | 60 V DC                                                                              |
| Number of positions   | 5                                                                                    |
| Insulation resistance | ≥ 100 MΩ                                                                             |
| Coding                | A - standard                                                                         |
| Signal type/category  | CANopen®                                                                             |
|                       | DeviceNet™                                                                           |

# Bus system cable - SAC-5P-10,0-920/M12FS - 1507492

## Technical data

### General

|                             |                        |
|-----------------------------|------------------------|
| Status display              | No                     |
| Overvoltage category        | II                     |
| Degree of pollution         | 3                      |
| Insertion/withdrawal cycles | ≥ 100                  |
| Torque                      | 0.4 Nm (M12 connector) |

### Material

|                                        |                                             |
|----------------------------------------|---------------------------------------------|
| Flammability rating according to UL 94 | HB                                          |
| Contact material                       | CuSn                                        |
| Contact surface material               | Ni/Au                                       |
| Contact carrier material               | TPU GF                                      |
| Material of grip body                  | TPU, hardly inflammable, self-extinguishing |
| Material, knurls                       | Zinc die-cast, nickel-plated                |
| Sealing material                       | NBR                                         |

### Pin assignment

|                                                           |                          |
|-----------------------------------------------------------|--------------------------|
| Contact   Color (signal designation)   Contact (optional) | 1 (Socket)   SR (shield) |
|                                                           | 2 (Socket)   RD (V+)     |
|                                                           | 3 (Socket)   BK (V-)     |
|                                                           | 4 (Socket)   WH (CAN_H)  |
|                                                           | 5 (Socket)   BU (CAN_L)  |

### Standards and Regulations

|                                        |    |
|----------------------------------------|----|
| Flammability rating according to UL 94 | HB |
|----------------------------------------|----|

### Cable

|                                     |                                                            |
|-------------------------------------|------------------------------------------------------------|
| Cable type                          | CANopen <sup>®</sup> /DeviceNet <sup>™</sup> , PUR, violet |
| Cable type (abbreviation)           | 920                                                        |
| UL AWM style                        | 21198 (80°C/300 V)                                         |
| Cable structure                     | 2xAWG24/19+2xAWG22/19                                      |
| Conductor cross section             | 2x 0.25 mm <sup>2</sup> (Data cable)                       |
|                                     | 2x 0.34 mm <sup>2</sup> (Power supply)                     |
|                                     | 1x 0.34 mm <sup>2</sup> (Drain wire)                       |
| AWG signal line                     | 24                                                         |
| AWG power supply                    | 22                                                         |
| Conductor structure signal line     | 19x 0.13 mm                                                |
| Conductor structure, voltage supply | 19x 0.15 mm                                                |
| Core diameter including insulation  | 1.95 mm ±0.05 mm (Data cable)                              |
|                                     | 1.4 mm ±0.05 mm (Power supply)                             |
| Wire colors                         | Red-black, blue-white                                      |
| Twisted pairs                       | 2 cores to the pair                                        |
| Type of pair shielding              | Plastic-coated aluminum foil, aluminum side outside        |
| Overall twist                       | 2 pairs around a drain wire in the center to the core      |

# Bus system cable - SAC-5P-10,0-920/M12FS - 1507492

## Technical data

### Cable

|                                                 |                                                                    |
|-------------------------------------------------|--------------------------------------------------------------------|
| Shielding                                       | Tinned copper braided shield                                       |
| Optical shield covering                         | 80 %                                                               |
| External sheath, color                          | violet RAL 4001                                                    |
| External cable diameter D                       | 6.7 mm $\pm$ 0.3 mm                                                |
| Minimum bending radius, fixed installation      | 5 x D                                                              |
| Minimum bending radius, flexible installation   | 10 x D                                                             |
| Number of bending cycles                        | 5000000                                                            |
| Bending radius                                  | 70 mm                                                              |
| Minimum bending radius, drag chain applications | 10 x D                                                             |
| Traversing path                                 | 4.5 m                                                              |
| Traversing rate                                 | 3 m/s                                                              |
| Acceleration                                    | 3 m/s <sup>2</sup>                                                 |
| Cable weight                                    | 90 kg/km                                                           |
| Outer sheath, material                          | PUR                                                                |
| Material conductor insulation                   | Foamed PE (Data cable)                                             |
|                                                 | PE (Power supply)                                                  |
| Conductor material                              | Tin-plated Cu litz wires                                           |
| Insulation resistance                           | $\geq 5 \text{ G}\Omega \cdot \text{km}$ (Data cable)              |
|                                                 | $\geq 5 \text{ G}\Omega \cdot \text{km}$ (Power supply)            |
| Loop resistance                                 | $\leq 181.80 \text{ }\Omega/\text{km}$ (Data cable)                |
|                                                 | $\leq 114.80 \text{ }\Omega/\text{km}$ (Power supply)              |
| Cable capacity                                  | nom. 40 nF/km (Data cable)                                         |
| Wave impedance                                  | 120 $\Omega \pm 10 \%$ (with 1 MHz)                                |
| Attenuation                                     | $\leq 22.9 \text{ dB/km}$ (with 1 MHz)                             |
|                                                 | $\leq 16.4 \text{ dB/km}$ (At 500 kHz)                             |
|                                                 | $\leq 9.5 \text{ dB/km}$ (At 125 kHz)                              |
| Nominal voltage, cable                          | $\leq 300 \text{ V}$ (Peak value, not for high-power applications) |
| Test voltage Core/Core                          | 2000 V (50 Hz, 1 min.)                                             |
| Test voltage Core/Shield                        | 2000 V (50 Hz, 1 min.)                                             |
| Flame resistance                                | UL 1581, Sec. 1060 (FT-1)                                          |
|                                                 | IEC 60332-1                                                        |
|                                                 | in accordance with ISO 6722-1 5.22 (UN ECE-R 118.01)               |
| Halogen-free                                    | in accordance with DIN VDE 0472 part 815                           |
|                                                 | according to IEC 60754-1                                           |
| Other resistance                                | Low adhesion                                                       |
| Ambient temperature (operation)                 | -40 °C ... 80 °C (cable, fixed installation)                       |
|                                                 | -20 °C ... 80 °C (cable, flexible installation)                    |

### Environmental Product Compliance

|            |                                                         |
|------------|---------------------------------------------------------|
| China RoHS | Environmentally friendly use period: unlimited = EFUP-e |
|------------|---------------------------------------------------------|

## Bus system cable - SAC-5P-10,0-920/M12FS - 1507492


### Technical data

#### Environmental Product Compliance

|  |                                                |
|--|------------------------------------------------|
|  | No hazardous substances above threshold values |
|--|------------------------------------------------|


### Drawings

Dimensional drawing



M12 x 1 socket, straight, shielded


Circuit diagram



Contact assignment of the M12 socket

## Bus system cable - SAC-5P-10,0-920/M12FS - 1507492

Schematic diagram



Pin assignment M12 socket, 5-pos., A-coded, socket side view

## Bus system cable - SAC-5P-10,0-920/M12FS - 1507492

Cable cross section



CANopen<sup>®</sup>/DeviceNet<sup>™</sup>, PUR, violet [920]

### Classifications

eCl@ss

|               |          |
|---------------|----------|
| eCl@ss 10.0.1 | 27060308 |
| eCl@ss 4.0    | 27060300 |
| eCl@ss 4.1    | 27060300 |
| eCl@ss 5.0    | 27061800 |
| eCl@ss 5.1    | 27061800 |
| eCl@ss 6.0    | 27279200 |
| eCl@ss 7.0    | 27279218 |
| eCl@ss 8.0    | 27279218 |
| eCl@ss 9.0    | 27060308 |

## Bus system cable - SAC-5P-10,0-920/M12FS - 1507492

### Classifications

#### ETIM

|          |          |
|----------|----------|
| ETIM 2.0 | EC000830 |
| ETIM 3.0 | EC001855 |
| ETIM 4.0 | EC001855 |
| ETIM 5.0 | EC002599 |
| ETIM 6.0 | EC001262 |
| ETIM 7.0 | EC001262 |

#### UNSPSC

|               |          |
|---------------|----------|
| UNSPSC 6.01   | 31251501 |
| UNSPSC 7.0901 | 31251501 |
| UNSPSC 11     | 31251501 |
| UNSPSC 12.01  | 31251501 |
| UNSPSC 13.2   | 31251501 |
| UNSPSC 18.0   | 26121604 |
| UNSPSC 19.0   | 26121604 |
| UNSPSC 20.0   | 26121604 |
| UNSPSC 21.0   | 26121604 |

### Approvals

#### Approvals

#### Approvals

UL Listed / cUL Listed / EAC-RoHS / EAC / cULus Listed

#### Ex Approvals

### Approval details

|                    |                                                                                     |                                                                                                                                                       |               |
|--------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------|---------------|
| UL Listed          |  | <a href="http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm">http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm</a> | FILE E 221474 |
| Nominal voltage UN | 125 V                                                                               |                                                                                                                                                       |               |
| Nominal current IN | 4 A                                                                                 |                                                                                                                                                       |               |

## Bus system cable - SAC-5P-10,0-920/M12FS - 1507492

### Approvals

|                    |                                                                                   |                                                                                                                                                       |               |
|--------------------|-----------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------|---------------|
| cUL Listed         |  | <a href="http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm">http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm</a> | FILE E 221474 |
| Nominal voltage UN |                                                                                   | 125 V                                                                                                                                                 |               |
| Nominal current IN |                                                                                   | 4 A                                                                                                                                                   |               |

|          |                                                                                   |                          |
|----------|-----------------------------------------------------------------------------------|--------------------------|
| EAC-RoHS |  | RU D-<br>DE.HB35.B.00387 |
|----------|-----------------------------------------------------------------------------------|--------------------------|

|     |                                                                                   |               |
|-----|-----------------------------------------------------------------------------------|---------------|
| EAC |  | EAC-Zulassung |
|-----|-----------------------------------------------------------------------------------|---------------|

|              |                                                                                     |
|--------------|-------------------------------------------------------------------------------------|
| cULus Listed |  |
|--------------|-------------------------------------------------------------------------------------|

### Accessories

#### Accessories

Circular connector (cable-side)

Data connector - SACC-M12FS-5PL SH DN - 1424672



Data connector, CANopen<sup>®</sup>, DeviceNet<sup>™</sup>, 5-position, shielded, Socket straight M12, Coding: A, Push-in connection, knurl material: Zinc die-cast, nickel-plated, external cable diameter 4 mm ... 8 mm

Data connector - SACC-M12MS-5PL SH DN - 1424670



Data connector, CANopen<sup>®</sup>, DeviceNet<sup>™</sup>, 5-position, shielded, Plug straight M12, Coding: A, Push-in connection, knurl material: Zinc die-cast, nickel-plated, external cable diameter 4 mm ... 8 mm

## Bus system cable - SAC-5P-10,0-920/M12FS - 1507492

### Accessories

Data connector - SACC-M12FR-5PL SH DN - 1424673



Data connector, CANopen<sup>®</sup>, DeviceNet<sup>™</sup>, 5-position, shielded, Socket angled M12, Coding: A, Push-in connection, knurl material: Zinc die-cast, nickel-plated, external cable diameter 4 mm ... 8 mm

Data connector - SACC-M12MR-5PL SH DN - 1424671



Data connector, CANopen<sup>®</sup>, DeviceNet<sup>™</sup>, 5-position, shielded, Plug angled M12, Coding: A, Push-in connection, knurl material: Zinc die-cast, nickel-plated, external cable diameter 4 mm ... 8 mm

### Data cable preassembled

Bus system cable - SAC-5P-M12FS/920/... - 1538128



Bus system cable, CANopen<sup>®</sup>, DeviceNet<sup>™</sup>, 5-position, PUR halogen-free, violet RAL 4001, shielded, free cable end, on Socket straight M12, coding: A, cable length: Free input (0.2 ... 40.0 m)

Bus system cable - SAC-5P-M12MS/920/... - 1538102



Bus system cable, CANopen<sup>®</sup>, DeviceNet<sup>™</sup>, 5-position, PUR halogen-free, violet RAL 4001, shielded, Plug straight M12, coding: A, on free cable end, cable length: Free input (0.2 ... 40.0 m)

Bus system cable - SAC-5P-M12MS-M12FS/920/... - 1538144



Bus system cable, CANopen<sup>®</sup>, DeviceNet<sup>™</sup>, 5-position, PUR halogen-free, violet RAL 4001, shielded, Plug straight M12, coding: A, on Socket straight M12, coding: A, cable length: Free input (0.2 ... 40.0 m)

### H-distributor

## Bus system cable - SAC-5P-10,0-920/M12FS - 1507492

### Accessories

H distributor - SAC-5PH-M-F/2XF SH1 SCO - 1417414



H distributor, 5-position, shielded, Plug straight M12, coding: A, on Socket straight M12, coding: A and Socket straight M12, coding: A, Thread M12 not rotatable, Parallel distributor

---

### Plug for cable screw gland

Screw plug - PROT-M12 MS-PA-CHAIN - 1430899

M12 sealing cap with fixing band, for sensor cables, for free M12 sockets



---

### Safety locking

Locking clip - SAC-M12-EXCLIP-F - 1558991



Locking clip for the socket side of sensor/actuator cables with M12 connector and M12 connectors for assembly, for knurl diameter: 15 mm or for Allen key with a wrench size of 14 mm, prevents the disconnection of plug-in connections without tools

---

### Screwdriver tools

Adapter insert - TSD-M SAC-BIT ADAPTER - 1212600



Adapter bit for TSD-M...torque tools, E6.3-1/4" drive with 4 mm hexagon to accommodate SAC bits

---

Tool - SAC BIT M12-D15 - 1208432



Nut for assembling sensor/actuator cables with M12 connector and M12 connectors for assembly, with a knurl diameter of 15 mm, for 4 mm hexagonal drive

---

### T-distributor

## Bus system cable - SAC-5P-10,0-920/M12FS - 1507492

### Accessories

T distributor - SAC-5P-M12T/2XM12 VP - 1541186



T distributor, 5-position, unshielded, Plug straight M12, coding: A, on Socket straight M12, coding: A and Socket straight M12, coding: A, Parallel distributor

T distributor - SAC-5PT-F/F-M VP - 1424712



T distributor, CANopen<sup>®</sup>, DeviceNet<sup>™</sup>, 5-position, unshielded, Socket straight M12, coding: A, on Socket straight M12, coding: A and Plug straight M12, coding: A, Parallel distributor

### Terminal resistor

Termination resistor - SAC-5P-M12MS CAN TR - 1507816



Terminating resistor CANopen<sup>®</sup>/DeviceNet<sup>™</sup> M12

### Torque tool

Torque screwdriver - TSD 04 SAC - 1208429



Torque screwdriver, with preset torque of 0.4 Nm and 4 mm hexagonal drive for M12 connectors

Torque screwdriver - TSD-M 1,2NM - 1212224



Torque screw driver, accuracy as per EN ISO 6789 standard, adjustable from 0.3 - 1.2 Nm

## Bus system cable - SAC-5P-10,0-920/M12FS - 1507492

### Accessories

Data connector - SACC-FS-5QO SH DN SCO - 1422760



Data connector, CANopen<sup>®</sup>, DeviceNet<sup>™</sup>, 5-position, halogen-free, shielded, Socket straight M12 SPEEDCON, Coding: A, Insulation displacement connection, knurl material: Zinc die-cast, nickel-plated, external cable diameter 5 mm ... 9.7 mm

---

Data connector - SACC-MS-5QO SH DN SCO - 1422759



Data connector, CANopen<sup>®</sup>, DeviceNet<sup>™</sup>, 5-position, halogen-free, shielded, Plug straight M12 SPEEDCON, Coding: A, Insulation displacement connection, knurl material: Zinc die-cast, nickel-plated, external cable diameter 5 mm ... 9.7 mm

---

Phoenix Contact 2020 © - all rights reserved  
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG  
Flachsmarktstr. 8  
32825 Blomberg  
Germany  
Tel. +49 5235 300  
Fax +49 5235 3 41200  
<http://www.phoenixcontact.com>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[1507492](#)