

## SMD male connectors - FP 1,27/ 16-MV 3,25 - 1714925

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



SMD male connector, Nominal current at 20 °C: 1.4 A, Test voltage: 500 V AC, number of positions: 16, pitch: 1.27 mm, color: black, contact surface: Gold, mounting: SMD soldering

The figure shows a 12-pos. version with 12 contacts

### Your advantages

- ✓ Gold-plated contacts ensure transfer quality remains stable over the long term
- ✓ Compact, high-position board-to-board or wire-to-board connectors for space-saving device designs
- ✓ Stacked, coplanar or orthogonal PCB connections enable maximum flexibility in the device
- ✓ Male and female connectors of different height can be combined – for individual PCB spacing of 8 mm ... 13.8 mm



### Key Commercial Data

|                        |               |
|------------------------|---------------|
| Packing unit           | 280 pc        |
| Minimum order quantity | 280 pc        |
| GTIN                   |               |
| GTIN                   | 4055626403014 |

### Technical data

#### Item properties

|                           |                     |
|---------------------------|---------------------|
| Brief article description | SMD male connectors |
| Plug-in system            | FINEPITCH 1,27 mm   |
| Type of contact           | Male connector      |
| Range of articles         | FP 1,27/...-MV 3,25 |
| Pitch                     | 1.27 mm             |
| Number of positions       | 16                  |
| Mounting type             | SMD soldering       |
| Pin layout                | Linear pad geometry |
| Number of levels          | 2                   |
| Number of potentials      | 16                  |

## SMD male connectors - FP 1,27/ 16-MV 3,25 - 1714925

### Technical data

#### Electrical data

|                          |                                  |
|--------------------------|----------------------------------|
| Nominal current at 20 °C | 1.4 A (50-pos.)                  |
| Test voltage             | 500 V AC                         |
| Contact resistance       | ≤25 mΩ, (IEC 60512-2-1:2002-02)  |
| Insulation resistance    | ≥ 10 GΩ, (IEC 60512-3-1:2002-02) |

#### Material data - contact

|                                           |                                                                                   |
|-------------------------------------------|-----------------------------------------------------------------------------------|
| Note                                      | WEEE/RoHS-compliant, free of whiskers according to IEC 60068-2-82/ JEDEC JESD 201 |
| Contact material                          | Cu alloy                                                                          |
| Surface characteristics                   | Selective coating                                                                 |
| Metal surface contact area (top layer)    | Gold (Au)                                                                         |
| Metal surface contact area (middle layer) | Nickel (Ni), Palladium nickel (PdNi)                                              |

#### Material data - housing

|                                        |      |
|----------------------------------------|------|
| Insulating material                    | LCP  |
| Insulating material group              | IIIa |
| CTI according to IEC 60112             | 175  |
| Flammability rating according to UL 94 | V0   |

#### Dimensions for the product

|                             |          |
|-----------------------------|----------|
| Length [ l ]                | 7.2 mm   |
| Width [ w ]                 | 15.25 mm |
| Height [ h ]                | 8.95 mm  |
| Pitch                       | 1.27 mm  |
| Height (without solder pin) | 8.25 mm  |
| Pin spacing                 | 1.27 mm  |
| Coplanarity                 | ≤ 0.1 mm |

#### Dimensions for PCB design

|             |         |
|-------------|---------|
| Pin spacing | 1.27 mm |
|-------------|---------|

#### Dimensions for the application

|                   |                                                                                        |
|-------------------|----------------------------------------------------------------------------------------|
| Contact cover     | 0.9 mm                                                                                 |
| Overlap length    | 1.5 mm                                                                                 |
| Medium offset     | ± 0.7 mm in longitudinal and transverse direction                                      |
| Angular tolerance | ± 4 ° in longitudinal direction                                                        |
|                   | ± 2 ° in transverse direction                                                          |
| Stack height      | 9.5 mm Tolerance: +1,5 mm (in combination with Range of articles:FP 1,27/...-FV 6,25)  |
|                   | 12.3 mm Tolerance: +1,5 mm (in combination with Range of articles:FP 1,27/...-FV 9,05) |

#### Packaging information

|                    |                 |
|--------------------|-----------------|
| Type of packaging  | 32 mm wide tape |
| Pieces per package | 280             |

# SMD male connectors - FP 1,27/ 16-MV 3,25 - 1714925

## Technical data

### Packaging information

|                             |                                          |
|-----------------------------|------------------------------------------|
| Denomination packing units  | Pcs.                                     |
| [W] tape width              | 32 mm                                    |
| [A] coil diameter           | 330 mm                                   |
| [W2] coil overall dimension | 38.4 mm                                  |
| Outer packaging type        | Transparent-Bag                          |
| ESD level                   | (D) electrostatically conductive         |
| Specification               | DIN EN 61340-5-1 (VDE 0300-5-1): 2008-07 |

### General product information

|              |                                                                                                                                                                                                                      |
|--------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Type of note | Notes on operation                                                                                                                                                                                                   |
| Note         | The permissible voltage during operation depends on the application, taking into consideration the air clearances and creepage distances within the scope of insulation requirements in accordance with IEC 60664-1. |

### Processing notes

|                                           |                                        |
|-------------------------------------------|----------------------------------------|
| Process                                   | Reflow soldering                       |
| Specification                             | Following IPC/JEDEC J-STD-020E:2014-12 |
| Moisture Sensitive Level                  | MSL 1                                  |
| Classification temperature T <sub>c</sub> | 260 °C                                 |

### Ambient conditions

|                                         |                   |
|-----------------------------------------|-------------------|
| Ambient temperature (storage/transport) | -40 °C ... 70 °C  |
| Ambient temperature (assembly)          | -5 °C ... 100 °C  |
| Ambient temperature (operation)         | -55 °C ... 125 °C |

### Mechanical tests

|                                            |               |
|--------------------------------------------|---------------|
| Insertion and withdrawal force per contact | approx. 0.5 N |
|--------------------------------------------|---------------|

### Air clearances and creepage distances

|                                       |             |
|---------------------------------------|-------------|
| Air clearances and creepage distances | min. 0.4 mm |
|---------------------------------------|-------------|

### Current carrying capacity / derating curves

|                  |                                               |
|------------------|-----------------------------------------------|
| Caption          | Type: FP 1,27/...-FH with FP 1,27/...-MV 3,25 |
| Specification    | IEC 60512-5-2:2002-02                         |
| Reduction factor | 0.8                                           |
| Note             | max. 1.4 A at 20 °C (50-pos.)                 |

### Service life

|              |                                                      |
|--------------|------------------------------------------------------|
| Service life | 500 Insertion/withdrawal cycles, Performance level 1 |
|--------------|------------------------------------------------------|


### Environmental Product Compliance

|            |                                                         |
|------------|---------------------------------------------------------|
| China RoHS | Environmentally friendly use period: unlimited = EFUP-e |
|            | No hazardous substances above threshold values          |

## Drawings


## SMD male connectors - FP 1,27/ 16-MV 3,25 - 1714925

Diagram



Type: FP 1,27/...-FH with FP 1,27/...-MV 3,25


Diagram



Type: FP 1,27/...-FV 6,25 with FP 1,27/...-MV 3,25


## SMD male connectors - FP 1,27/ 16-MV 3,25 - 1714925

Diagram



Type: FP 1,27/...-FV 9,05 with FP 1,27/...-MV 3,25

Schematic diagram



### Classifications

eCl@ss

|               |          |
|---------------|----------|
| eCl@ss 10.0.1 | 27440402 |
| eCl@ss 4.0    | 27260700 |
| eCl@ss 4.1    | 27260700 |

## SMD male connectors - FP 1,27/ 16-MV 3,25 - 1714925

### Classifications

#### eCl@ss

|            |          |
|------------|----------|
| eCl@ss 5.0 | 27260700 |
| eCl@ss 5.1 | 27260700 |
| eCl@ss 6.0 | 27260700 |
| eCl@ss 7.0 | 27440402 |
| eCl@ss 8.0 | 27440402 |
| eCl@ss 9.0 | 27440402 |

#### ETIM

|          |          |
|----------|----------|
| ETIM 5.0 | EC002637 |
| ETIM 6.0 | EC002637 |
| ETIM 7.0 | EC002637 |

### Approvals

#### Approvals

#### Approvals

cULus Recognized / EAC

#### Ex Approvals

#### Approval details

|                  |                                                                                     |                                                                                                                                                                        |
|------------------|-------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| cULus Recognized |  | <a href="http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm">http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm</a> E118976-20170331 |
|------------------|-------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------|

|     |                                                                                     |         |
|-----|-------------------------------------------------------------------------------------|---------|
| EAC |  | B.01687 |
|-----|-------------------------------------------------------------------------------------|---------|

### Accessories

#### Additional products

SMD female connectors - FP 1,27/ 16-FV 9,05 - 1715000



SMD female connector, Nominal current at 20 °C: 1.4 A, Test voltage: 500 V AC, number of positions: 16, pitch: 1.27 mm, color: black, contact surface: Gold, mounting: SMD soldering

## SMD male connectors - FP 1,27/ 16-MV 3,25 - 1714925

### Accessories

#### SMD female connectors - FP 1,27/ 16-FV 6,25 - 1714892



SMD female connector, Nominal current at 20 °C: 1.4 A, Test voltage: 500 V AC, number of positions: 16, pitch: 1.27 mm, color: black, contact surface: Gold, mounting: SMD soldering

---

#### SMD female connectors - FP 1,27/ 16-FH - 1714871



SMD female connector, Nominal current at 20 °C: 1.4 A, Test voltage: 500 V AC, number of positions: 16, pitch: 1.27 mm, color: black, contact surface: Gold, mounting: SMD soldering

---


#### IDC female connectors - FP 1,27/ 16-FWL - 1714903



IDC female connector, Nominal current at 20 °C: 1.2 A, Test voltage: 500 V AC, number of positions: 16, pitch: 1.27 mm, color: black, contact surface: Gold

---

#### Preassembled IDC female connector - FP 1,27/ 16-FWL-10/.../... - 1010258



Assembled IDC female connector, rated current: 1.2 A, cable length: Free input (0.05 ... 0.95 m), Cable type: Flat-ribbon conductor, Flat-ribbon conductor

---

#### Preassembled IDC female connector - FP 1,27/ 16-FWL-11/.../... - 1010251



Assembled IDC female connector, rated current: 1.2 A, cable length: Free input (0.05 ... 0.95 m), Cable type: Flat-ribbon conductor, Flat-ribbon conductor

## SMD male connectors - FP 1,27/ 16-MV 3,25 - 1714925

### Accessories


Preassembled IDC female connector - FP 1,27/ 16-FWL-12/.../... - 1010241



Assembled IDC female connector, rated current: 1.2 A, cable length: Free input (0.05 ... 0.95 m), Cable type: Flat-ribbon conductor, Flat-ribbon conductor

---

Preassembled IDC female connector - FP 1,27/ 16-FWL-20/.../... - 1010232



Assembled IDC female connector, rated current: 1.2 A, cable length: Free input (0.05 ... 0.95 m), Cable type: Flat-ribbon conductor, Flat-ribbon conductor

---

Preassembled IDC female connector - FP 1,27/ 16-FWL-21/.../... - 1010215



Assembled IDC female connector, rated current: 1.2 A, cable length: Free input (0.05 ... 0.95 m), Cable type: Flat-ribbon conductor, Flat-ribbon conductor

---

Phoenix Contact 2020 © - all rights reserved  
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG  
Flachsmarktstr. 8  
32825 Blomberg  
Germany  
Tel. +49 5235 300  
Fax +49 5235 3 41200  
<http://www.phoenixcontact.com>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[1714925](#)