

## Cable connector - CA-07S1N1280DN - 1619772

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Cable connector, CA, straight, shielded: yes, Screw locking, M23, No. of pos.: 7, type of contact: Socket, Solder connection, cable diameter range: 3 mm ... 14.5 mm

The figure shows the 6-pos. product version

### Your advantages

- ✓ Safe use in the field, thanks to high degree of protection
- ✓ Connector for flexible on-site assembly
- ✓ Consistent EMC protection for reliable transmission of signals
- ✓ Solder connection: proven connection technology for various litz wires

RoHS

### Key Commercial Data

|              |                                                                                                         |
|--------------|---------------------------------------------------------------------------------------------------------|
| Packing unit | 1 pc                                                                                                    |
| GTIN         | <br>4 046356 821452 |
| GTIN         | 4046356821452                                                                                           |

### Technical data

#### Temperature range

|                     |                   |
|---------------------|-------------------|
| Ambient temperature | -40 °C ... 125 °C |
|---------------------|-------------------|

#### Data of the insulating body

|                                        |                   |
|----------------------------------------|-------------------|
| Coding                                 | N                 |
| Insulator material                     | PBT               |
| Contact material                       | CuZn              |
| Contact surface material               | Ni/Au             |
| Insertion/withdrawal cycles mechanical | 100               |
| Contact connection method              | Solder connection |
| Type of contacts                       | Socket            |
| Application                            | Signal            |
| Number of positions                    | 7                 |

## Cable connector - CA-07S1N1280DN - 1619772

### Technical data

#### Data of the insulating body

|                                                 |                     |
|-------------------------------------------------|---------------------|
| Direction of rotation                           | Standard            |
| Contact diameter of signal contacts             | 2 mm                |
| Litz wire cross section of signal contacts max. | 2.5 mm <sup>2</sup> |
| Nominal current per signal contact              | 20 A                |
| Rated voltage of signal contact                 | 300 V               |
| Rated surge voltage                             | 2.5 kV              |
| Overvoltage category                            | II                  |
| Degree of pollution                             | 3                   |

#### Housing data

|                                        |                                                                      |
|----------------------------------------|----------------------------------------------------------------------|
| Housing material                       | Turned parts: copper zinc alloy (CuZn), die-cast parts: zinc (GD-Zn) |
| Type of locking                        | Screw locking                                                        |
| Degree of protection (when plugged in) | IP67                                                                 |
| Thread type                            | M23                                                                  |

#### Cable seal data

|                  |                  |
|------------------|------------------|
| Cable diameter   | 3 mm ... 14.5 mm |
| Sealing material | NBR              |


#### Environmental Product Compliance

|            |                                                                                                     |
|------------|-----------------------------------------------------------------------------------------------------|
| REACH SVHC | Lead 7439-92-1                                                                                      |
| China RoHS | Environmentally Friendly Use Period = 50 years                                                      |
|            | For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration" |

### Drawings

## Cable connector - CA-07S1N1280DN - 1619772

Schematic diagram



## Cable connector - CA-07S1N1280DN - 1619772

Dimensional drawing



### Classifications

#### eCl@ss

|               |          |
|---------------|----------|
| eCl@ss 10.0.1 | 27440102 |
| eCl@ss 4.0    | 27260700 |
| eCl@ss 4.1    | 27260700 |
| eCl@ss 5.0    | 27260700 |
| eCl@ss 5.1    | 27260700 |
| eCl@ss 6.0    | 27260700 |
| eCl@ss 7.0    | 27440102 |
| eCl@ss 8.0    | 27440102 |
| eCl@ss 9.0    | 27440102 |

#### ETIM

|          |          |
|----------|----------|
| ETIM 3.0 | EC001121 |
| ETIM 4.0 | EC002635 |
| ETIM 5.0 | EC002635 |
| ETIM 6.0 | EC002061 |

#### UNSPSC

|               |          |
|---------------|----------|
| UNSPSC 6.01   | 43172015 |
| UNSPSC 7.0901 | 43201404 |
| UNSPSC 11     | 43172015 |
| UNSPSC 12.01  | 43201404 |
| UNSPSC 13.2   | 39121413 |
| UNSPSC 18.0   | 39121413 |
| UNSPSC 19.0   | 39121413 |

## Cable connector - CA-07S1N1280DN - 1619772

### Classifications

#### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 20.0 | 39121413 |
| UNSPSC 21.0 | 39121413 |

### Approvals

#### Approvals

#### Approvals

UL Recognized / cUL Recognized / EAC / cULus Recognized

#### Ex Approvals

### Approval details

|                    |                                                                                     |                                                                                                                                                                        |
|--------------------|-------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| UL Recognized      |  | <a href="http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm">http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm</a> E335019-20141210 |
|                    |                                                                                     |                                                                                                                                                                        |
| Nominal voltage UN | 300 V                                                                               |                                                                                                                                                                        |
| Nominal current IN | 20 A                                                                                |                                                                                                                                                                        |
| mm²/AWG/kcmil      | 14                                                                                  |                                                                                                                                                                        |

|                    |                                                                                     |                                                                                                                                                                        |
|--------------------|-------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| cUL Recognized     |  | <a href="http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm">http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm</a> E335019-20141210 |
|                    |                                                                                     |                                                                                                                                                                        |
| Nominal voltage UN | 300 V                                                                               |                                                                                                                                                                        |
| Nominal current IN | 10 A                                                                                |                                                                                                                                                                        |
| mm²/AWG/kcmil      | 14                                                                                  |                                                                                                                                                                        |

|     |                                                                                     |         |
|-----|-------------------------------------------------------------------------------------|---------|
| EAC |  | B.01687 |
|-----|-------------------------------------------------------------------------------------|---------|

|                  |                                                                                     |
|------------------|-------------------------------------------------------------------------------------|
| cULus Recognized |  |
|------------------|-------------------------------------------------------------------------------------|

### Accessories

#### Accessories

## Cable connector - CA-07S1N1280DN - 1619772

### Accessories

Circular connectors (device side)

Hook wrench - SF-Z0027 - 1607455



Hook wrench

---

### Mounting material

Torque screwdriver - SF-Z0028 - 1607456



Torque screwdriver

---

Color-coding - RF-Z0014 - 1620588



Color-coding, color: green

---

Color-coding - RF-Z0015 - 1620592



Color-coding, color: orange

---

Color-coding - RF-Z0016 - 1620593



Color-coding, color: black

## Cable connector - CA-07S1N1280DN - 1619772

### Accessories

Square mounting flange - RF-Z0003 - 1607905



Square mounting flange, Axial seal, 4xM3, flange dimensions: 35 mm x 35 mm

---

### Protective cover

Protective cap - RC-Z2058 - 1604223



Plastic protection cap for connectors with M23 knurled nut

---

Plastic anti-static dust protection cap - RC-Z2468 - 1611796



Plastic protection cap, antistatic, for connectors with M23 knurled nut

---

Metal protective cap - CA-Z0077 - 1627224



Metal protection cap with steel wire and loop, for M23 signal connectors with knurled nut for fastening to the cable

---

Phoenix Contact 2020 © - all rights reserved  
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG  
Flachsmarktstr. 8  
32825 Blomberg  
Germany  
Tel. +49 5235 300  
Fax +49 5235 3 41200  
<http://www.phoenixcontact.com>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[1619772](#)