

Electronic housing - DCS 5,7 L 1F R W C 7035 - 2203176

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Display housing, 5.7", light gray, consisting of two half shells with screws, window on the left. Front 1.1 mm recessed, keypad area on the right recessed for wall installation

Your advantages

- ✓ Display housings for mobile and stationary operator panels
- ✓ Integration of TFT display and membrane keypads
- ✓ Degree of protection: up to IP54
- ✓ Temperature range: -20°C to +50°C
- ✓ Shock-resistant ABS plastic
- ✓ Flammability rating UL 94-V0



Key Commercial Data

Packing unit	2 pc
GTIN	 4 055626 378329
GTIN	4055626378329

Technical data

Item properties

Type	DCS 5,7 L 1F R W C 7035
Order No.	2203176
Housing type	Display housing
Max. IP code to attain	IP54
Mounting type	Wall mounting (with accessories as an option)
Battery compartment	for APP battery housing
Wall fastening	yes
Ventilation openings present	no

Measurements

Width [w]	224 mm
-------------	--------

Electronic housing - DCS 5,7 L 1F R W C 7035 - 2203176

Technical data

Measurements

Height [h]	157 mm
Depth [d]	40 mm
Diagonal	5.7 in. (Window for display)
Dimensions	118 mm x 88 mm (Window for display, left position)
	44 mm x 104.8 mm (recessed area on the front, right position for membrane keypad)
	28.5 mm x 3.5 mm (Opening for the membrane keypad cable)

Material specifications

Color (RAL)	light gray (7035)
Flammability rating according to UL 94	V0
Housing material	ABS

Packaging information

Pieces per package	2
Denomination packing units	Pcs.


Standards and regulations

Flammability rating according to UL 94	V0
--	----

Drawings

Electronic housing - DCS 5,7 L 1F R W C 7035 - 2203176

Dimensional drawing



Classifications

eCl@ss

eCl@ss 10.0.1	27182702
eCl@ss 5.1	27180506
eCl@ss 6.0	27180800
eCl@ss 7.0	27182702
eCl@ss 8.0	27182702
eCl@ss 9.0	27182702

ETIM

ETIM 5.0	EC001031
ETIM 6.0	EC001031

Electronic housing - DCS 5,7 L 1F R W C 7035 - 2203176

Classifications

ETIM

ETIM 7.0	EC001031
----------	----------

Accessories

Accessories

Screwdriver tools

Philips screwdriver - SF-PH 0-60 - 1212558



Screwdriver, PH crosshead, size: PH 0 x 60, 2-component grip, with non-slip grip

Additional products

Seal - DCS 5,7-7,0 SEAL - 2203584



Sealing set, including cord and O-rings

Display - D L 5,7 QVGA P - 2203549



Graphic LCD module, 5.7", 320 x 240 pixels, FSTN transmissive/negative 12:00, LED backlight, interface: parallel, operating temperature: -20 °C ... 70 °C

Mounting set - DCS D-FIX 5,7 - 2203829



Mounting set including plates and screws, for display mounting

Electronic housing - DCS 5,7 L 1F R W C 7035 - 2203176

Accessories

Seal - DCS D-SEAL 3,0MM - 2203749



Sealing strip, self-adhesive, for displays of the DCS housing series (roll: 100 m)

Washer/ring - DCS 5,7 WIN 1,5 CLEAR - 2203595



Acrylic glass, satin-finished, for housing DCS 5.7

Wall bracket - DCS 5,7-7,0 WALL MOUNT 7035 - 2203752



Wall bracket for housing

Membrane keypad - KP DCS 4,8-6,4 K6 C4 P7 - 2203572



Membrane keypad, self-adhesive, silver conduction technology, 6 keys, embossed, 4 colors, connection cable: 50 mm, operating temperature -20°C ... 70°C

Phoenix Contact 2020 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Phoenix Contact:

2203176