

MKKDS 1,5/ 3-5,08 BD:NC-GND - 1715227

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

PCB terminal block, pitch: 5.08 mm, number of positions: 3, color: green, Pin layout: Linear pinning, Solder pin [P]: 3.5 mm



Key Commercial Data

Packing unit	100 pc
Minimum order quantity	100 pc
GTIN	 4 055626 612249
GTIN	4055626612249

Technical data

Item properties

Number of positions	3
Pin layout	Linear pinning

Material data - housing

Housing color	green (6021)
---------------	--------------

Dimensions for the product

Length [l]	21.4 mm
Width [w]	17.78 mm
Height [h]	29.5 mm
Pitch	5.08 mm
Height (without solder pin)	26 mm
Solder pin [P]	3.5 mm

Dimensions for PCB design

Hole diameter	1.3 mm
---------------	--------

Packaging information

Type of packaging	packed in cardboard
Pieces per package	100
Denomination packing units	Pcs.

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

MKKDS 1,5/ 3-5,08 BD:NC-GND - 1715227

Technical data

Environmental Product Compliance

China RoHS	Environmentally Friendly Use Period = 50 years
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

Classifications

eCl@ss

eCl@ss 10.0.1	27440401
eCl@ss 5.1	27261100
eCl@ss 6.0	27261100
eCl@ss 7.0	27440401
eCl@ss 8.0	27440401
eCl@ss 9.0	27440401

ETIM

ETIM 5.0	EC002643
ETIM 6.0	EC002643
ETIM 7.0	EC002643

Approvals

Approvals

Approvals

EAC / UL Recognized / cUL Recognized / SEV / IECCEB Scheme / cULus Recognized

Ex Approvals

Approval details

EAC		B.01687
-----	---	---------

UL Recognized		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	FILE E 60425
	B	D	
Nominal voltage UN	125 V	300 V	
Nominal current IN	10 A	10 A	

MKKDS 1,5/ 3-5,08 BD:NC-GND - 1715227

Approvals

	B	D
mm²/AWG/kcmil	30-14	30-14

cUL Recognized				http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	FILE E 60425
	B	D			
Nominal voltage UN	125 V	300 V			
Nominal current IN	10 A	10 A			
mm²/AWG/kcmil	30-14	30-14			

SEV		https://www.eurofins.ch/de/	IK-4497
Nominal voltage UN	250 V		
Nominal current IN	24 A		
mm²/AWG/kcmil	2.5		

IECEE CB Scheme			http://www.iecee.org/	CH-10787
Nominal voltage UN		250 V		
Nominal current IN		24 A		
mm²/AWG/kcmil		2.5		

cULus Recognized	
------------------	---

Phoenix Contact 2020 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
 Flachsmarktstr. 8
 32825 Blomberg
 Germany
 Tel. +49 5235 300
 Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[1715227](#)