

FO cable - FL FOC PN-B-980/1000 - 2313397

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



PROFINET polymer fiber cable, duplex 980 µm/1000 µm, heavy-weight design, for installation in stationary systems and machines, by the meter, without male connector

Your advantages

- ✓ Universal installation cable for installation in stationary systems and machines
- ✓ For indoors
- ✓ 2.2 mm individual wires made from extremely hard-wearing polyamide (PA)
- ✓ Rugged polyurethane (PUR) outer sheath
- ✓ PROFINET type B
- ✓ Halogen-free, ozone, and UV resistant



Ethernet
#5000

Key Commercial Data

Packing unit	1 M
GTIN	 4 046356 418515
GTIN	4046356418515

Technical data

Mechanical characteristics

Weight	51.74 g
--------	---------

Ambient conditions

Ambient temperature (operation)	-20 °C ... 70 °C
	-20 °C ... 70 °C (with quick mounting connector)
Ambient temperature (storage/transport)	-40 °C ... 80 °C
Altitude	5000 m

Material data

Material	Aluminum (Separating foil)
----------	----------------------------

Electrical characteristics

FO cable - FL FOC PN-B-980/1000 - 2313397

Technical data

Electrical characteristics

Number of positions	2
---------------------	---

Line characteristics

Cable abbreviation	J-V11Y 4Y2P 980/1000 160A 10
Length of cable	Free input (0.4 ... 100 m)
External cable diameter	8 mm
Wire colors	Black and orange with arrow labeling
External sheath, color	green
Outer sheath, material	PUR
Strain relief elements, external sheath	Non-metallic, aramide fiber
Cable weight	49 kg/km
Bending radius, single element	30 mm (Short-term) 30 mm (Permanent)
Bending radius, entire cable	65 mm (Short-term) 65 mm (Permanent)
Tensile strength short-term/long-term	1000 N / 100 N
Lateral pressure short term	200 N/cm
Lateral pressure, long-term	20 N/cm
Impact strength	2 Nm / 10 x
cable layer type	Indoors
Halogen-free	According to IEC 60754-2
Resistance to oil	IRM 902 No.2, 100 °C, DIN VDE 0473-811-2-1
Fiber	Polymer fiber, 980/1000 µm

Attenuation

660 nm	230 dB/km
--------	-----------

Standards and Regulations

Resistance to oil	IRM 902 No.2, 100 °C, DIN VDE 0473-811-2-1
Impact strength	2 Nm / 10 x
Halogen-free	According to IEC 60754-2
Behavior in fire	1.62 MJ/m (0.39 kWh/m)

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Classifications

eCl@ss

eCl@ss 10.0.1	27061803
eCl@ss 4.0	24010400
eCl@ss 4.1	24010400

FO cable - FL FOC PN-B-980/1000 - 2313397

Classifications

eCl@ss

eCl@ss 5.0	19030300
eCl@ss 5.1	19030300
eCl@ss 6.0	27061800
eCl@ss 7.0	27061803
eCl@ss 8.0	27061803
eCl@ss 9.0	27061803

ETIM

ETIM 2.0	EC000034
ETIM 3.0	EC000034
ETIM 4.0	EC000034
ETIM 5.0	EC000034
ETIM 6.0	EC000034
ETIM 7.0	EC000034

UNSPSC

UNSPSC 6.01	26121607
UNSPSC 7.0901	26121607
UNSPSC 11	26121607
UNSPSC 12.01	26121607
UNSPSC 13.2	26121607
UNSPSC 18.0	26121607
UNSPSC 19.0	26121607
UNSPSC 20.0	26121607
UNSPSC 21.0	26121607

Accessories

Accessories

Data cable preassembled

FO patch cable - FOC-PN-B-1000/IP20/... - 2901551



POF PROFINET installation cable for assembly (IP20 heads only) for installation in stationary systems and machines, individual elements of polyamide (PA), halogen-free, ozone- and UV-resistant, with reinforced polyurethane (PUR) outer sheath

FO cable - FL FOC PN-B-980/1000 - 2313397

Accessories

FO patch cable - FOC-PN-B-1000/... - 1402172



POF PROFINET installation cable for fixed installation in the inner area with individual elements made of highly durable polyamide (PA). Individual elements made of extremely wear-resistant polyamide (PA). The cable is halogen-free, ozone and UV resistant and has a rugged polyurethane (PUR) outer sheath.

Data plug

FO connectors - PSM-SET-SCRJ-DUP/2-POF - 2708656



SC-RJ connector set for polymer fiber, for self assembly, consisting of 2 duplex quick mounting connectors with bending protection

FO connectors - PSM-SET-FSMA/4-KT - 2799720



F-SMA plug set for polymer fiber, for self assembly consisting of 4 quick mounting connectors with bend protection sleeve

Assembly tool - PSM-SET-FSMA-POLISH - 2799348



Polymer fiber polishing set, for F-SMA quick mounting connectors

Assembly tool - PSM-POF-KONFTOOL - 2744131



Polymer fiber DIY case, consisting of: Stripping knife, stripping pliers, polishing wheels for F-SMA and SC-RJ quick mounting connectors, polishing pad and emery paper

Stripping tool

FO cable - FL FOC PN-B-980/1000 - 2313397

Accessories

Stripping tool - WIREFOX-D 16 - 1212173



Stripping tool, for stripping lines (specially for fiber optics lines) of Ø 4 - 16 mm

FO accessories - VS-SCRJ-POF-POLISH - 1656673



Refilling set for VS-SC-RJ-POF-KONFTOOL-POLISH, consisting of two polishing discs and a polisher

Phoenix Contact 2020 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[2313397](#)