

Touch panel - TP11AM/702001 S00001 - 2400860

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Touch panel with 9.7 cm/3.8" FSTN-display (analog resistive (polyester)), 320 x 240 pixel(s) (QVGA), 5 grayscales, Arm9™, 200 MHz, 2x USB host 2.0, 1 x Ethernet (10/100 Mbps), RJ45, Windows CE 5.0 and user software: TSvisRT. (bus system: without)

RoHS

Key Commercial Data

Packing unit	1 pc
GTIN	 4 055626 097305
GTIN	4055626097305

Technical data

Dimensions

Outer dimensions: width, height, depth	130 mm x 96 mm x 5 mm (Dimensions of the front plate)
Installation dimensions: width, height, depth	122 mm x 88 mm x 45 mm (Mounting cutout, depth with bus if bus system present in the device)

Display

Display type	9.7 cm/3.8" FSTN
Screen resolution	320 x 240 Pixel(s) (QVGA)
Touch technology	analog resistive (polyester)
Brightness	90 cd/m ²
Backlighting	LED
Display backlight MTBF	30000 h
Colors	5 grayscales
Reading angle left	40 °
Reading angle right	40 °
Reading angle top	40 °
Reading angle bottom	40 °

Computer data

Processor	Arm9™, 200 MHz
-----------	----------------

Touch panel - TP11AM/702001 S00001 - 2400860

Technical data

Computer data

Operating system	Windows® CE 5.0
User software	TSvisRT
RAM	64 MB SDRAM
	512 KB SRAM
Mass storage	NOR-Flash, 32 MB
Network	1 x Ethernet (10/100 Mbps), RJ45
Interfaces	2x USB Host 2.0
Bus system	without
Optional interfaces	none
Realtime clock	Yes
Service life of battery	5 years (typical)

General

Material front plate	Aluminum (natural anodized)
Housing material	Steel sheet, zinc-plated
Mounting type	Front installation
Weight	680 g

Ambient conditions

Degree of protection	IP65 (front), IP20 (back)
	NEMA 4X
Ambient temperature (operation)	0 °C ... 50 °C
Ambient temperature (storage/transport)	-25 °C ... 70 °C
Permissible humidity (operation)	20 % ... 85 %
Vibration (operation)	1g, according to EN 60068-2-6
Shock	15g, according to IEC 60068-2-27

Device supply

Typical current consumption	0.25 A
Power supply unit	24 V DC ±20 %

Standards and Regulations

Shock	15g, according to IEC 60068-2-27
Vibration (operation)	1g, according to EN 60068-2-6

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
China RoHS	Environmentally Friendly Use Period = 15;
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

Touch panel - TP11AM/702001 S00001 - 2400860

Classifications

eCl@ss

eCl@ss 10.0.1	27330201
eCl@ss 4.0	27330200
eCl@ss 4.1	27330200
eCl@ss 5.0	27330200
eCl@ss 5.1	27330200
eCl@ss 6.0	27242300
eCl@ss 7.0	27242302
eCl@ss 8.0	27242302
eCl@ss 9.0	27330201

ETIM

ETIM 4.0	EC001412
ETIM 5.0	EC001412
ETIM 6.0	EC001412
ETIM 7.0	EC001412

UNSPSC

UNSPSC 13.2	43211904
UNSPSC 18.0	43211904
UNSPSC 19.0	43211904
UNSPSC 20.0	43211904
UNSPSC 21.0	43211904

Accessories

Accessories

Battery module

Battery / accumulator - HMI BATTERY - 2701383

Lithium battery



Mounting material

Mounting material - HMI SCB MOUNTING KIT 4 - 2701384



HMI mounting kit for installation on a front plate. The mounting kit includes 4 x mounting brackets, 4 x screw threads, and a hexagonal wrench.

Touch panel - TP11AM/702001 S00001 - 2400860

Accessories

Mounting material - HMI SCB MOUNTING KIT 6 - 2701385



HMI mounting kit for installation on a front plate. The mounting kit includes 6 x mounting brackets, 6 x screw threads, and a hexagonal wrench.

Mounting material - HMI SCB MOUNTING KIT 8 - 2701387



HMI mounting kit for installation on a front plate. The mounting kit includes 8 x mounting brackets, 8 x screw threads, and a hexagonal wrench.

Mounting material - HMI WALL MOUNTING KIT - 2701380



HMI mounting kit for panel installation. The mounting kit includes 2 spring clips.

Operating stylus

Touch pen - TOUCH PEN - 2701379



Touch pen for analog-resistive HMIs, silver coated. Delivery includes self-adhesive pen holder.

PCB plug

Printed-circuit board connector - MSTB 2,5/ 3-STF BD:1-3 - 1896381



PCB connector, nominal current: 12 A, rated voltage (III/2): 320 V, nominal cross section: 2.5 mm², number of positions: 3, pitch: 5 mm, connection method: Screw connection with tension sleeve, color: green, contact surface: Tin

Storage medium

Touch panel - TP11AM/702001 S00001 - 2400860

Accessories

USB memory stick - USB FLASH DRIVE - 2402809



USB memory stick, 8 GB

Phoenix Contact 2020 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[2400860](#)