

Touch panel - TP11AM/762001 S00001 - 2400867

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Touch panel with 9.7 cm/3.8" FSTN-display (analog resistive (polyester)), 320 x 240 pixel(s) (QVGA), 5 grayscales, Arm9™, 200 MHz, 2x USB host 2.0, 1 x Ethernet (10/100 Mbps), RJ45, Windows CE 5.0 and user software: TSvisRT. (bus system: INTERBUS 512 kbps)



Key Commercial Data

| | |
|--------------|---|
| Packing unit | 1 pc |
| GTIN |  4 055626 097237 |
| GTIN | 4055626097237 |

Technical data

Dimensions

| | |
|---|---|
| Outer dimensions: width, height, depth | 130 mm x 96 mm x 5 mm (Dimensions of the front plate) |
| Installation dimensions: width, height, depth | 122 mm x 88 mm x 45 mm (Mounting cutout, depth with bus system present in the device) |

Display

| | |
|------------------------|------------------------------|
| Display type | 9.7 cm/3.8" FSTN |
| Screen resolution | 320 x 240 Pixel(s) (QVGA) |
| Touch technology | analog resistive (polyester) |
| Brightness | 90 cd/m² |
| Backlighting | LED |
| Display backlight MTBF | 30000 h |
| Colors | 5 grayscales |
| Reading angle left | 40 ° |
| Reading angle right | 40 ° |
| Reading angle top | 40 ° |
| Reading angle bottom | 40 ° |

Computer data

| | |
|-----------|----------------|
| Processor | Arm9™, 200 MHz |
|-----------|----------------|

Touch panel - TP11AM/762001 S00001 - 2400867

Technical data

Computer data

| | |
|-------------------------|----------------------------------|
| Operating system | Windows® CE 5.0 |
| User software | TSvisRT |
| RAM | 64 MB SDRAM |
| | 512 KB SRAM |
| Mass storage | NOR-Flash, 32 MB |
| Network | 1 x Ethernet (10/100 Mbps), RJ45 |
| Interfaces | 2x USB Host 2.0 |
| Bus system | INTERBUS 512 kbps |
| Optional interfaces | none |
| Realtime clock | Yes |
| Service life of battery | 5 years (typical) |

General

| | |
|----------------------|-----------------------------|
| Material front plate | Aluminum (natural anodized) |
| Housing material | Steel sheet, zinc-plated |
| Mounting type | Front installation |
| Weight | 680 g |

Ambient conditions

| | |
|---|----------------------------------|
| Degree of protection | IP65 (front), IP20 (back) |
| | NEMA 4X |
| Ambient temperature (operation) | 0 °C ... 50 °C |
| Ambient temperature (storage/transport) | -25 °C ... 70 °C |
| Permissible humidity (operation) | 20 % ... 85 % |
| Vibration (operation) | 1g, according to EN 60068-2-6 |
| Shock | 15g, according to IEC 60068-2-27 |

Device supply

| | |
|-----------------------------|---------------|
| Typical current consumption | 0.25 A |
| Power supply unit | 24 V DC ±20 % |

Standards and Regulations

| | |
|-----------------------|----------------------------------|
| Shock | 15g, according to IEC 60068-2-27 |
| Vibration (operation) | 1g, according to EN 60068-2-6 |

Environmental Product Compliance

| | |
|------------|---|
| China RoHS | Environmentally Friendly Use Period = 15; |
| | For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration" |

Classifications

eCl@ss

| | |
|------------|----------|
| eCl@ss 4.0 | 27330200 |
|------------|----------|

Touch panel - TP11AM/762001 S00001 - 2400867

Classifications

eCl@ss

| | |
|------------|----------|
| eCl@ss 4.1 | 27330200 |
| eCl@ss 5.0 | 27330200 |
| eCl@ss 5.1 | 27330200 |
| eCl@ss 6.0 | 27242300 |
| eCl@ss 7.0 | 27242302 |
| eCl@ss 8.0 | 27242302 |
| eCl@ss 9.0 | 27330201 |

ETIM

| | |
|----------|----------|
| ETIM 4.0 | EC001412 |
| ETIM 5.0 | EC001412 |
| ETIM 6.0 | EC001412 |
| ETIM 7.0 | EC001412 |

UNSPSC

| | |
|-------------|----------|
| UNSPSC 13.2 | 43211904 |
| UNSPSC 19.0 | 43211904 |

Accessories

Accessories

Battery module

Battery / accumulator - HMI BATTERY - 2701383

Lithium battery



Mounting material

Mounting material - HMI SCB MOUNTING KIT 4 - 2701384



HMI mounting kit for installation on a front plate. The mounting kit includes 4 x mounting brackets, 4 x screw threads, and a hexagonal wrench.

Touch panel - TP11AM/762001 S00001 - 2400867

Accessories

Mounting material - HMI SCB MOUNTING KIT 6 - 2701385



HMI mounting kit for installation on a front plate. The mounting kit includes 6 x mounting brackets, 6 x screw threads, and a hexagonal wrench.

Mounting material - HMI SCB MOUNTING KIT 8 - 2701387



HMI mounting kit for installation on a front plate. The mounting kit includes 8 x mounting brackets, 8 x screw threads, and a hexagonal wrench.

Mounting material - HMI WALL MOUNTING KIT - 2701380



HMI mounting kit for panel installation. The mounting kit includes 2 spring clips.

Operating stylus

Touch pen - TOUCH PEN - 2701379



Touch pen for analog-resistive HMIs, silver coated. Delivery includes self-adhesive pen holder.

PCB plug

Printed-circuit board connector - MSTB 2,5/ 3-STF BD:1-3 - 1896381



PCB connector, nominal current: 12 A, rated voltage (III/2): 320 V, nominal cross section: 2.5 mm², number of positions: 3, pitch: 5 mm, connection method: Screw connection with tension sleeve, color: green, contact surface: Tin

Storage medium

Touch panel - TP11AM/762001 S00001 - 2400867

Accessories

USB memory stick - USB FLASH DRIVE - 2402809



USB memory stick, 8 GB

Phoenix Contact 2020 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[2400867](#)