

## Adapter plate - HC-B 6-ADP/2 DSUB 15 - 1775486


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



D-SUB adapter plate, for two D-SUB connectors, no. of positions 15, housing series HC-B 6...

RoHS

### Key Commercial Data

|                        |   |
|------------------------|---|
| Packing unit           | 2 pc  |
| Minimum order quantity | 2 pc  |
| GTIN                   | <br>4 017918 038083 |
| GTIN                   | 4017918038083   |

### Technical data

#### Dimensions

|        |         |
|--------|---------|
| Length | 51.5 mm |
| Height | 10 mm   |
| Width  | 34.5 mm |

#### General

|  |  |
|--|--|
| Note                                   | For housing HC-B6  |
| Material                               | PA   |
| Flammability rating according to UL 94 | HB   |
| Color                                  | gray   |
| Number of positions                    | 15   |
| Type                                   | B6   |
| Connection                             | Mounting position of the adapter plate in the sleeve housing: T is visible after mounting in the housing. Mounting position of the adapter plate in the panel mounting base/socket housing/coupling housing: A is visible after mounting in the housing. Mounting position of the D-SUB (after mounting in the housing): in front of the mounting plate (front mounting) |

### Standards and Regulations

|  |    |
|--|----|
| Flammability rating according to UL 94 | HB |
|--|----|

## Adapter plate - HC-B 6-ADP/2 DSUB 15 - 1775486


### Technical data

#### Environmental Product Compliance

|            |   |
|------------|---|
| China RoHS | Environmentally Friendly Use Period = 50 years  |
|            | For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration" |

### Drawings

Dimensional drawing



See assembly instruction

### Classifications

eCl@ss

|               |          |
|---------------|----------|
| eCl@ss 10.0.1 | 27440201 |
| eCl@ss 4.0    | 27140800 |
| eCl@ss 4.1    | 27140800 |
| eCl@ss 5.0    | 27143400 |
| eCl@ss 5.1    | 27143400 |
| eCl@ss 6.0    | 27261200 |
| eCl@ss 7.0    | 27440201 |
| eCl@ss 8.0    | 27440201 |
| eCl@ss 9.0    | 27440201 |

## Adapter plate - HC-B 6-ADP/2 DSUB 15 - 1775486

### Classifications

#### ETIM

|          |          |
|----------|----------|
| ETIM 3.0 | EC002309 |
| ETIM 4.0 | EC002309 |
| ETIM 5.0 | EC002309 |
| ETIM 6.0 | EC002309 |
| ETIM 7.0 | EC002309 |

#### UNSPSC

|               |          |
|---------------|----------|
| UNSPSC 6.01   | 30211808 |
| UNSPSC 7.0901 | 39121408 |
| UNSPSC 11     | 39121408 |
| UNSPSC 12.01  | 39121408 |
| UNSPSC 13.2   | 31261501 |
| UNSPSC 18.0   | 31261501 |
| UNSPSC 19.0   | 31261501 |
| UNSPSC 20.0   | 31261501 |
| UNSPSC 21.0   | 31261501 |

### Approvals

#### Approvals

#### Approvals

#### EAC

#### Ex Approvals

#### Approval details

|     |   |                          |
|-----|---|--------------------------|
| EAC |  | RU C-<br>DE.AI30.B.01102 |
|-----|---|--------------------------|

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Phoenix Contact:

1775486