

## Measuring instrument - PSM-FO-POWERMETER - 2799539

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Fiber optic measuring case, consisting of an optical power meter, F-SMA, B-FOC adapters, reference fibers and operating instructions

### Your advantages

- ✓ Suitable for termination devices with and F-SMA, B-FOC (ST®) connection
- ✓ Measurement at SC-RJ and SC duplex connection using add-on set
- ✓ The power meter can be switched between the following wavelengths: 660 nm, 780 nm, and 850 nm
- ✓ Reference cables with polymer fibers, PCF fibers, and fiberglass

**RoHS**

### Key Commercial Data

|              |                                                                                                         |
|--------------|---------------------------------------------------------------------------------------------------------|
| Packing unit | 1 pc                                                                                                    |
| GTIN         | <br>4 017918 126735 |
| GTIN         | 4017918126735                                                                                           |

### Technical data

#### Environmental Product Compliance

|            |                                                         |
|------------|---------------------------------------------------------|
| China RoHS | Environmentally friendly use period: unlimited = EFUP-e |
|            | No hazardous substances above threshold values          |

### Classifications

#### eCl@ss

|               |          |
|---------------|----------|
| eCl@ss 10.0.1 | 27144440 |
| eCl@ss 4.0    | 24010400 |
| eCl@ss 4.1    | 24010400 |
| eCl@ss 5.0    | 19030300 |
| eCl@ss 5.1    | 19030300 |
| eCl@ss 6.0    | 27061800 |

## Measuring instrument - PSM-FO-POWERMETER - 2799539

### Classifications

#### eCl@ss

|            |          |
|------------|----------|
| eCl@ss 7.0 | 27061803 |
| eCl@ss 8.0 | 27149249 |
| eCl@ss 9.0 | 27144440 |

#### ETIM

|          |          |
|----------|----------|
| ETIM 2.0 | EC001125 |
| ETIM 3.0 | EC001125 |
| ETIM 4.0 | EC002609 |
| ETIM 5.0 | EC002609 |
| ETIM 6.0 | EC002609 |
| ETIM 7.0 | EC002609 |

#### UNSPSC

|               |          |
|---------------|----------|
| UNSPSC 6.01   | 26121607 |
| UNSPSC 7.0901 | 26121607 |
| UNSPSC 11     | 26121607 |
| UNSPSC 12.01  | 26121607 |
| UNSPSC 13.2   | 26121650 |
| UNSPSC 18.0   | 26121650 |
| UNSPSC 19.0   | 26121650 |
| UNSPSC 20.0   | 26121650 |
| UNSPSC 21.0   | 26121650 |

### Accessories

#### Accessories

#### Data plug

#### Measuring device adapter - PSM-FO-POWERMETER SCRJ-SET - 2901560



Powermeter supplementary set for devices with SC-RJ interface, consisting of one-meter polymer reference fiber (SC Simplex connector to F-SMA connector), one-meter of PCF-GI reference fiber (SC Simplex connector to B-FOC (ST®) connector) and SC-RJ coupling

### Additional products

#### Measuring device adapter - PSM-FO-POWERMETER SCRJ-SET - 2901560



Powermeter supplementary set for devices with SC-RJ interface, consisting of one-meter polymer reference fiber (SC Simplex connector to F-SMA connector), one-meter of PCF-GI reference fiber (SC Simplex connector to B-FOC (ST®) connector) and SC-RJ coupling

## Measuring instrument - PSM-FO-POWERMETER - 2799539

### Accessories

---

Phoenix Contact 2020 © - all rights reserved  
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG  
Flachsmarktstr. 8  
32825 Blomberg  
Germany  
Tel. +49 5235 300  
Fax +49 5235 3 41200  
<http://www.phoenixcontact.com>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Phoenix Contact:

2799539