

Media module - FL IF 2FX SC-F - 2832412

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Fiber optic interface module for connecting 100 Base-FX multi-mode glass fibers (1300 nm), SC, connection direction forward

Your advantages

- ✓ Robust Ethernet transmission even for medium-range environments prone to interference

RoHS

Key Commercial Data

Packing unit	1 pc
GTIN	 4 017918 974466
GTIN	4017918974466

Technical data

Note

Utilization restriction	EMC: class A product, see manufacturer's declaration in the download area
-------------------------	---

Dimensions

Caption	The figure shows a version of the interface module with the head station FL SWITCH MM HS
Width	31 mm
Height	75.7 mm
Depth	72.5 mm

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	0 °C ... 55 °C (non-condensing)
Ambient temperature (storage/transport)	-20 °C ... 70 °C
Permissible humidity (operation)	10 % ... 95 % (non-condensing)
Permissible humidity (storage/transport)	10 % ... 95 % (non-condensing)

Interfaces

Media module - FL IF 2FX SC-F - 2832412

Technical data

Interfaces

Interface	Ethernet: 100Base-FX in acc. with IEEE 802.3
Transmission length	10000 m (maximum (depends on the fiber used))
Interface	Ethernet: 100Base-FX in acc. with IEEE 802.3
No. of ports	2 (SC multi-mode)
Transmission speed	100 Mbps
Transmission length	2800 m (fiberglass with F-G 50/125 1.6 dB/km F800)
	6400 m (fiberglass with F-G 50/125 0.7 dB/km F1200)
	3000 m (fiberglass with F-G 62.5/125 2.6 dB/km F600)
	2800 m (fiberglass with F-G 50/125 1.6 dB/km F800)
Wavelength	1300 nm

Function

Basic functions	Media module for modular managed switch
-----------------	---

Supply voltage

Supply voltage	via head station
Typical current consumption	200 mA

General

Mounting type	In the host system
Type AX	Stand-alone
Net weight	80 g
Housing material	PA

Mechanical tests

Type of test	Shock in acc. with EN 60068-2-27/IEC 60068-2-27
Test result	Operation: 25g, 11 ms duration, semi-sinusoidal shock impulse
Type of test	Shock in acc. with EN 60068-2-27/IEC 60068-2-27
Test result	Storage/Transport: 50g, 11 ms duration, semi-sinusoidal shock impulse
Flammability rating according to UL 94	V0

Conformity with EMC directives

Developed in acc. with standard	IEC 61000-6-2
Test standard	IEC 61000-4-2 (ESD)
Test result	Criterion B
Test standard	IEC 61000-4-3 (immunity to radiated interference)
Test result	Criterion A
Test standard	IEC 61000-4-4 (burst)
Test result	Criterion A
Test standard	IEC 61000-4-5 (surge)
Test result	Criterion A
Test standard	IEC 61000-4-6 (immunity to conducted interference)
Test result	Criterion A

Media module - FL IF 2FX SC-F - 2832412

Technical data

Conformity with EMC directives

Test standard	IEC 61000-4-8 (immunity to magnetic fields)
Test result	Criterion A
Test standard	EN 55022 (emitted interference)
Test result	Criterion A

Standards and Regulations

Electromagnetic compatibility	Conformance with EMC Directive 2004/108/EC
Type of test	Shock in acc. with EN 60068-2-27/IEC 60068-2-27
Test result	Operation: 25g, 11 ms duration, semi-sinusoidal shock impulse
Type of test	Shock in acc. with EN 60068-2-27/IEC 60068-2-27
Test result	Storage/Transport: 50g, 11 ms duration, semi-sinusoidal shock impulse
Noise emission	EN 61000-6-3/-4
Noise immunity	EN 61000-6-2:2005
Vibration (storage/transport)	5g, 150 Hz, in acc. with IEC 60068-2-6
Free from substances that could impair the application of coating	In acc. with VW specification
Connection in acc. with standard	CUL
Electrical isolation	100Base-FX // supply
Flammability rating according to UL 94	V0
Vibration (operation)	in acc. with IEC 60068-2-6: 5g, 150 Hz

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Classifications

eCl@ss

eCl@ss 4.0	27250500
eCl@ss 4.1	27250500
eCl@ss 5.0	19030100
eCl@ss 5.1	19030100
eCl@ss 6.0	19170100
eCl@ss 7.0	19170390
eCl@ss 8.0	19170390
eCl@ss 9.0	19170390

ETIM

ETIM 2.0	EC000734
ETIM 3.0	EC000734
ETIM 4.0	EC001467
ETIM 5.0	EC000309

Media module - FL IF 2FX SC-F - 2832412

Classifications

ETIM

ETIM 6.0	EC000309
ETIM 7.0	EC000309

UNSPSC

UNSPSC 6.01	43172015
UNSPSC 7.0901	43201404
UNSPSC 11	43172015
UNSPSC 12.01	43201410
UNSPSC 13.2	43201410
UNSPSC 18.0	43223108
UNSPSC 19.0	43223108
UNSPSC 20.0	43223108
UNSPSC 21.0	43223108

Approvals

Approvals

Approvals

UL Recognized / cUL Recognized / KC / EAC / cULus Recognized

Ex Approvals

UL Listed / cUL Listed / cULus Listed

Approval details

UL Recognized		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	FILE E 140324
---------------	---	---	---------------

cUL Recognized		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	FILE E 140324
----------------	---	---	---------------

KC		http://eng.kcc.go.kr/user/ehpMain.do	KCC-REI- PCK-FL283241
----	---	---	--------------------------

EAC			RU*DE*08.B.00731/19
-----	---	--	---------------------

Media module - FL IF 2FX SC-F - 2832412

Approvals

cULus Recognized



Accessories

Accessories

Data cable by the meter

FO cable - PSM-LWL-GDM-RUGGED- 50/125 - 2799322



Fiber glass cable, duplex 50 µm/125 µm, by the meter, without male connector, for installation in stationary systems and machines

FO cable - PSM-LWL-GDO- 50/125 - 2799432



Fiberglass cable, duplex 50/125 µm, by the meter, without connector, for outdoor installation

FO cable - FL FOC PN-C-HCS-GI-200/230 - 2313410



PROFINET HCS GI fiber cables, duplex 200/230 µm, increased bandwidth for Ethernet applications in particular. Robust PUR outer sheath. Heavy version suitable for drag chains and indoor installation, sold by the meter without plugs

Data cable preassembled

FO patch cable - FOC-LC:PA-SC:PA-OM2:D01/1 - 1115607



Media module - FL IF 2FX SC-F - 2832412

Accessories

FO patch cable - FOC-LC:PA-SC:PA-OM2:D01/2 - 1115605



FO patch cable - FOC-SC:PA-SC:PA-OM2:D01/1 - 1115536



Multi-mode OM2 duplex jumper, SC-SC, UPC polishing, length 1 m

FO patch cable - FOC-SC:PA-SC:PA-OM2:D01/1 - 1115536



Multi-mode OM2 duplex jumper, SC-SC, UPC polishing, length 1 m

FO patch cable - FOC-SC:PA-SC:PA-OM2:D01/2 - 1115535



Multi-mode OM2 duplex jumper, SC-SC, UPC polishing, length 2 m

FO patch cable - FOC-ST:PA-SC:PA-OM2:D01/1 - 1115574



Multi-mode OM2 duplex jumper, ST-SC, UPC polishing, length 1 m

Media module - FL IF 2FX SC-F - 2832412

Accessories

FO patch cable - FOC-ST:PA-SC:PA-OM2:D01/2 - 1115573



Multi-mode OM2 duplex jumper, ST-SC, UPC polishing, length 2 m

FO patch cable - FOC-LC:PA-SC:PA-OM4:D01/1 - 1115601



Multi-mode OM4 duplex jumper, LC-SC, UPC polishing, length 1 m

FO patch cable - FOC-LC:PA-SC:PA-OM4:D01/2 - 1115600



Multi-mode OM4 duplex jumper, LC-SC, UPC polishing, length 2 m

FO patch cable - FOC-SC:PA-SC:PA-OM4:D01/1 - 1115424



Multi-mode OM4 duplex jumper, SC-SC, UPC polishing, length 1 m

FO patch cable - FOC-SC:PA-SC:PA-OM4:D01/2 - 1115423



Multi-mode OM4 duplex jumper, SC-SC, UPC polishing, length 2 m

Media module - FL IF 2FX SC-F - 2832412

Accessories

FO patch cable - FOC-GDM-RUGGED-1016/IP20/... - 2901558



Robust GOF installation cable for assembly (IP20 heads only) for installation in stationary systems and machines, aramid strain-relief elements, with individual elements made from FRNC material, halogen-free, ozone and UV resistant, with a polyurethane (PUR) outer sheath

FO patch cable - FOC-GDM-RUGGED-1016/... - 1402193



rugged GOF installation cable for inner areas with highly tear-proof aramid strain-relief elements. Individual elements consist of highly flexible FRNC material. The cable is halogen-free, ozone and UV resistant and has a rugged polyurethane (PUR) outer sheath.

FO patch cable - FOC-GDO-1017/IP20/... - 2901559



Highly rugged GOF round cable (IP20 heads only) for assembly and for outdoor installation with integrated moisture barrier as well as rodent-proof scrim. Individual elements made from highly flexible FRNC material. The wire is ozone and UV resistant with a very rugged polyethylene outer sheath.

FO patch cable - FOC-PN-HCS-GI-1005/IP20/... - 2901554



PROFINET HCS GI installation cable for assembly (IP20 heads only), suitable for drag chains, for indoor installation, gradient index fibers. Individual elements made from highly flexible FRNC material. Halogen-free, ozone and UV resistant with a polyurethane (PUR) outer sheath.

FO patch cable - FOC-PN-HCS-GI-1005/... - 1402189



HCS-GI installation cable for assembly for fixed installation in the inner area, with gradient index fibers for the highest performance requirements, as well as individual elements made of highly flexible FRNC material. The cable is halogen-free, ozone and UV resistant and has a rugged polyurethane (PUR) outer sheath.

Terminal marking

Media module - FL IF 2FX SC-F - 2832412

Accessories

Zack Marker strip, flat - ZBF 29:UNBEDRUCKT - 0829003



Zack Marker strip, flat, Strip, white, unlabeled, can be labeled with: PLOTMARK, CMS-P1-PLOTTER, mounting type: snap into flat marker groove, for terminal block width: 29 mm, lettering field size: 29 x 6.4 mm, Number of individual labels: 3

Phoenix Contact 2020 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[2832412](#)